

HIGH CARRYING CURRENT TYPE MINIATURE LOW PROFILE AUTOMOTIVE RELAY





FEATURES

Compact flat type

We successfully developed a high carrying current type that is the same size as our CP relay (14 mm (L) x 13 mm (W) x 9.5 mm (H) .551 inch (L) x .512 inch (W) x .374 inch (H))

• 35A maximum carrying current Current carrying of 35 A/1h and 45 A/2 min. at 20°C (450 W type, 16 V applied) is possible due to use of N.O. double pin terminals

and COM terminal width expansion.

 Supports capacitor loads required for power supply applications
 Inrush current: 60A, steady-state current: 1A and 10⁵ switching times possible.


• Plastic sealed type
This plastic sealed type can be
automatically cleaned.

TYPICAL APPLICATIONS

For automotive system

Defoggers, Ignitions, Heaters, Accessories, Power windows, etc.

ORDERING INFORMATION



TYPES

Contact arrangement	Coil voltage	Pick-up voltage (at 20°C 68°F)	Part No.	
1 Form C	12 V DC	Max. 7.2 V DC (Initial)	CP1H-12V	
		Max. 6.5 V DC (Initial)	CP1H-N-12V	
1 Form A		Max. 7.2 V DC (Initial)	CP1aH-12V	
		Max. 6.5 V DC (Initial)	CP1aH-N-12V	

Standard packing: Carton (Tube): 40 pcs.; Case: 1,000 pcs.

Note: THD type only

CP POWER

RATING

1. Coil data

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power (at 20°C 68°F)	Usable voltage range (at 85°C 185°F)
12V DC	Max. 7.2 V DC (Initial)	Min. 1.0 V DC (Initial)	37.5 mA	320Ω	450 mW	10 to 16V DC
	Max. 6.5 V DC (Initial)		53.3 mA	225Ω	640 mW	10 to 16V DC

Specifications

Characteristics	Item		Specifications		
Contact	Arrangement		1 Form A, 1 Form C		
	Contact resistance (Initial)		N.O.: Typ 6mΩ, N.C.: Typ 8mΩ (By voltage drop 6V DC 1A)		
	Contact material		Ag alloy (Cadmium free)		
Rating	Nominal switching capacity (resistive load)		N.O.: 20 A 14V DC, N.C.: 10 A 14V DC		
	Max. carrying current (16V DC)*3		N.O.: <for 450="" mw=""> 45 A for 2 minutes, 35 A for 1 hour at 20°C 68°F 40 A for 2 minutes, 30 A for 1 hour at 85°C 185°F <for 640="" mw=""> 40 A for 2 minutes, 30 A for 1 hour at 20°C 68°F 35 A for 2 minutes, 25 A for 1 hour at 85°C 185°F</for></for>		
	Nominal operating power		450 mW for pick-up voltage 7.2 V DC, 640 mW for pick-up voltage 6.5 V DC		
	Min. switching capacity (resistive load)*1		1 A 14V DC		
Electrical characteristics	Insulation resistance (Initial)		Min. 100 MΩ (at 500V DC, Measurement at same location as "Breakdown voltage" section.)		
	Breakdown voltage (Initial)	Between open contacts	500 Vrms for 1 min. (Detection current: 10mA)		
		Between contacts and coil	500 Vrms for 1 min. (Detection current: 10mA)		
	Operate time (at nominal voltage)		Max. 10ms (at 20°C 68°F, excluding contact bounce time) (Initial)		
	Release time (at nominal voltage)		Max. 10ms (at 20°C 68°F, excluding contact bounce time) (Initial)		
Mechanical characteristics	Shock resistance	Functional	Min. 100 m/s² {10G} (Half-wave pulse of sine wave: 11ms; detection time: 10μs)		
		Destructive	Min. 1,000 m/s ² {100G} (Half-wave pulse of sine wave: 6ms)		
	Vibration resistance	Functional	10 Hz to 100 Hz, Min. 44.1 m/s² {4.5G} (Detection time: $10\mu s$)		
		Destructive	10 Hz to 500 Hz, Min. 44.1 m/s² {4.5G}, Time of vibration for each direction; X, Y direction: 2 hours, Z direction: 4 hours		
Expected life	Mechanical		Min. 10 ⁷ (at 120 cpm)		
	Electrical		<resistive load=""> Min. 10⁵ (at nominal switching capacity, operating frequency: 1s ON, 9s OFF) <capacitor load=""> Min. 10⁵ (at Inrush 60A, Steady 1A 14 V DC, operating frequency: 1s ON, 9s OFF)</capacitor></resistive>		
Conditions	Conditions for operation, transport and storage*2		Ambient temperature: -40°C to +85°C -40°F to +185°F, Humidity: 5% R.H. to 85% R.H. (Not freezing and condensing at low temperature)		
	Max. operating speed		6 cpm (at nominal switching capacity)		
Mass			Approx. 4.5 g .16 oz		


Notes:
*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.
*2. The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. Refer to "6. Usage, Storage and Transport Conditions" in AMBIENT ENVIRONMENT section in Relay Technical Information.

Please inquire if you will be using the relay in a high temperature atmosphere (110°C 230°F).


*3. Depends on connection conditions. Also, this does not guarantee repeated switching. We recommend that you confirm operation under actual conditions.

REFERENCE DATA


1-(1). Coil temperature rise Sample: CP1H-12V, 3pcs Point measured : Inside the coil Ambient temperature: 27°C 81°F



1-(2). Coil temperature rise Sample: CP1H-12V, 3pcs Point measured : Inside the coil Ambient temperature: 85°C 185°F




2. Ambient temperature and operating voltage range




3-(1). Distribution of pick-up and drop-out voltage

Sample: CP1H-12V, 20pcs.




3-(2). Distribution of pick-up and drop-out voltage

Sample: CP1H-N-12V, 20pcs.



4-(1). Distribution of operate and release time Sample: CP1H-12V, 20pcs.





4-(2). Distribution of operate and release time Sample: CP1H-N-12V, 20pcs.


5-(1). Electrical life test (at rated load)

Sample : CP1H-12V

Quantity: n = 6
Load: Resistive load (N.O. side: 20 A 14 V DC)
Operating frequency: ON 1s, OFF 9s
Ambient temperature: Room temperature










5-(2). Electrical life test (at capacitor load)

Sample : CP1H-12V, 6pcs. Load: Inrush 60A/steady 1A
Operating frequency: ON 1s, OFF 9s
Ambient temperature: Room temperature

Circuit:








DIMENSIONS (mm inch)

Download **CAD Data** from our Web site.

CAD Data

External dimensions




 Dimension:
 Tolerance

 Max. 1mm .039 inch:
 ±0.1 ±.004

 1 to 3mm .039 to .118 inch:
 ±0.2 ±.008

 Min. 3mm .118 inch:
 ±0.3 ±.012

PC board pattern (Bottom view)



Tolerance: ±0.1 ±.004

Schematic (Bottom view)



* Dimensions (thickness and width) of terminal is measured before pre-soldering. Intervals between terminals is measured at A surface level.

For Cautions for Use, see Relay Technical Information.