# **MEDER electronic**

DIP Series Molded DIP Reed Relays

## **DESCRIPTION**

The DIP series is a very compact design having a low profile package and a high profile package. This series is compatible with all DIP relays.



### FEATURES


- · High resistance option available
- · Diode option available

## **CHARACTERISTICS**


- · Low profile package
- Standard pin configurations
- IC-pin compatible
- 4.25 kVDC breakdown voltage for pin out 13
- UL approval

## DIMENSIONS

#### All dimensions in mm [inches]



#### High profile package w/ magnetic shield



## **ORDER INFORMATION**

#### **Part Number Example**


DIP12 - 1A75 - 13L


12 is the nominal voltage
1A is the contact form
75 is the switch model
13 is the pin out
L is the option


Series	Nominal Voltage	Contact Switch Form Model		Pin Out	Option () Version with magn. Shield				
DIP	ХХ -	хх	ХХ -	хх	x				
		1A	72, 75	11, 13*					
0	05, 12, 15, 24	1B	72	19	L(M), D(Q),E(R), F(S)				
Options		2A	72	21					
	05, 12,15. 24	1C	90	51					
*Selects 4-25 (3.0 kVRMS) breakdown voltage contact to coil.									


## **PIN OUT**


# View from top of component 2.54mm [0.10"] pitch grid












w.m	T-TA	Ar.	$\sim \circ$	1919

DIP Series Molded DIP Reed Relays

## **OPTIONS**

() Versions with magnetic shield

View from top of component 2.54mm [0.10"] pitch grid



## **OPTIONS DEPENDENCE ON CASE SIZES**

Contact Form	Package	Pin Out	Options							
	Size		L	D	Е	F	м	Q	R	S
	Low Drofilo	11	х		х					
	Low Profile	13	х							
1 <b>A</b>	High Profile	11		x		x	х	х		х
		13		х			х	х		
1B	High Profile	19	х	х			х	х		
2A	High Profile	21	х	х	х	х	х	х	х	х
1C	Low Profile	51	х							
	High Profile	51		х	х	х	х	х	х	х

- L = No option
- D = With Diode between pin 2 and 6 (Pin 2 is positive)
- E = Internal shield on pin 9
- F = With Diode between pin 2 and 6 (Pin 2 is positive) and Internal shield on pin 9
- M = External magnetic shield
- Q = External magnetic shield and diode between pin 2 and 6 (Pin 2 is positive)
- R = External magnetic shield and internal shield on pin 9
- S = External magnetic shield and with diode between pin 2 and 6 (Pin 2 is positive) and internal shield on pin 9

## DIP Series Molded DIP Reed Relays

## **RELAY DATA**

All Data at 20° C	Switch Model $\rightarrow$ Contact Form $\rightarrow$		Switch 72 Form A / B			Switch 75 Form A			Switch 90 Form C		
Contact Ratings	Conditions		Тур.	Max.	Min.	Тур.	Max.	Min.	Тур.	Max.	Unit
Switching Power	Any DC combination of V & A not to exceed their individual max.'s			15			10			3	W
Switching Voltage	DC or peak AC			200			500			175	V
Switching Current	DC or peak AC			1.0			0.5			0.25	А
Carry Current	DC or peak AC			1.25			1.0			1.2	А
Static Contact Resistance	w/ 0.5 V & 10mA			150			200			150	mΩ
Dynamic Contact Resistance	Measured w/ 0.5 V & 50mA , 1.5 ms after closure			200			200			250	mΩ
Insulation Resistance across Contacts	100 volts applied	10 <sup>12</sup> 10 <sup>12</sup>			10 <sup>12</sup> 10 <sup>12</sup>			10 <sup>9</sup> 10 <sup>12</sup>			Ω
Breakdown Voltage across Contact	Across contacts Contact to coil	250 1500**			1500* 1500**			200 1500			VDC
Operation Time incl. Bounce	Measured w/ 100 % overdrive			0.5			0.5			0.7	ms
Release Time	Measured w/ no coil suppression			0.1			0.1			1.0	ms
Capacitance	at 10 kHz cross contact		0.2 2.0			0.4 2.0			1.0 3.0		pF
Life Expectancies											
Switching 5 V - 10 mA	DC only & <10 pF stray cap.		1000			500			100		10 <sup>6</sup> Cycles
For other load requirements plea	use see our life test section on P. 112.						,				
Environmental Data											
Shock Resistance	1/2 sinus wave duration 11 ms			50			50			30	g
Vibration Resistance	From 10 - 2000 Hz			20			20			10	g
Ambient Temperature	10°C/ minute max. allowable	-20		70	-20		70	-20		70	°C
Stock Temperature	10°C/ minute max. allowable	-35		95	-35		95	-35		95	°C
Soldering Temperature	5 sec.			260			260			260	°C

600 VDC with 5V coil, 1000 VDC with 12V coil.
 \*\* Selects Pin out 13 and 425 kVDC (3.0 kVRMS) breakdown voltage contact to coil.

DIP Series Molded DIP Reed Relays

Contact Form	Switch Model	Co Volt	oil age	Coil Resistance			Pull-in Voltage	Drop-out Volage	Nominal Coil Powe
All Data at 20 °C		VE	C		Ω		VDC	VDC	mW
		Nom.	Max.	. Min. Typ. Max.		Max.	Min.	Тур.	
		5	7.5	450 (180)	500 (200)	550 (220)	3.5	0.75	50
1A	72	12	16	900	1000	1100	8.4	1.8	145
	75	15	20	1800	2000	2200	10.5	2.2	115
		24	30	1800	2000	2200	16.8	3.6	290
	72	5	7.5	450	500	550	3.5	0.75	50
1B **		12	16	900	1000	1100	8.4	1.8	145
		15	20	1800	2000	2200	10.5	2.2	115
		24	30	1800	2000	2200	16.8	3.6	290
		5	7.5	180	200	220	3.5	0.75	125
2A	72	12	16	450	500	550	8.4	1.8	290
28	12	15	20	1800	2000	2200	10.5	2.2	115
		24	30	1800	2000	2200	16.8	3.6	290
		5	7.5	180	200	220	3.5	0.75	125
1C	90	12	16	450	500	550	8.4	1.8	290
10	50	15	20	1800	2000	2200	10.5	2.2	115
		24	30	1800	2000	2200	16.8	3.6	290

## **COIL DATA**

() For Switch 75.

\* The pull-in / drop-out voltage and coil resistance will change at rate of 0.4% per °C.

\*\* Re-closure of Form B may occur if the max. coil voltage is exceeded. Coil polarity on Form B must be observed. Pin 2 is positive.