Carbon Film Resistors

CFR Series

Normal & Miniature Style

FEATURES

Industry's Lowest Cost Delivery From Stock in Bulk, Taped and Strip Pack

Exceptional Long-Term Stability

Exceeds Carbon Comp MIL-R-11 Performance

Resistance Tolerance: $\pm 2\%, \pm 5\%$

Variety of Packaging–Bulk, Strip Pack, 26mm and 52mm Tape and Reel, Cut and Formed, or Radial Panasert/Avisert

DERATING CURVE

HOT-SPOT TEMPERATURE





FIG. I TEMPERATURE COEFFICIENT

STYLE	Max.Value of Temp. Coefficient ppm/°C					
	under 100K Ω	100K to I M Ω excl.	I M Ω and over			
CFR100, CFR200, CFR2WS	±350	+350 -500	+350 -1000			
CFR-12, CFR-25, CFR-50, CFR25S, CFR50S, CFR1WS	+350 -500	+350 -700	+350 -1000			

DIMENSIONS



STYLE		DIMENSIC	N			
Normal	Miniature	L	øD	н	ød	
CFR-12	CFR25S	3.3±0.4	1.8±0.3	28±2.0	0.5±0.05	
CFR-25	CFR50S	6.3±0.5	2.3±0.3	28±2.0	0.6±0.05	
CFR-50	CFRIWS	9.0±0.5	3.2±0.5	26±2.0	0.6±0.05	
CFR100	CFR2WS	11.5±1.0	4.5±0.5	35±2.0	0.8±0.05	
CFR200	_	15.5±1.0	5.0±0.5	32±2.0	0.8±0.05	

INTRODUCTION

Billions of products are already in use worldwide in all types of applications-from process control instrumentation to telephone receivers and FM radio to color television. The secret is in a proprietary production system and baking by a uniquely designed and automated production technique. Years of experience in making raw materials and production machinery prove the unique quality and high reliability of these products. The meet-or far exceed-such specifications as EIA RS196A. JIS-C-6402 and IEC-115. The resistors are coated with layers of tan color lacquer.

Unit : mm

Note :

(m)¹²

ELECTRICAL CHARACTERISTICS

STYLE	CFR-12	CFR25S	CFR-25	CFR50S	CFR-50	CFRIWS	CFR100	CFR2WS	CFR200
Power Rating at 70°C	1/6W	1/4W		1/2W		IW		2W	
Operating Temp. Range	-55°C to +1	155°C							
Maximum Working Voltage	150V	200∨	250V	300V	350V	400V	500V	500V	500V
Maximum Overload Voltage	300V	400V	500V	600V	700∨	800V	1000V	1000V	1000V
Dielectric Withstanding Voltage	300V	400V	500V	500V	500V	700∨	1000V	1000V	1000V
Value Range ±2%, ±5%	Ω~ 0MΩ								
Temperature Coefficient (by Type)	see FIG. I								

* Standard resistance is 1 $\Omega{\sim}10\text{M}\Omega$, below or over this resistance on request.

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	JIS-C-5202 5.5	2.5 Times RCWV for 5 Seconds	$\pm(0.75\%+0.05\Omega)$
Dielectric Withstanding Voltage	JIS-C-5202 5.7	in V-Block for 60 Seconds	by Type
Temperature Coefficient of Resistance	JIS-C-5202 5.2	-55°C to +155°C	by Type
Insulation Resistance	JIS-C-5202 5.6	in V-Block	>1000MΩ
Solderability	JIS-C-5202 6.5	235°C for 5±0.5 Seconds	95% Min. Coverage
Resistance to Solvent	JIS-C-5202 6.9	Trichroethane for 1 Min. with Ultrasonic	No Deterioration of Coatings and Markings
Terminal Strength	Direct Load for 10 Sec. i	≥2.5kg (24.5N)	
Pulse Overload	JIS-C-5202 5.8	\pm (1%+0.05 Ω)	
Load Life in Humidity	JIS-C-5202 7.9	40±2°C, 90~95% RH at RCWV for 1000 Hrs. (1.5 Hrs. on , 0.5 Hrs. off)	±(3%+0.05Ω)
Load Life	JIS-C-5202 7.10	70°C at RCWV for 1000 Hrs. (1.5 Hrs. on , 0.5 Hrs. off)	$\pm(3\%+0.05\Omega)$
Temperature Cycling	JIS-C-5202 7.4	-65°C→Room Temp.→ I 50°C→Room Temp. for 5 Cycles	$\pm(1\%+0.05\Omega)$
Resistance to Soldering Heat	JIS-C-5202 6.4	350°C±10°C for 3±0.5 Seconds	$\pm(1\%+0.05\Omega)$

* Rated Continuous Working Voltage (RCW V)= $\sqrt{Power Rating \times Resistance Value}$