


ULTRA-SMALL PACKAGE SLIM POLARIZED RELAY

5.70-0.3 10 60-0 3 9.00-0.3 10.60-0.3



mm inch

FEATURES • Compact slim body saves space Thanks to the small surface area of 5.7 $mm \times 10.6 mm$.224 inch \times .417 inch and low height of 9.0 mm .354 inch, the packaging density can be increased to

allow for much smaller designs. • Outstanding surge resistance. Surge withstand between open contacts: 1,500 V 10×160 µs (FCC part 68) Surge withstand between contacts and coil: 2,500 V 2×10 µs (Telcordia)

 The use of twin crossbar contacts ensures high contact reliability. AgPd contact is used because of its good sulfide resistance. Adopting low-gas molding material. Coil assembly molding technology which avoids generating volatile gas from coil.

Increased packaging density

(AGN

GN RELAYS

Due to highly efficient magnetic circuit design, leakage flux is reduced and changes in electrical characteristics from components being mounted closetogether are minimized. This all means a packaging density higher than ever before.

- Nominal operating power: 140 mW
- Outstanding vibration and shock resistance.

Functional shock resistance: 750 m/s² {75G} Destructive shock resistance: 1,000 m/s² {100G} Functional vibration resistance: 10 to 55 Hz (at double amplitude of 3.3 mm .130 inch) Destructive vibration resistance: 10 to 55 Hz (at double amplitude of 5 mm .197 inch)

SPECIFICATIONS

Contact

Arrangemen	t	2 Form C			
	t resistance, r drop 6 V DC 1	100 mΩ			
Contact mat	erial	Stationary: AgPd+Au clad Movable: AgPd			
	Nominal swit (resistive loa	tching capacity	1 A 30 V DC 0.3 A 125 V AC		
Rating	Max. switchi (resistive loa		30 W, 37.5 V A		
	Max. switchi	ng voltage	110 V DC, 125 V AC		
	Max. switchi	ng current	1 A		
	Min. switchir	ng capacity *1	10 µA 10 mV DC		
Nominal	Single side s	stable	140mW (1.5 to 12 V DC) 230mW (24 V DC)		
operating power	1 coil latchin	g	100mW (1.5 to 12 V DC) 120mW (24 V DC)		
	Mechanical	(at 180 cpm)	5 × 10 ⁷		
Expected life (min. operations)	Electrical	1 A 30 V DC resistive	10 ⁵		
	(at 20 cpm)	0.3 A 125 V AC resistive	10 ⁵		

Remarks:

- *2 Detection current: 10mA
- *3 Nominal voltage applied to the coil, excluding contact bounce time.
- *4 By resistive method, nominal voltage applied to the coil; contact carrying current: 1 A
- *5 Half-wave pulse of sine wave: 6 ms; detection time: 10 $\mu s.$ *6 Half-wave pulse of sine wave: 6 ms.
- *7 Detection time: 10µs.

*8 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT (see catalog).

Characteristics

Characteris	STICS			
Initial insulat	ion resista	Min. 1,000MΩ (at 500V DC)		
Initial	Between	open contacts	750 Vrms for 1min.	
breakdown	Between	contact sets	1,000 Vrms for 1min.	
voltage*2	Between	contacts and coil	1,500 Vrms for 1min.	
Initial surge	Between (10×160	open contacts us)	1,500 V (FCC Part 68)	
voltage	Between (2×10 μs)	contacts and coil	2,500 V (Telcordia)	
Operate time	e [Set time]	Max. 4 ms (Approx. 2 ms) [Max. 4 ms (Approx. 2 ms)]		
Release time [Reset time]	· ·	Max. 4 ms (Approx. 1 ms) [Max. 4 ms (Approx. 2 ms)]		
Temperature	rise*4 (at 2	Max. 50°C		
Shock resist	2000	Functional*5	Min. 750 m/s²{75G]	
SHOCK TESISI	ance	Destructive*6	Min. 1,000 m/s²{100G]	
Vibratian rad	iatanaa	Functional*7	10 to 55 Hz at double amplitude of 3.3 mm	
Vibration resistance		Destructive	10 to 55 Hz at double amplitude of 5 mm	
Conditions for operation, transport		Ambient temperature *2	−40°C to 85°C −40°F to 185°F	
(Not freezing condensing	and storage ^{*8} (Not freezing and condensing at low temperature)		5 to 85% R.H.	
Unit weight			Approx. 1 g .035 oz	

Notes:

- — 1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load

*2 The upper limit for the ambient temperature is the maximum temperature that can satisfy the coil temperature rise. Under the packing condition, allowable temperature range is from -40 to +70°C -40° to +158°F

Specifications will vary with foreign standards certification ratings. Measurement at same location as "Initial breakdown voltage" section.

GN (AGN)

TYPICAL APPLICATIONS

- Communications (XDSL, Transmission)
- Measurement
- Security

- Home appliances, and audio/visual equipment
- Automotive equipment
- Medical equipment

ORDERING INFORMATION

Ex. AGN 2 0 0 A 1 H Z									
Contact arrangement	Operating function	Type of operation	Terminal shape Coil voltage (DC)		Packing style				
2: 2 Form C	0: Single side stable 1: 1 coil latching	0: Standard type (B.B.M.)	Nil: Standard PC board terminal A: Surface-mount terminal A type S: Surface-mount terminal S type		Nil: Tube packing Z: Tape and reel packing (picked from 5/6/7/8 pin side)				

Note: Tape and reel packing symbol "-Z" is not marked on the relay. "X" type tape and reel packing (picked from 1/2/3/4-pin side) is also available. Suffix "X" instead of "Z".

TYPES AND COIL DATA (at 20°C 68°F)

(1) Standard PC board terminal

	Part No.		Pick-up	Drop-out	Nominal		Nominal	Max. allowable	
Operating Function	Standard PC board terminal	Coil Rating, V DC	voltage, V DC (max.) (initial)	voltage, V DC (min.) (initial)	operating current, mA (±10%)	Coil resistance, Ω (±10%)	operating power, mW	voltage, V DC	
	AGN2001H	1.5	1.13	0.15	93.8	16	140	2.25	
	AGN20003	3	2.25	0.3	46.7	64.2	140	4.5	
	AGN2004H	4.5	3.38	0.45	31	145	140	6.75	
Single side stable	AGN20006	6	4.5	0.6	23.3	257	140	9	
Stable	AGN20009	9	6.75	0.9	15.5	579	140	13.5	
	AGN20012	12	9	1.2	11.7	1,028	140	18	
	AGN20024	24	18	2.4	9.6	2,504	230	28.8	
	Part No.		Set voltage,	Reset voltage,	Nominal		Nominal operating power, mW	Max. allowable voltage, V DC	
Operating Function	Standard PC board terminal	Coil Rating, V DC	V DC (max.) (initial)	V DC (max.) (initial)	operating current, mA (±10%)	Coil resistance, Ω (±10%)			
	AGN2101H	1.5	1.13	1.13	66.7	22.5	100	2.25	
	AGN21003	3	2.25	2.25	33.3	90	100	4.5	
1 coil latching	AGN2104H	4.5	3.38	3.38	22.2	202.5	100	6.75	
	AGN21006	6	4.5	4.5	16.7	360	100	9	
	AGN21009	9	6.75	6.75	11.1	810	100	13.5	
	AGN21012	12	9	9	8.3	1,440	100	18	
						1		1	

1) Standard packing: Tube: 50 pcs.; Case: 1,000 pcs.

2) Specified value of pick-up, drop-out, set and reset voltage is with the condition of square wave coil pulse.

(2) Surface-mount terminal

Operating Function	Part No.		0 11 0 11	Pick-up	Drop-out	Nominal	Coil	Nominal	Max.
	Tube packing	Tape and reel packing	Coil Rating, V DC	voltage, V DC (max.) (initial)	voltage, V DC (min.) (initial)	operating current, mA (±10%)	resistance, Ω (±10%)	operating power, mW	allowable voltage, V DC
Single side stable	AGN200O1H	AGN200O1HZ	1.5	1.13	0.15	93.8	16	140	2.25
	AGN200003	AGN200003Z	3	2.25	0.3	46.7	64.2	140	4.5
	AGN200O4H	AGN200O4HZ	4.5	3.38	0.45	31	145	140	6.75
	AGN200006	AGN200006Z	6	4.5	0.6	23.3	257	140	9
	AGN200009	AGN200009Z	9	6.75	0.9	15.5	579	140	13.5
	AGN200012	AGN200012Z	12	9	1.2	11.7	1,028	140	18
	AGN200024	AGN200024Z	24	18	2.4	9.6	2,504	230	28.8

O: For each surface-mounted terminal variation, input the following letter.

A type: <u>A</u>, S type: <u>S</u>

Tape and reel: 500 pcs.; Case: 1,000 pcs.

2) Specified value of pick-up, drop-out, set and reset voltage is with the condition of square wave coil pulse.

¹⁾ Standard packing: Tube: 50 pcs.; Case: 1,000 pcs.

GN (AGN)

mm inch

Operating Function	Part No.			Set voltage,	Reset	Nominal	Coil	Nominal	Max.
	Tube packing	Tape and reel packing	Coil Rating, V DC	V DC (max.) (initial)	voltage, V DC (max.) (initial)	operating current, mA (±10%)	resistance, Ω (±10%)	operating power, mW	allowable voltage, V DC
1 coil latching	AGN210O1H	AGN210O1HZ	1.5	1.13	1.13	66.7	22.5	100	2.25
	AGN210O03	AGN210O03Z	3	2.25	2.25	33.3	90	100	4.5
	AGN210O4H	AGN210O4HZ	4.5	3.38	3.38	22.2	202.5	100	6.75
	AGN210O06	AGN210O06Z	6	4.5	4.5	16.7	360	100	9
	AGN210O09	AGN210O09Z	9	6.75	6.75	11.1	810	100	13.5
	AGN210O12	AGN210O12Z	12	9	9	8.3	1,440	100	18
	AGN210O24	AGN210O24Z	24	18	18	5.0	4,800	120	36

O: For each surface-mounted terminal variation, input the following letter.

A type: <u>A</u>, S type: <u>S</u>


1) Standard packing: Tube: 50 pcs.: Case 1,000 pcs.

Tape and reel: 500 pcs.; Case: 1,000 pcs.

2) Specified value of pick-up, drop-out, set and reset voltage is with the condition of square wave coil pulse.


DIMENSIONS







2. Surface-mount terminal











Single side stable
(Deenergized condition)1 coil latching
(Reset condition) $-\frac{8}{n}$ 76 $\frac{1}{n}$ 00 $\frac{1}{n}$ 00 $\frac{1}{n}$ 00 $\frac{1}{n}$ 00 $\frac{1}{n}$ 00 $\frac{1}{n}$ 00 $\frac{1}{n}$ 0 $\frac{1}{n}$ 0

Schematic (Top view)











Tolerance: ±0.1 ±.004




REFERENCE DATA





2. Life curve



3.20-0.15


126

GN (AGN)

NOTES


1. Packing style

1) The relay is packed in a tube with the relay orientation mark on the left side, as shown in the figure below.




2) Tape and reel packing(A type)(1)-1 Tape dimensions


mm inch



(S type) (1)-2 Tape dimensions




(2) Dimensions of plastic peel



2. Automatic insertion

To maintain the internal function of the relay, the chucking pressure should not exceed the values below. Chucking pressure in the direction A: 4.9 N {500gf} or less Chucking pressure in the direction B: 9.8 N {1 kgf} or less Chucking pressure in the direction C: 9.8 N {1 kgf} or less



Please chuck the *means* portion. Avoid chucking the center of the relay. In addition, excessive chucking pressure to the pinpoint of the relay should be avoided.

For Cautions for Use, see Relay Technical Information (see catalog).