# Proximity Sensors Capacitive Thermoplastic Polyester Housing Type EC, M 30, AC







- Featuring TRIPLESHIELD™ Sensor Protection
- Adjustable sensing distance 2-16 mm or 4-25 mm
- Rated operational voltage: 20-250 VAC
- Output: SCR
- Make and break switching function
- LED indication

Connection type

- High noise immunity
- · Flush and non-flush types
- Plug and Cable versions available
- DC versions in the same housing

### **Product Description**

Capacitive proximity switches with either sensing distance 16 mm flush mounted or 25 mm sensing distance non-flush mounted. 2-wire AC output with a switch for choosing NO and NC

switching. Grey M 30 polyester housing with 2 m PVC cable or plug. Ideal for use in level and plastic machinery applications. Both types are available in metal housings.

# Type: Capacitive proximity switch Housing diameter (mm) Rated operating dist. (mm) Output type Housing material Housing type

# **Type Selection**

Housing diameter	Rated operating dist. (S <sub>n</sub> ) 1)	Mounting	Ordering no. SCR, cable Make & break switching	Ordering no. SCR, plug Make & break switching		
M30	16 mm	Flush (built-in)	EC 3016 TBAPL	EC 3016 TBAPL-6		
M30	25 mm	Non-flush	EC 3025 TBAPL	EC 3025 TBAPL-6		

<sup>1)</sup> Object: Grounded steel plate


## **Specifications**


Rated operating dist. $(S_n)$ 3016:	2 to 16 mm			
3025:	factory set at 16 mm 4 to 25 mm factory set at 25 mm			
Sensitivity	Adj. multiturn pot.meter			
Effective operating dist. (S <sub>r</sub> )	$0.9 \times S_n \le S_r \le 1.1 \times S$			
Usable operating dist. (S <sub>u</sub> )	$0.8 \times S_r \le S_n > 1.2 \times S_r$			
Repeat accuracy (R)	≤ 5%			
Hysteresis (H)	4 to 20% of sensing distance			
Rated operational volt. (U <sub>B</sub> )	20 to 250 VAC (ripple included)			
Ripple	≤ 10%			
Rated operational current (I <sub>e</sub> )				
Continuous	≤ 500 mA			
Short-time	< 2.5 A (max. 20 ms)			
Min. load current	≤ 10 mA			
OFF-state current (I <sub>r</sub> )	< 2.5 mA (@ 240 VAC) 1.7 mA (@ 120 VAC)			
Voltage drop (U <sub>d</sub> )	$\leq$ 10 VAC (at loads $\geq$ 20 mA)			
Protection	Transients			

Frequency of operating cycles (f) Indication for output ON Environment Degree of protection  Temperature Operating temperature	10 Hz LED, yellow IP 67 (Nema 1, 3, 4, 6, 13)			
Indication for output ON Environment Degree of protection Temperature	LED, yellow			
Environment Degree of protection Temperature				
Degree of protection  Temperature	IP 67 (Nema 1, 3, 4, 6, 13)			
Temperature	IP 67 (Nema 1, 3, 4, 6, 13)			
•				
Operating temperature				
	-25° to +80°C (-13° to +176°F)			
Storage temperature	-40° to +85°C (-40° to +185°F)			
Housing material				
Body	Grey, thermoplastic polyester			
Cable end	Polyester			
Nuts	Black reinforced nylon			
Connection				
Cable	Grey, 2 m, 2 x 0.5 mm <sup>2</sup>			
	Oil proof, PVC			
Plug (-6)	M12 x 1 double keyed			
Cable for plug (-6)	CON6A-series			
Weight (incl. nuts)	<b>3016:</b> 140 g			
	<b>3025:</b> 150 g			
Approvals	UL, CSA			
CE-marking	Yes			



#### **Dimensions**





Туре	A	B Ø mm	l	D mm	ı	
EC 3016TBAPL(-6) EC 3025TBAPL(-6)						


## **Adjustment Guide**

The environments in which capacitive sensors are installed can often be unstable regarding temperature, humidity, object distance and industrial (noise) interference. Because of this, Carlo Gavazzi offers as standard features in all *TRIP-LESHIELD*<sup>TM</sup> capacitive sensors a user-friendly sensitivity adjustment instead of having a fixed sensing range, extended sensing range to accom-

modate mechanically demanding areas, temperature stability to ensure minimum need for adjusting sensitivity if temperature varies and high immunity to electromagnetic interference (EMI).

#### Note:

Sensors are factory set (default) to maximum rated sensing range.



#### **Installation Hints**

Capacitive sensors have the unique ability to detect almost all materials, either in liquid or solid form. Capacitive sensors can detect metallic as well as non-metallic objects, however, their traditional use is for non-metallic materials such as:

 Plastic Industry
 Resins, regrinds or moulded products.

#### Chemical Industry

Cleansers, fertilisers, liquid soaps, corrosives and petrochemicals.

#### Wood Industry

Saw dust, paper products, door and window frames.

#### Ceramic & Glass Industry


Raw material, clay or finished products, bottles.

#### Packaging Industry

Package inspection for level or contents, dry goods, fruits and vegetables, dairy products.

Materials are detected due to their dielectric constant. The bigger the size of an object, the higher the density of material, the better or easier it is to detect the object. Nominal sensing distance for a capacitive sensor is referenced to a grounded metal plate (ST37). For additional information regarding dielectric ratings of materials please refer to Technical Information.

## **Wiring Diagram**



## **Delivery Contents**

- Capacitive switch: EC 30.. TBAPL(-6)
- Screw driver
- 2 nuts
- Packaging: Cardboard box
- Installation & Adjustment Guide (MAN CAP ENG/GER)

## **Accessories**

• Plugs CONH6A.. serie.

For further information please refer to "Accessories.