

Item No.: 1754481

Type: MSTB 2,5/ 4-ST

PCB connector, Screw connection with tension sleeve



The figure shows a 10-position version of the product

1 Main features



- | | | | |
|---------------------------|--------------------------------------|------------------------|---------------------|
| • No. of pos. | 4 | • Nominal current | 12 A |
| • Conductor cross section | 2.5 mm ² | • Nominal voltage | 320 V |
| • Color | green (6021) | • Connection direction | 0 ° |
| • Pitch | 5 mm | • Type of packaging | packed in cardboard |
| • Connection method | Screw connection with tension sleeve | | |

2 Your advantages

- ✓ Well-known connection principle allows worldwide use
- ✓ Low temperature rise, thanks to maximum contact force
- ✓ Allows connection of two conductors




Make sure you always use the latest documentation.
It can be downloaded at: phoenixcontact.net/product/1754481

3 Table of contents

1	Main features.....	1
2	Your advantages	1
3	Table of contents	2
4	3D model in PDF can be activated (Acrobat Reader only).....	3
5	General Technical Data	4
6	Mounting.....	5
7	Conductor connection	6
8	Material properties.....	7
9	Dimensions.....	8
10	Series drawing.....	9
11	Product drawing	10
12	Product notes	11
13	Packaging information	11
14	Application.....	11
15	General tests	12
16	Mechanical tests.....	12
17	Insertion and withdrawal forces	14
18	Electrical tests	15
19	Air and creepage distances	16
20	Current carrying capacity/derating curves	17
21	Environmental and durability tests	22
22	Type approval and special tests	23
23	Classification for connectors.....	23
24	Approvals / Certificates.....	24
25	Commercial Data.....	25
26	corresponding headers.....	25
27	Accessories.....	25
28	Combination tests.....	26

4 3D model in PDF can be activated (Acrobat Reader only)



1754481 MSTB 2,5/ 4-ST**5 General Technical Data****5.1 item properties**

Item no.	1754481
Type	MSTB 2,5/ 4-ST
Product line	COMBICON Connectors M
Connector system	CLASSIC COMBICON
Product type	PCB connector
Type of contact	Female connector
Range of articles	MSTB 2,5/..-ST
Pitch	5 mm
Number of positions	4
Number of rows	1
Number of connections	4
Number of potentials	4
Connection method	Screw connection with tension sleeve
Screw thread	M3
Drive form screw head	Slotted (L)
Connection direction of the conductor to plug-in direction	0 °
Type	Standard

1754481 MSTB 2,5/ 4-ST

6 Mounting

6.1 Flange mounting

Type of locking	without
Mounting flange	without

1754481 MSTB 2,5/ 4-ST**7 Conductor connection****7.1 Connection capacity**

Nominal cross section	2.5 mm ²
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 2.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve	0.25 mm ² ... 2.5 mm ²
2 conductors with same cross section, solid	0.2 mm ² ... 1 mm ²
2 conductors with same cross section, stranded	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, stranded, with ferrule without plastic sleeve	0.25 mm ² ... 1 mm ²
2 conductors with the same cross section flexible with TWIN ferrule and plastic sleeve	0.5 mm ² ... 1.5 mm ²
Cylindrical gauge a x b / diameter	2.8 mm x 2.0 mm / 2.4 mm
Stripping length	7 mm
Tightening torque	0.5 Nm ... 0.6 Nm

7.2 Connection capacity AWG

Conductor cross section AWG	24 ... 12
-----------------------------	-----------

1754481 MSTB 2,5/ 4-ST**8 Material properties****8.1 Material of metal parts**

Note	WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Terminal point surface	Tin (5 - 7 µm Sn)
Surface contact area	Tin (5 - 7 µm Sn)
Surface characteristics	hot-dip tin-plated

8.2 Material of plastic parts


	Housing
Color	green (6021)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

1754481 MSTB 2,5/ 4-ST**9 Dimensions****9.1 Dimensions for the product**

Length		18.2 mm
Width		20 mm
Installed height		15 mm
Total height		15 mm

1754481 MSTB 2,5/ 4-ST

10 Series drawing



DIN A3	document-No. / Ri 00655999 / 02	date 25.11.2015	scale 1:5:1
TECDOC	document-type TECDOC 2D-PRODUCTFAMILY	description MSTB 2,5/..-ST-5,00	
page 1	of 1	6	

1754481 MSTB 2,5/ 4-ST

11 Product drawing

1	2	3	4	5	6																		
<p> <small> Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Verbreitung, auch auszugsweise, ist ohne schriftliche Genehmigung der Phoenix Contact AG. Die Phoenix Contact AG übernimmt keine Haftung für die Richtigkeit der Angaben. Alle Rechte vorbehalten. </small> </p> <p> <small> In case of patent, utility model or design patent registrations, in case of patent, utility model or design patents inherent in the design, communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved </small> </p> <p> <small> Transfer or duplication of this document as well as the utilisation or distribution of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved </small> </p>																							
<table border="1"> <tr> <td> </td> <td> document-No. / R / Ri 01083836 / 700 </td> <td> date 22.09.2017 </td> <td> scale 1:1 </td> <td colspan="2"> Simplified representation - Reduced drawing - Free choice of views - Linear dimensions (mm) - EN ISO 291, 2950 </td> </tr> <tr> <td colspan="3"> document-type TECDOC 2D_Productdrawing </td> <td colspan="3"> description MSTB 2,5/ 4-ST </td> </tr> <tr> <td colspan="6"> page 1 of 1 </td> </tr> </table>							document-No. / R / Ri 01083836 / 700	date 22.09.2017	scale 1:1	Simplified representation - Reduced drawing - Free choice of views - Linear dimensions (mm) - EN ISO 291, 2950		document-type TECDOC 2D_Productdrawing			description MSTB 2,5/ 4-ST			page 1 of 1					
	document-No. / R / Ri 01083836 / 700	date 22.09.2017	scale 1:1	Simplified representation - Reduced drawing - Free choice of views - Linear dimensions (mm) - EN ISO 291, 2950																			
document-type TECDOC 2D_Productdrawing			description MSTB 2,5/ 4-ST																				
page 1 of 1																							

1754481 MSTB 2,5/ 4-ST**12 Product notes****12.1 General information**

Notes on operation

In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load.

13 Packaging information

Type of packaging

packed in cardboard

Pieces per package

100

14 Application**14.1 Temperature limit values**

Ambient temperature (storage/transport)

-40 °C ... 70 °C

Relative humidity (storage/transport)

30 % ... 70 %

Ambient temperature (assembly)

-5 °C ... 100 °C

Ambient temperature (operation)

-40 °C ... 100 °C (dependent on the derating curve)

1754481 MSTB 2,5/ 4-ST**15 General tests****15.1 Specification**

Specification	IEC 61984
Specification	IEC 60999-1
Brief description	Printed-circuit board connector

16 Mechanical tests**16.1 Check for damage to conductor or loosening**

Result	Test passed
Specification	IEC 60999-1:1999-11

16.2 Pull-out test

Specification	IEC 60999-1:1999-11
Result	Test passed
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / solid / > 10 N
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / flexible / > 10 N
Conductor cross section/conductor type/tractive force actual value	2.5 mm ² / solid / > 50 N
Conductor cross section/conductor type/tractive force actual value	2.5 mm ² / flexible / > 50 N

16.3 Torque test

Specification	IEC 60999-1:1999-11
Result	Test passed

16.4 Visual examination

Specification	IEC 61984:2008-10
Visual examination	Test passed
Specification	IEC 60512-1-1:2002-02

16.5 Dimensional test

Dimensional test	Test passed
Specification	IEC 60512-1-2:2002-02

16.6 Resistance of marking

Resistance of marking	Test passed
Specification	IEC 60068-2-70:1995-12

16.7 Polarization and coding

1754481 MSTB 2,5/ 4-ST



Polarization when inserted
Requirement >20 N

Test passed

Specification

IEC 60512-13-5:2006-02

1754481 MSTB 2,5/ 4-ST**17 Insertion and withdrawal forces**

Insertion and withdrawal force	
Specification	Test passed
No. of cycles	25
Insertion strength per pos. approx.	8 N
Withdraw strength per pos. approx.	6 N

1754481 MSTB 2,5/ 4-ST**18 Electrical tests**

Rated current / conductor cross section	12 A / 2.5 mm ²
Rated insulation voltage (III/2)	320 V
Rated surge voltage (III/2)	4 kV
Contact resistance	1.4 mΩ
Degree of pollution	2

1754481 MSTB 2,5/ 4-ST**19 Air and creepage distances**


Component	PCB connector		
Specification	IEC 60664-1:2007-04		
Mains type	unearthed mains		
Insulating material group	I		
Comparative tracking index (IEC 60112:2003-01)	CTI 600		
Rated insulation voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Degree of pollution	3	2	2
Overvoltage category	III	III	II
Minimum clearance case A (inhomogeneous field)	3 mm	3 mm	3 mm
Minimum value of the creepage path requirement in acc. with table	3.2 mm	3 mm	3.2 mm

1754481 MSTB 2,5/ 4-ST


20 Current carrying capacity/derating curves

Specification	IEC 61984:2008-10
Note	Representation based on IEC 60512-5-2:2002-02
Note	For number of positions, see diagram
Reduction factor	0.8
Conductor cross section	2.5 mm ²


Type: MSTB 2,5/...-ST with MSTBA 2,5/...-G



Type: MSTB 2,5/...-ST with MSTBVA 2,5/...-G




Type: MSTB 2,5/...-ST with MDSTB 2,5/...-G




1754481 MSTB 2,5/ 4-ST


Type: MSTB 2,5/...-ST with MDSTBV 2,5/...-G




Type: MSTB 2,5/...-ST with MDSTBW 2,5/...-G



Type: MSTB 2,5/...-ST with MSTBW 2,5/...-G




Type: MSTB 2,5/...-ST with CCA 2,5/...-G P20 THR




1754481 MSTB 2,5/ 4-ST


Type: MSTB 2,5/...-ST with CCVA 2,5/...-G P20 THR



Type: MSTB 2,5/...-ST with SMSTBA 2,5/...-G




Type: MSTB 2,5/...-ST with MSTBO 2,5/...-G1L




1754481 MSTB 2,5/ 4-ST


Type: MSTB 2,5/...-ST with MSTBO 2,5/...-G1R



Type: MSTB 2,5/...-ST with FKIC 2,5/...-ST




Type: MSTB 2,5/...-ST with MSTBV 2,5/...-G




1754481 MSTB 2,5/ 4-ST


Type: MSTB 2,5/...-ST with MSTBHK 2,5/...-G



Type: MSTB 2,5/...-ST with MSTB 2,5/...-G



Type: MSTB 2,5/...-ST with MDSTB 2,5/...-G1



1754481 MSTB 2,5/ 4-ST**21 Environmental and durability tests****21.1 Vibration test**

Specification	IEC 60068-2-6:2007-12
Result	Test passed
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Acceleration	5g (60.1 - 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis
Note	The connected conductor loops were guided to the test sample at a distance of approx. 10 cm.

21.2 Insulation resistance






Specification	IEC 60512-3-1:2002-02
Result	Test passed
Insulation resistance, neighboring positions	> 5 MΩ

1754481 MSTB 2,5/ 4-ST**22 Type approval and special tests****23 Classification for connectors**

Specification	IEC 61984:2008-10
Main features	Connectors without switching capacity (COC)
Construction form	Fixed connectors
Strain relief elements	without strain relief
Connection method	Can be reconnected
Protection against electric shock	Not encapsulated - touch-proof when inserted
Protective conductor	without PE
Locking	no
Connection method	Screw terminal points

1754481 MSTB 2,5/ 4-ST

24 Approvals / Certificates

CSA 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
Usegroup B				
	300 V	15 A	28 - 12	-
Usegroup D				
	300 V	10 A	28 - 12	-
IECEE CB Scheme 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
	250 V	12 A	-	0.2 - 2.5
EAC 				
cULus Recognized 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
Usegroup B				
	300 V	15 A	30 - 12	-
Usegroup D				
	300 V	10 A	30 - 12	-
VDE Zeichengenehmigung 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
	250 V	12 A	-	0.2 - 2.5

1754481 MSTB 2,5/ 4-ST**25 Commercial Data**

Item no.	1754481
Type	MSTB 2,5/ 4-ST
Pieces per package	100
Net weight	6.79 g
GTIN	4017918028657
	Information that applies locally, see link on page 1

26 corresponding headers





Item no.	Type
1736098	MSTBW 2,5/ 4-G
1736690	MDSTB 2,5/ 4-G1
2697194	MSTBO 2,5/ 4-G1L THRR44 BK

27 Accessories

Description	Item No.	Type
Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip	1205053	SZS 0,6X3,5
	0804183	SK 5/3,8:FORTL.ZAHLEN
	1803882	KGK-MSTB 2,5/ 4
Coding profile, is inserted into the slot on the plug or inverted header, red insulating material	1734634	CP-MSTB
Insertion bridge for connectors with 5.0 mm or 5.08 mm pitch	1733169	EBP 2- 5


1754481 MSTB 2,5/ 4-ST

28 Combination tests





MSTB 2,5/..-ST	MSTBA 2,5/..-G	MSTBVA 2,5/..-G	MDSTB 2,5/..-G	MDSTBV 2,5/..-G
IEC 61984	IEC 61984	IEC 61984	IEC 61984	IEC 61984
Mechanical tests (A)				
Insertion/withdrawal force per position	approx. 8 N / 6 N	approx. 8 N / 6 N	approx. 8 N / 6 N	approx. 8 N / 6 N
Polarization when inserted Requirement >20 N	Test passed	Test passed	Test passed	Test passed
Contact holder in insert Requirements >20 N	Test passed	Test passed	Test passed	Test passed
Durability tests (B)				
Contact resistance R ₁ 1st level	1.4 mΩ	2.5 mΩ	1.4 mΩ	2.5 mΩ
Contact resistance R ₁ 2nd level			1.8 mΩ	1.5 mΩ
Insertion/withdrawal cycles	25	25	25	25
Contact resistance R ₂	1.5 mΩ	2.5 mΩ	1.5 mΩ	2.6 mΩ
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Insulation resistance Requirements > 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ
Thermal tests (C)				
Tested number of positions	24	24	12	12
Tested conductor cross section	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²
Test current	12 A	12 A	10 A	10 A
Upper limiting temperature Requirements < 100°C	Test passed	Test passed	Test passed	Test passed
Climatic tests (D)				
Test sequence 1: low temperature storage	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h
Test sequence 2: heat storage	100 °C/168 h	100 °C/168 h	100 °C/168 h	100 °C/168 h
Test sequence 3: noxious gas storage (ISO 6988)	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Environmental and endurance tests (E)				
Specification	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10
Degree of protection	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger

1754481 MSTB 2,5/ 4-ST




MSTB 2,5/..-ST	MDSTBW 2,5/..-G	MSTBW 2,5/..-G	CCA 2,5/..-G	CCVA 2,5/..-G
IEC 61984	IEC 61984	IEC 61984	IEC 61984	IEC 61984
Mechanical tests (A)				
Insertion/withdrawal force per position	approx. 8 N / 6 N	approx. 8 N / 7 N	approx. 8 N / 6 N	approx. 8 N / 6 N
Polarization when inserted Requirement >20 N	Test passed	Test passed	Test passed	Test passed
Contact holder in insert Requirements >20 N	Test passed	Test passed	Test passed	Test passed
Durability tests (B)				
Contact resistance R ₁ 1st level	1.4 mΩ	1.4 mΩ	1.1 mΩ	1.2 mΩ
Contact resistance R ₁ 2nd level	1.7 mΩ			
Insertion/withdrawal cycles	25	25	25	25
Contact resistance R ₂	1.5 mΩ	1.5 mΩ	1.2 mΩ	1.2 mΩ
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Insulation resistance Requirements > 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ
Thermal tests (C)				
Tested number of positions	12	20	24	24
Tested conductor cross section	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²
Test current	10 A	12 A DC	12 A	12 A
Upper limiting temperature Requirements < 100°C	Test passed	Test passed	Test passed	Test passed
Climatic tests (D)				
Test sequence 1: low temperature storage	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h
Test sequence 2: heat storage	100 °C/168 h	100 °C/168 h	100 °C/168 h	100 °C/168 h
Test sequence 3: noxious gas storage (ISO 6988)	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Environmental and endurance tests (E)				
Specification	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10
Degree of protection	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger

1754481 MSTB 2,5/ 4-ST



MSTB 2,5/..-ST	SMSTBA 2,5/..-G	MSTBO 2,5/..-G1L	MSTBO 2,5/..-G1R	FKIC 2,5/..-ST
IEC 61984	IEC 61984	IEC 61984	IEC 61984	IEC 61984
Mechanical tests (A)				
Insertion/withdrawal force per position	approx. 8 N / 6 N	approx. 8 N / 6 N	approx. 8 N / 6 N	approx. 8 N / 6 N
Polarization when inserted Requirement >20 N	Test passed	Test passed	Test passed	Test passed
Contact holder in insert Requirements >20 N	Test passed	Test passed	Test passed	Test passed
Durability tests (B)				
Contact resistance R ₁ 1st level	1.3 mΩ	1.5 mΩ	1.6 mΩ	1.6 mΩ
Contact resistance R ₁ 2nd level				
Insertion/withdrawal cycles	25	25	25	25
Contact resistance R ₂	1.4 mΩ	1.5 mΩ	1.6 mΩ	1.6 mΩ
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Insulation resistance Requirements > 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ
Thermal tests (C)				
Tested number of positions	24	4	4	18
Tested conductor cross section	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²
Test current	12 A	12 A	12 A	12 A
Upper limiting temperature Requirements < 100°C	Test passed	Test passed	Test passed	Test passed
Climatic tests (D)				
Test sequence 1: low temperature storage	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h
Test sequence 2: heat storage	100 °C/168 h	100 °C/168 h	100 °C/168 h	100 °C/168 h
Test sequence 3: noxious gas storage (ISO 6988)	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Environmental and endurance tests (E)				
Specification	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10
Degree of protection	Finger safety with IP20 test finger	No contact safety (IP00) in acc. with IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08	No contact safety (IP00) in acc. with IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08	Finger safety with IP20 test finger

1754481 MSTB 2,5/ 4-ST



MSTB 2,5/..-ST	MSTBV 2,5/..-G	MSTBHK 2,5/..-G	MSTB 2,5/..-G	MDSTB 2,5/..-G1
IEC 61984	IEC 61984	IEC 61984	IEC 61984	IEC 61984
Mechanical tests (A)				
Insertion/withdrawal force per position	approx. 8 N / 6 N	approx. 7 N / 5 N	approx. 8 N / 6 N	approx. 8 N / 6 N
Polarization when inserted Requirement >20 N	Test passed	Test passed	Test passed	Test passed
Contact holder in insert Requirements >20 N	Test passed	Test passed	Test passed	Test passed
Durability tests (B)				
Contact resistance R ₁ 1st level	2.5 mΩ	1.7 mΩ	1.4 mΩ	1.3 mΩ
Contact resistance R ₁ 2nd level				2.2 mΩ
Insertion/withdrawal cycles	25	25	25	25
Contact resistance R ₂	2.6 mΩ	1.6 mΩ	1.5 mΩ	1.4 mΩ
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Insulation resistance Requirements > 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ	> 5 MΩ
Thermal tests (C)				
Tested number of positions	24	10	24	20
Tested conductor cross section	2.5 mm ²	2.5 mm ²	2.5 mm ²	2.5 mm ²
Test current	12 A	12 A	12 A	10 A
Upper limiting temperature Requirements < 100°C	Test passed	Test passed	Test passed	Test passed
Climatic tests (D)				
Test sequence 1: low temperature storage	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h	-40 °C/2 h
Test sequence 2: heat storage	100 °C/168 h	105 °C/168 h	100 °C/168 h	100 °C/168 h
Test sequence 3: noxious gas storage (ISO 6988)	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	4.8 kV	4.8 kV	4.8 kV	4.8 kV
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	2.21 kV	2.21 kV	2.21 kV	2.21 kV
Environmental and endurance tests (E)				
Specification	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10	IEC 61984:2008-10
Degree of protection	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger	Finger safety with IP20 test finger