

Cylindrical Inductive Proximity Sensor

E2E2

Long Barrel Metal Body Inductive Proximity Sensors in a Wide Range of Configurations

- Available in prewired or quick-disconnect versions
- Quick-disconnect versions feature metal connectors for durability
- Easy-to-see LED indicator
- Flats for wrench tightening
- Ideal for a wide variety of applications

Ordering Information _____

SENSORS

DC 2-wire Models

Туре	Size	Sensing Distance	Output Configuration	Part Number
Shielded	M12	3 mm	NO (see note)	E2E2-X3D1
			NC	E2E2-X3D2
	M18	7 mm	NO (see note)	E2E2-X7D1
			NC	E2E2-X7D2
	M30	10 mm	NO (see note)	E2E2-X10D1
		NC	E2E2-X10D2	
Unshielded	M12	8 mm	NO (see note)	E2E2-X8MD1
			NC	E2E2-X8MD2
	M18	14 mm	NO (see note)	E2E2-X14MD1
M30		NC	E2E2-X14MD2	
	M30	20 mm	NO (see note)	E2E2-X20MD1
			NC	E2E2-X20MD2

Note: A different oscillating frequency is available to reduce mutual interference and allow closer mounting. Add a "5" to the part number (e.g., E2E2-X3D15). Consult OMRON for availability.



((₽1∰

DC 3-wire/Pre-wired Models

Туре	Size	Sensing Distance	Output Configuration	Part Number
Shielded	M12	2 mm	NPN NO	E2E2-X2C1
			NPN NC	E2E2-X2C2
			PNP NO	E2E2-X2B1
			PNP NC	E2E2-X2B2
	M18	5 mm	NPN NO	E2E2-X5C1
			NPN NC	E2E2-X5C2
			PNP NO	E2E2-X5B1
M30			PNP NC	E2E2-X5B2
	M30	10 mm	NPN NO	E2E2-X10C1
			NPN NC	E2E2-X10C2
			PNP NO	E2E2-X10B1
			PNP NC	E2E2-X10B2
Unshielded	M12	5 mm	NPN NO	E2E2-X5MC1
			NPN NC	E2E2-X5MC2
			PNP NO	E2E2-X5MB1
			PNP NC	E2E2-X5MB2
	M18	10 mm	NPN NO	E2E2-X10MC1
			NPN NC	E2E2-X10MC2
			PNP NO	E2E2-X10MB1
			PNP NC	E2E2-X10MB2
	M30	18 mm	NPN NO	E2E2-X18MC1
			NPN NC	E2E2-X18MC2
			PNP NO	E2E2-X18MB1
			PNP NC	E2E2-X18MB2

DC 3-wire/Connector Models

Туре	Size	Sensing Distance	Output Configuration	Part Number
Shielded	M12	2 mm	NPN NO	E2E2-X2C1-M1
			NPN NC	E2E2-X2C2-M1
			PNP NO	E2E2-X2B1-M1
			PNP NC	E2E2-X2B2-M1
	M18	5 mm	NPN NO	E2E2-X5C1-M1
			NPN NC	E2E2-X5C2-M1
			PNP NO	E2E2-X5B1-M1
			PNP NC	E2E2-X5B2-M1
	M30	10 mm	NPN NO	E2E2-X10C1-M1
			NPN NC	E2E2-X10C2-M1
			PNP NO	E2E2-X10B1-M1
			PNP NC	E2E2-X10B2-M1
Unshielded	M12	5 mm	NPN NO	E2E2-X5MC1-M1
			NPN NC	E2E2-X5MC2-M1
			PNP NO	E2E2-X5MB1-M1
			PNP NC	E2E2-X5MB2-M1
	M18	10 mm	NPN NO	E2E2-X10MC1-M1
			NPN NC	E2E2-X10MC2-M1
			PNP NO	E2E2-X10MB1-M1
			PNP NC	E2E2-X10MB2-M1
	M30	18 mm	NPN NO	E2E2-X18MC1-M1
			NPN NC	E2E2-X18MC2-M1
			PNP NO	E2E2-X18MB1-M1
			PNP NC	E2E2-X18MB2-M1

Note: Connector cordsets: Use OMRON Y96E-44 D or equivalent.

AC 2-wire/Pre-wired Models

Туре	Size	Sensing Distance	Output Configuration	Part Number
Shielded	M12	2 mm	NO	E2E2-X2Y1–US
			NC	E2E2-X2Y2–US
M18 M30	M18	5 mm	NO	E2E2-X5Y1–US
			NC	E2E2-X5Y2–US
	10 mm	NO	E2E2-X10Y1-US	
			NC	E2E2-X10Y2-US
Unshielded	M12	5 mm	NO	E2E2-X5MY1-US
			NC	E2E2-X5MY2-US
	M18	10 mm	NO	E2E2-X10MY1-US
			NC	E2E2-X10MY2-US
	M30	18 mm	NO	E2E2-X18MY1–US
			NC	E2E2-X18MY2-US

AC 2-wire/Connector Models

Туре	Size	Sensing Distance	Output Configuration	Part Number
Shielded	M12	2 mm	NO	E2E2-X2Y1-M4
			NC	E2E2-X2Y2-M4
M18	M18	5 mm	NO	E2E2-X5Y1-M4
			NC	E2E2-X5Y2-M4
M30	10 mm	NO	E2E2-X10Y1-M4	
			NC	E2E2-X10Y2-M4
Unshielded	M12	5 mm	NO	E2E2-X5MY1-M4
			NC	E2E2-X5MY2-M4
M18 M30	M18	10 mm	NO	E2E2-X10MY1-M4
			NC	E2E2-X10MY2-M4
	M30	18 mm	NO	E2E2-X18MY1-M4
			NC	E2E2-X18MY2-M4

Note: Connector cordsets: Use OMRON Y96E-33 A or equivalent.

ACCESSORIES

Description		Part Number
Mounting brackets	Fits M12 size sensors Fits M18 size sensors Fits M30 size sensors	Y92E-B12 Y92E-B18 Y92E-B30
Silicone rubber covers for shielded sensors	Fits M12 size sensors Fits M18 size sensors Fits M30 size sensors	Y92E-E12-2 Y92E-E18-2 Y92E-E30-2
Connector cordsets	See Y96E Connector Cordsets data sheet for details	

REPLACEMENT PARTS

Description		Part Number
Mounting hardware including one pair of metal nuts and one washer	Fits M12 size sensors Fits M18 size sensors Fits M30 size sensors	M12-MHWS M18-MHWS M30-MHWS

Specifications _____

E2E2-X D DC 2-wire Models

Part numbe	er	E2E2-X3D	E2E2-X8MD	E2E2-X7D	E2E2-X14MD	E2E2-X10D	E2E2-X20M
Size		M12	1	M18		M30	
Туре		Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded
Sensing dis	stance	3 mm (0.12 in) ±10%	8 mm (0.31 in) ±10%	7 mm (0.28 in) ±10%	14 mm (0.55) ±10%	10 mm (0.39) ±10%	20 mm (0.79 in) ±10%
Supply volt voltage ran	tage (operating nge)	12 to 24 VDC, ri	pple (p-p): 10% n	nax., (10 to 30 VE	DC)		
Leakage cu	urrent	0.8 mA max.					
Sensing ob	oject	Magnetic metals	(refer to Engine	<i>ering Data</i> for nor	n-magnetic metals)		
Setting dist	tance	0 to 2.4 mm (0 to 0.09 in)	0 to 6.4 mm (0 to 0.25 in)	0 to 5.6 mm (0 to 0.22 in)	0 to 11.2 mm (0 to 0.44 in)	0 to 8.0 mm (0 to 0.31 in)	0 to 16.0 mm (0 to 0.63 in)
Standard o	bject (mild steel)	12 x 12 x 1 mm (0.47 x 0.47 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	18 x 18 x 1 mm (0.71 x 0.71 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	54 x 54 x 1 mm (2.13 x 2.13 x 0.04 in)
Differential	travel	10% max. of ser	nsing distance				
Response	frequency	1.0 kHz	0.8 kHz	0.5 kHz	0.4 kHz	0.4 kHz	0.1 kHz
Operation approachin	(with sensing object	D1 models: Load ON D2 models: Load OFF					
Control out capacity)	put (switching	3 to 100 mA					
Circuit prot	ection	Surge absorber,	load short-circuit	protection			
Indicator			eration indicator (r eration indicator (r	// I	on set indicator (gr	een LED)	
Ambient te	mperature	Operating: -25°	C to 70°C with no	icing (-13°F to 1	58°F)		
Ambient hu	umidity	Operating: 35% to 95%					
Temperatu	re influence	±10% max. of sensing distance at 23°C in temperature range of -25°C to 70°C (-13°F to 158°F)					
Voltage infl	luence	±1% max. of ser	nsing distance in	rated voltage ran	ge ±15%		
Residual ve	oltage	3.0 V max. (und	er load current of	100 mA with cab	le length of 2 m)		
Insulation r	resistance	50 M Ω min. (at 500 VDC) between current carry parts and case					
Dielectric s	strength	1,000 VAC for 1 min between current carry parts and case					
Vibration re	esistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 10 times each in X, Y, and Z directions					
Shock resist	stance	Destruction: 1,0	00 m/s ² (approx.	100G) for 10 time	es each in X, Y, and	d Z directions	
Enclosure	IEC	IP67					
rating	NEMA	1, 4, 6, 12, 13					
Weight	-	65 g		150 g		220 g	
Material	Body	Brass					
	Sensing face	PBT					

E2E2-X C /B DC 3-wire Models

Part numbe	er	E2E2-X2C□/ B□	E2E2-X5MC□/ B□	E2E2-X5C□/ B□	E2E2-X10MC	E2E2-X10C□/ B□	E2E2-X18MC
Size		M12		M18		M30	
Туре		Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded
Sensing dis	stance	2 mm (0.08 in) ±10%	5 mm (0.20 in) ±10%	5 mm (0.20 in) ±10%	10 mm (0.39 in) ±10%	10 mm (0.39 in) ±10%	18 mm (0.71 in) ±10%
Supply volt voltage ran	tage (operating nge)	12 to 24 VDC, ri	2 to 24 VDC, ripple (p-p): 10% max., (10 to 55 VDC)				
Current cor	nsumption	13 mA max.					
Sensing ob	oject	Magnetic metals	(refer to Enginee	ring Data for non-	magnetic metals)		
Setting dist	tance	0 to 1.6 mm (0 to 0.06 in)	0 to 4.0 mm (0 to 0.16 in)	0 to 4.0 mm (0 to 0.16 in)	0 to 8.0 mm (0 to 0.31 in)	0 to 8.0 mm (0 to 0.31 in)	0 to 14.0 mm (0 to 0.55 in)
Standard o	bject (mild steel)	12 x 12 x 1 mm (0.47 x 0.47 x 0.04 in)	15 x 15 x 1 mm (0.59 x 0.59 x 0.04 in)	18 x 18 x 1 mm (0.71 x 0.71 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	54 x 54 x 1 mm (2.13 x 2.13 x 0.04 in)
Differential	travel	10% max. of ser	nsing distance				
Response	frequency	1.5 kHz	0.4 kHz	0.6 kHz	0.2 kHz	0.4 kHz	0.1 kHz
Operation (approachin	(with sensing object	B1/C1 models: Load ON B2/C2 models: Load OFF					
Control out capacity)	put (switching	200 mA max., open collector					
Circuit prot	ection	Reverse connect	tion protection, su	rge absorber, loa	d short-circuit pro	tection	
Indicator		Operation indica	tor (red LED)				
Ambient te	mperature	Operating: -40°	C to 85°C with no	icing (-40°F to 18	35°F)		
Ambient hu	umidity	Operating: 35%	to 95%				
Temperatu	re influence		ensing distance at ensing distance at				
Voltage infl	luence	±1% max. of ser	nsing distance in r	ated voltage rang	e ±15%		
Residual vo	oltage	2.0 V max. (und	er load current of 2	200 mA with cable	e length of 2 m)		
Insulation r	resistance	50 MΩ min. (at 5	500 VDC) betweer	n current carry pa	rts and case		
Dielectric s	strength	1,000 VAC for 1	min between curr	ent carry parts an	id case		
Vibration re	esistance	Destruction: 10 t	to 55 Hz, 1.5-mm	double amplitude	for 10 times each	n in X, Y, and Z di	rections
Shock resis	stance	Destruction: 1,000 m/s ² (approx. 100G) for 10 times each in X, Y, and Z directions					
Enclosure	IEC	IP67					
rating	NEMA	1, 4, 6, 12, 13					
Weight	•	65 g		150 g		220 g	
Material	Body	Brass					
	Sensing face	PBT					

E2E2-X Y AC 2-wire Models

Part numb	er	E2E2-X2Y□- US	E2E2-X5M□-U S	E2E2-X5Y□ -US	E2E2-X10MY□- US	E2E2-X10□-U S	E2E2-X18MY⊡- US	
Size		M12		M18		M30		
Туре		Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	
Sensing di	stance	2 mm (0.08 in) ±10%	5 mm (0.20 in) ±10%	5 mm (0.20 in) ±10%	10 mm (0.39 in) ±10%	10 mm (0.39 in) ±10%	18 mm (0.71 in) ±10%	
	tage (operating nge) (see note 1)	24 to 240 VAC,	24 to 240 VAC, 50/60 Hz (20 to 264 VAC)					
Leakage c	urrent	1.7 mA max.						
Sensing of	oject	Magnetic metals	6					
Setting dis	tance	0 to 1.6 mm (0 to 0.06 in)	0 to 4.0 mm (0 to 0.16 in)	0 to 4.0 mm (0 to 0.16 in)	0 to 8.0 mm (0 to 0.31 in)	0 to 8.0 mm (0 to 0.31 in)	0 to 14.0 mm (0 to 0.55 in)	
Standard c	bbject (mild steel)	12 x 12 x 1 mm (0.47 x 0.47 x 0.04 in)	15 x 15 x 1 mm (0.59 x 0.59 x 0.04 in)	18 x 18 x 1 mm (0.71 x 0.71 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	30 x 30 x 1 mm (1.18 x 1.18 x 0.04 in)	54 x 54 x 1 mm (2.13 x 2.13 x 0.04 in)	
Differential	travel	10% max. of sensing distance						
Response	frequency	25 Hz						
•	(with sensing	Y1 models: Load ON						
object app	8,	Y2 models: Load OFF						
Control out capacity)	tput (switching	5 to 200 mA 5 to 300 mA (see note 2)						
Indicator		Operation indica	ator (red LED)					
Ambient te	emperature	Operating: -40°	C to 85°C with no	icing (-40°F to	185°F)			
Ambient hu	umidity	Operating: 35%	to 95%					
Temperatu	re influence				rature range of -40 rature range of -25			
Voltage inf	luence	±1% max. of se	nsing distance in	rated voltage ra	nge ±15%			
Residual v	oltage	Refer to Engine	ering Data					
Insulation I	resistance	50 $M\Omega$ min. (at	500 VDC) betwee	n current carry	parts and case			
Dielectric s	strength	4,000 VAC for 1	min between cur	rent carry parts	and case			
Vibration re	esistance	Destruction: 10	to 55 Hz, 1.5-mm	double amplitu	de for 10 times eac	h in X, Y, and Z di	rections	
Shock resi	stance	Destruction: 1,0	00 m/s ² (approx.	100G) for 10 tin	nes each in X, Y, an	d Z directions		
Enclosure	IEC	IP67						
rating	NEMA	1, 4, 6, 12, 13						
Weight		65 g		150 g		220 g		
Approvals	UL	Recognized, Fil	e Number E76675	5				
	CSA	Certified, File N	Certified, File Number LR45951					
Material	Body	Brass						
	Sensing face	PBT						

Note: 1. When using an M18 or M30 size E2E2 at an ambient temperature between 70°C and 85°C, make sure the E2E2 has a control output of 200 mA maximum.


When supplying 24 VAC to any of the above models, make sure that the operating ambient temperature range is -25°C to 85°C (-13°F to 185°F).


Engineering Data _

OPERATING RANGE (TYPICAL)

Shielded Models

E2E2-X D






Sensing distance X (mm)

E2E .X5M


8

Y (mm)

E2E2-X MC /B E2E2-X MY



Unshielded Models E2E2-X MD











-8 -6 -4 -2 0 2 4 6


₿

















■ SENSING DISTANCE VS. SENSING OBJECT (TYPICAL)




E2E2




12 (mm) ╒┬╬ 10 Sensing distance Mild steel Stainless ste (SUS304) Brass Aluminum Copper 0 10 15 20 30 40 60 70 50

Side length of sensing object d (mm)



Side length of sensing object d (mm)




E2E2-X2C /B E2E2-X2Y 2.5 Mild steel Sensing distance (mm) 2.0 steel (SUS304) Stainl 1.5 -X **┎**┎┋┓ EŌ 1.0 Brass 0.5 Aluminum 0 10 15 20 25

5 10 15 20 Side length of sensing


object d (mm)

E2E2-X5MC /B E2E2-X5MY




Side length of sensing object d (mm)






Side length of sensing object d (mm)




E2E2-X10C /B E2E2-X10Y



Side length of sensing object d (mm)


E2E2-X18MC□/B□ E2E2-X18MY□




Operation

OUTPUT CIRCUITS

E2E2-X D DC 2-wire Models




E2E2-X Y AC 2-wire Models




OPERATING CHARTS


E2E2-X D DC 2-wire Models




E2E2-X C /B DC 3-wire Models




E2E2-X C DC 3-wire Models




E2E2-X B DC 3-wire Models



NC Type



E2E2-X Y AC 2-wire Models




E2E2

Dimensions


Unit: mm (inch)





CONNECTOR MODELS (SHIELDED)

E2E2-X2C -M1/B -M1




E2E2-X2Y -M4

E2E2-X5C -M1/B -M1


29 dia (1.14)

24




M18 x 1


CONNECTOR MODELS (UNSHIELDED)




E2E2-X5MY -M4




E2E2-X10MC□-M1/B□-M1



E2E2-X5Y - M4





-75 (2.95)

+ 10

Two clamping nut


Toothed washer

M12 x 1

Operation indicator


60 (2.36)


E2E2-X10MY ...- M4




CONNECTOR MODELS (SHIELDED)

CONNECTOR MODELS (UNSHIELDED)










42 dia. (1.65)

36




Mounting Holes




Dimensions	M12	M18	M30
F (mm)	12.5 dia.	18.5 dia.	30.5 dia.

Installation

E2E2-X DD DC 2-wire Models E2E2-X Y AC 2-wire Models







Note: The load can be connected as shown in the above diagrams.

Connected to PC

E2E2-X D D DC 2-wire Models








■ PIN ARRANGEMENT

E2E2-X B -M1 DC 3-wire Models

Output Configuration	Applicable Models	Pin Arrangement
NO	E2E2-X□B1-M1	Dc Note: Terminal 2 is not used.
	E2E2-X□C1-M1	DC Note: Terminal 2 is not used.
NC	E2E2-X□B2-M1	Doc Note: Terminal 4 is not used.
	E2E2-X□C2-M1	DC Note: Terminal 4 is not used.


E2E2-X Y -M4 AC 2-wire Model



MOUNTING

Do not tighten the nut with excessive force. A washer must be used with the nut.






Effects of Surrounding Metal

When mounting the E2E2 within a metal panel, ensure that the clearances given in the table below are maintained. Failure to maintain these distances may cause deterioration in the performance of the sensor.

Note: The table below shows the tightening torques for part A and part B nuts. In the previous examples, the nut is on the sensor head side (part B) and hence the tightening torque for part B applies. If this nut is in part A, the tightening torque for part A applies instead.

Туре	Torque
M12	30 N • m (310 kgf • cm)
M18	70 N • m (710 kgf • cm)
M30	180 N • m (1,800 kgf • cm)



Туре		Item	M12	M18	M30
E2E2-X□D□	Shielded	l	0 mm	0 mm	0 mm
DC 2-wire		d	12 mm	18 mm	30 mm
		D	0 mm	0 mm	0 mm
		m	8 mm	20 mm	40 mm
		n	18 mm	27 mm	45 mm
	Unshielded	l	15 mm	22 mm	30 mm
		d	40 mm	70 mm	90 mm
		D	15 mm	22 mm	30 mm
		m	20 mm	40 mm	70 mm
		n	40 mm	70 mm	90 mm
E2E2-X B E2E2-X C DC 3-wire E2E2-X Y AC 2-wire	Shielded	l	0 mm	0 mm	0 mm
		d	12 mm	18 mm	30 mm
		D	0 mm	0 mm	0 mm
		m	8 mm	20 mm	40 mm
		n	18 mm	27 mm	45 mm
	Unshielded	l	15 mm	22 mm	30 mm
		d	40 mm	55 mm	90 mm
		D	15 mm	22 mm	30 mm
		m	20 mm	40 mm	70 mm
		n	36 mm	54 mm	90 mm

E2E2 -

L

MUTUAL INTERFERENCE

When installing two or more Sensors face to face or side by side, ensure that the minimum distances given in the following table are maintained.

Туре		Item	M12	M18	M30
E2E2-X□D□ DC 2-wire	Shielded	A	30 (20) mm	50 (30) mm	100 (50) mm
		В	20 (12) mm	35 (18) mm	70 (35) mm
	Unshielded	A	120 (60) mm	200 (100) mm	300 (100) mm
		В	100 (50) mm	110 (60) mm	200 (100) mm
E2E2-X B E2E2-X C DC 3-wire E2E2-X Y AC 2-wire	Shielded	A	30 mm	50 mm	100 mm
		В	20 mm	35 mm	70 mm
	Unshielded	A	120 mm	200 mm	300 mm
		В	100 mm	110 mm	200 mm

Note: The figures in parentheses refer to Sensors operating at different frequencies.

The colors in parentheses are previous wire colors.

Item	Examples	
Power supply	DC 3-wire models	DC 2-wire models
Do not impose an excessive voltage on the E2E, otherwise it may explode or burn. Do not impose 100 VAC on any E2E DC model, otherwise it may explode or burn.	Brown (red) Sensor Blue (black) Blue	Brown (white) Sensor Blue (black)
Wiring	DC 3-wire models	
Be sure to wire the E2E and load correctly, otherwise it may explode or burn.	Brown (red) Sensor Blue (black)	Brown (red) Sensor Blue (black) Black (white)
Connection with no load	DC 2-wire models	
Make sure to connect a proper load to the E2E in operation, otherwise it may explode or burn.	Brown (white) Sensor Blue (black)	

Precautions

INSTALLATION

Power Reset Time

The Proximity Sensor is ready to operate within 100 ms after power is supplied. If power supplies are connected to the Proximity Sensor and load respectively, be sure to supply power to the Proximity Sensor before supplying power to the load.

Power OFF

The Proximity Sensor may output a pulse signal when it is turned off. Therefore, it is recommended to turn off the load before turning off the Proximity Sensor.

Power Supply Transformer

When using a DC power supply, make sure that the DC power supply has an insulated transformer. Do not use a DC power supply with an auto-transformer.

Sensing Object

Metal Coating:

The sensing distances of the Proximity Sensor vary with the metal coating on sensing objects.

WIRING

High-tension Lines:

Wiring through Metal Conduit

If there is a power or high-tension line near the cord of the Proximity Sensor, wire the cord through an independent metal conduit to prevent against Proximity Sensor damage or malfunctioning.

CONNECTING LOAD TO AC OR DC 2-WIRE SENSOR

Refer to the following before using AC or DC 2-wire Proximity Sensors.

Surge Protection

Although the Proximity Sensor has a surge absorption circuit, if there is any machine that has a large surge current (e.g., a motor or welding machine) near the Proximity Sensor, connect a surge absorber to the machine.

Leakage Current

When the Proximity Sensor is OFF, the Proximity Sensor has leakage current. Refer to Leakage Current Characteristics. In this case, the load is imposed with a small voltage and the load may not be reset. Before using the Proximity Sensor, make sure that this voltage is less than the load reset voltage. The AC 2-wire Proximity Sensor cannot be connected to any card-lift-off relay (e.g., the G2A) because contact vibration of the relay will be caused by the leakage current and the life of the relay will be shortened.

Countermeasures Against Leakage Current

AC 2-wire Models

Connect a bleeder resistor as the bypass for the leakage current so that the current flowing into the load will be less than the load reset current.

As shown in the following diagram, connect the bleeder resistor so that the current flowing into the Proximity Sensor will be 10 mA minimum and the residual voltage imposed on the load will be less than the load reset voltage.



Cord Tractive Force

Do not pull cords with the tractive forces exceeding the following.

Diameter	Tractive force
4 mm dia. max.	30 N max.
4 mm dia. min.	50 N max.

MOUNTING

The Proximity Sensor must not be subjected to excessive shock with a hammer when it is installed, otherwise the Proximity Sensor may be damaged or lose its water-resistance.

ENVIRONMENT

Water Resistance

Do not use the Proximity Sensor underwater, outdoors, or in the rain.

Operating Environment

Be sure to use the Proximity Sensor within its operating ambient temperature range and do not use the Proximity Sensor outdoors so that its reliability and life expectancy can be maintained. Although the Proximity Sensor is water resistant, a cover to protect the Proximity Sensor from water or water soluble machining oil is recommended so that its reliability and life expectancy can be maintained. Do not use the Proximity Sensor in an environment with chemical gas (e.g., strong alkaline or acid gasses including nitric, chromic, and concentrated sulfuric acid gases).

Refer to the following to calculate the bleeder resistance and the allowable power of the bleeder resistor.

- $R \leq V_S/(10 I) (k\Omega)$
- $P > V_S^2/R (mW)$
- P: The allowable power of the bleeder resistor. (The actual power capacity of the bleeder resistor must be at least a few times as large as the allowable power of the bleeder resistor.)
- I: Load current (mA)

The following resistors are recommended.

100 VAC (supply voltage): A resistor with a resistance of 10 k Ω maximum and an allowable power of 3 W minimum

200 VAC (supply voltage): A resistor with a resistance of 20 $k\Omega$ maximum and an allowable power of 10 W minimum

If these resistors generate excessive heat, use a resistor with a resistance of 10 k Ω maximum and an allowable power of 5 W minimum at 100 VAC and a resistor with a resistance of 20 k Ω maximum and an allowable power of 10 W minimum at 200 VAC instead.

DC 2-wire Models

Connect a bleeder resistor as the bypass for the leakage current so that the current flowing into the load will be less than the load reset current.



E2E2 -

DC 2-wire Models, continued

Refer to the following to calculate the bleeder resistance and the allowable power of the bleeder resistor.

 $\mathsf{R}\, \leq\, \mathsf{V}_{\mathsf{S}}/(\mathsf{i}_{\mathsf{R}}-\mathsf{i}_{\mathsf{OFF}})\;(\mathsf{k}\Omega)$

$$P > V_S^2/R (mW)$$

- P: The allowable power of the bleeder resistor. (The actual power capacity of the bleeder resistor must be at least a few times as leave as the ellowable power for the bleeder resistor must be at leave to be at leave large as the allowable power of the bleeder resistor.)
- i_R: Leakage current of Sensors (mA)

iOFF: Release current of load (mA)

The following resistors are recommended. 12 VDC (supply voltage): A resistor with a resistance of 15 k Ω maximum and an allowable power of 450 mW minimum 24 VDC (supply voltage): A resistor with a resistance of 30 k Ω maximum and an allowable power of 0.1 W minimum

Inrush Current

A load that has a large inrush current (e.g., a lamp or motor) will damage the Proximity Sensor, in which case connect the load to the Proximity Sensor through a relay.

PRECAUTIONS FOR AC OR DC 2-WIRE PROXIMITY SENSORS IN OPERATION

Connection

Model	Connection Type	Method	Description
DC 2-wire	AND (serial connection)	Correct	The Sensors connected together must satisfy the following conditions.
			$\begin{array}{ll} V_S - N \; x \; V_R \; \geqq \; Load \; operating \; voltage \\ N: & No. \; of \; Sensors \\ V_R: \; Residual \; voltage \; of \; each \; Sensor \\ V_S: \; \; Supply \; voltage \end{array}$
			If each Proximity Sensor is not supplied with the rated voltage and current, the indicator will not be lit properly or unnecessary pulses may be output for approximately 1 ms.
	OR (parallel connection)	Correct	The Sensors connected together must satisfy the following conditions.
			 N x i ≤ Load operating voltage N: No. of Sensors i: Leakage current of each Sensor
			If the MY Relay, which operates at 24 VDC, is used as a load for example, a maximum of four Proximity Sensors can be connected to the load.
AC 2-wire	AND (serial connection)		If 100 or 200 VAC is imposed on the Proximity Sensors, V_L (i.e., the voltage imposed on the load) will be obtained from the following.
			$V_L = V_S -$ (residual voltage x no. of Proximity Sensors) (V)
		Correct	Therefore, if V_L is lower than the load operating voltage, the load will not operate.
			A maximum of three Proximity Sensors can be connected in series provided that the supply voltage is 100 V minimum.

Model Method **Connection Type** Description AC OR In principle, more than two Proximity Sensors Incorrect 2-wire (parallel connection) cannot be connected in parallel. Load Provided that Proximity Sensor A does not operate with Proximity Sensor B simultaneously and there is no need to keep the load operating continuously, the Proximity Sensors can be Correct connected in parallel. In this case, however, due to the total leakage current of the Proximity Load Sensors, the load may not reset properly. VAC power supply V_S 0 It is not possible to keep the load operating continuously with Proximity Sensors A and B in simultaneous operation to sense sensing objects due to the following reason. When Proximity Sensor A is ON, the voltage imposed on Proximity Sensor A will drop to approximately 10 V and the load current flows into Proximity Sensor A, and when one of the sensing objects is close to Proximity Sensor B, Proximity Sensor B will not operate because the voltage imposed on Proximity Sensor B is 10 V, which is too low. When Proximity Sensor A is OFF, the voltage imposed on Proximity Sensor B will reach the supply voltage and Proximity Sensor B will be ON. Then, Proximity Sensor A as well as Proximity Sensor B will be OFF for approximately 10 ms, which resets the load for an instant. To prevent the instantaneous resetting of the load, use a relay as shown on the left. DC The Sensors connected together must satisfy the Correct 3-wire (serial connection) following conditions. i_L + (N –1) x i \leq Upper-limit of control output of Load each Sensor $V_S - N \times V_R \ge$ Load operating voltage ٧s N: No. of Sensors V_R: Residual voltage of each Sensor V_S: Supply voltage i: Current consumption of the Sensor Load current iL: If the MY Relay, which operates at 24 VDC, is used as a load for example, a maximum of two Proximity Sensors can be connected to the load. A minimum of three Sensors with current outputs OR Correct (parallel connection) can be connected in parallel. The number of Sensors connected in parallel varies with the Load Proximity Sensor model.

PRECAUTIONS FOR AC OR DC 2-WIRE PROXIMITY SENSORS IN OPERATION, CONTINUED

E2E2	F	2E2

NOTE: DIMENSIONS SHOWN ARE IN MILLIMETERS. To convert millimeters to inches divide by 25.4.

ORRON ELECTRONICS, INC. One East Commerce Drive Schaumburg, IL 60173 1-800-55-OMRON

OMRON CANADA, INC. 885 Milner Avenue Scarborough, Ontario M1B 5V8 416-286-6465

Cat. No. CEDSAX2

3/97

Specifications subject to change without notice.

Printed in U.S.A.