

ALS-PDIC17-79NB/TR8

Surface - Mount I²C Digital Ambient Light Sensor

Features

LIGHTING

- · Close to the human eye's response
- 15 bit effective resolution
- 50Hz/60Hz rejection
- Low sensitivity variation across various light sources
- Operating temperature performance, -40°C to 85°C
- Wide supply voltage range, 2.7V to 5.5V
- \bullet Low power consumption, less than 2mW while operating
- Shut-down mode, current consumption less than 0.1uA
- I²C serial port communication: (1) Standard 100kHz, (2).Fast 400kHz
- High dynamic sensing range and from 0 to 220,000 Lux
- Size: 2.0mm(L)*2.0mm(W)*0.6mm(H)
- RoHS compliant and Pb Free

Description

The ALS-PDIC17-79NB/TR8 is a digital-output light sensor with a two-wire, I²C serial interface that is compatible with SMBus when working at 100kHz serial clock frequency. It combines a photodiode and an analog-to-digital converter (ADC) on a single CMOS integrated circuit to provide light measurements over an effective 15-bit dynamic range. Two operation modes are provided with one for constantly refreshing ADC and the other for one time integration. When working in "one time integration" mode, no external resister is required. The integrating conversion technique used by ALS-PDIC17-79NB/TR8 effectively eliminates the effect of flicker from AC-powered lamps, increasing the stability of the measurement. ALS-PDIC17-79NB/TR8 wavelength is close to human-eye, and low response to non-visible light, such as infrared and ultra-violet light.


Applications

- Detection of ambient light for controlling the backlighting of TFT LCD display
- Automatic residential and commercial lighting management
- Automatic contrast enhancement for electronic signboard
- Ambient light monitoring device for daylight and artificial light



LIGHTING FOREVER Surface - Mount I²C Digital Ambient Light Sensor

Package Dimensions



Unit: mm



FOREVER

LIGHTING

ALS-PDIC17-79NB/TR8

Surface - Mount I²C Digital Ambient Light Sensor

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Min.	Max.	Units
Storage temperature	Тѕтс	-40	100	°C
Operating temperature	TOPR	-40	85	°C
Supply voltage	VDD	-0.3	6.0	V
Digital output voltage	Vo	-0.3	6.0	V
Digital output current	lo	-10	+10	mA
ESD tolerance, human body model	-	2	-	KV

Block Diagram & Pad Descriptions




Figure 1. ALS-PDIC17-79NB/TR8 Functional Block Diagram

LIGHTING

ALS-PDIC17-79NB/TR8

Surface - Mount I²C Digital Ambient Light Sensor

FOREVER

Electrical and Optical Characteristics (Ta=25 $^{\circ}$ C , V_{DD}=3.3V)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Units
Cupply surrent	Idd	Active mode	-	0.4	0.5	mA
Supply current	Iddq	Power-down mode	-	-	0.1	uA
I ² C output low voltage	Vol	Io = 4mA	-	-	0.4	V
Data ati an linait		Full scale	-	-	32,767	counts
Detection limit		T int = 100mS	-	-	44,200	Lux
Peak sensitivity wavelength	λр		-	550	-	nm
Response in dark environment	Rdak	Ev= 0lx, T int = 100mS	-	-	1	counts
Response to incandescent lamp	Ricd	Ev= 100lx T int = 100mS	65	108	151	counts
Response to fluorescent lamp	Rfrst	Ev= 100lx T int = 100mS	44	73	102	counts

Note:

- 1. Fluorescent light (Color Temperature = 6500K) is used as light source. However, White LED is substituted in mass production.
- 2. Illuminance by CIE standard illuminant A 2856K of incandescent lamp.

DC Characteristics of I²C Signals in Standard and Fast Mode

Devenueter	Combal	Standard Mode		Fast Mode		
Parameter	Symbol	Min.	Max.	Min.	max.	Unit
Power supply voltage (recommend)	Vdd	2.7	5.5	2.7	5.5	V
Low level input voltage	Vil	-0.5	1.0	-0.5	1.0	V
High level input voltage	Vih		VDD*0.6		VDD*0.6	V
Hysteresis of Schmitt trigger inputs (VDD > 2V)	Vhys	0.05Vdd	-	0.05Vdd	-	V
Low level output voltage (open drain) at 3mA sink current (VDD > 2V)	Vol1	0	0.4	0	0.4	V
Output fall time from VIHMIN to VILMAX with a bus capacitance from 10pF to 400pF	tr	-	250 ^[2]	20+0.1C b ^[1]	250 ^[2]	nS
Input current of each IO pins with an input voltage between 0.1VDD and 0.9VDD	Iinput	-10	10	-10	10	uA
Capacitance for each IO pin	Ci	-	10	-	10	рF



FOREVER

Surface - Mount I²C Digital Ambient Light Sensor

Notes:

LIGHTING


- 1. Cb = capacitance of one bus line in pF
- 2. The maximum tf for the I²C data and clock bus lines quoted in the AC table is longer than the specified maximum tof for the output stages (250nS). This allows series protection resistors (Rs) to be connected between I²C data / clock pins and the I²C data / clock bus lines without exceeding the maximum specified tf.
- 3. The I²C bus operation voltage is 1.8V, The ALS-PDIC17-79NB supply voltage must \leq 3V (3V*0.6=1.8V)

AC Characteristics of I2C Signals in Standard and Fast Mode

		Standar	d Mode	Fast Mode		
Parameter	Symbol	Min.	Max.	Min.	max	Unit
I ² C clock frequency	fscl	0	100	0	400	KHz
Hold time (repeated) START						
condition. After this period, the first clock pulse is generated.	thd;sta	4.0		0.6	-	us
Low period of I ² C clock	tLOW	4.7		1.3		us
High period of I ² C clock	tнigн	4.0		0.6		us
Set-up time for a repeated START condition	tsu;sta	4.7		0.6		us
Data hold time for I ² C-bus devices	t hd;dat	0	3.45	0	0.9	us
Data set-up time	tsu;dat	250	-	100	-	ns
Rise time of both I ² C data and clock signal's	tr	-	1000	5	300	ns
Fall time of both I ² C data and clock signal's	tf	-	300	0.1	300	ns
Set-up time for STOP condition	tsu;sто	4.0	-	0.6	-	us
Bus free time between STOP and START condition	tbuf	4.7	-	1.3	-	us
Capacitive load for each bus line	Cb	-	400	-	400	pF
Noise margin at the low level for each connected device (including hysteresis)	VnL	0.1Vdd	-	0.1Vdd	-	V
Noise margin at the high level for each connected device (including hysteresis)	VnH	0.2Vdd	-	0.2Vdd	-	V

LIGHTING FOREVER Surface - Mount I²C Digital Ambient Light Sensor

ALS-PDIC17-79NB/TR8



Typical Electrical and Optical Characteristics Curves

Fig.3 Output code vs. Illuminance






Fig.5 Output code vs. Supply voltage










Fig.4 Output code vs. Supply voltage

Surface - Mount I²C Digital Ambient Light Sensor

Fig.7 Supply current vs. Temperature




Fig.9 Output code vs. Temperature




Fig.8 Output code vs. Temperature

ALS-PDIC17-79NB/TR8





Fig.10 Spectral response

(typ.)




ALS-PDIC17-79NB/TR8


Surface - Mount I²C Digital Ambient Light Sensor

Communication Protocol

ALS-PDIC17-79NB contains an 8-bit command register that can be written and read via the I²C bus. The command register controls the overall operation of the device. There is a two-byte word read-only register that contains the latest converted value of A/D converter. The I²C slave address is hardwired internally as 00111001 (0x39, MSB to LSB, A6 to A0). All the Send Byte protocol, the Receive Byte protocol and Receive Word protocol are implemented in ALS-PDIC17-79NB.

The Send Byte protocol allows single bytes of data to be written to the device (see Figure 11-a). The written byte is called the COMMAND byte. The Receive Byte protocol allows one-byte data to be read from the device (see Figure 11-b). Two-byte data can be read by following the Receive Word Protocol shown in Figure 11-c. In Figure 11, the clear area represents data sent by the host (master) and the shaded area represents data returned by the ambient light sensor (slave device).





Communication Format

ALS-PDIC17-79NB is capable of working as an I^2C slave. Address of this device on I^2C bus is always 0x39 (hexadecimal number 39). Registers of the slave device can be programmed by sending commands over I^2C bus.

Figure 12 shows an I^2C write operation. To write to an internal register of the slave device a command must be sent by an I^2C master. As illustrated in Figure 12, the I^2C write command begins with a start condition. After the start condition, seven bits of address are sent with MSB going first. RD / WRn (=Low) command bit follows the address bits. Upon receiving a valid address the slave device responds by driving SDA low for an ACK. After receiving an ACK, I^2C master sends eight bits of data with MSB first. Upon receiving eight bits of data the slave device generates an ACK. I^2C master terminates this write command with a stop condition.




Figure 12. I²C Timing Diagram for Send Byte Format

Figure 13 shows an I^2C read command sent by the master to the slave device. I^2C read command begins with a start condition. After the start condition seven bits of address are sent by the master with MSB going first. After the address bits, RD / WRn command bit is sent. For a read command the RD / WRn bits is high. Upon receiving the address bits and RD / WRn command bits the slave device responds with an ACK. After sending an ACK, the slave device sends eight bits of data with MSB going first. After receiving the one byte data, the I^2C master terminates this transaction by issuing a NACK command to indicate that the master only wanted to read one byte from the device. The master generates a stop condition to end this transaction.

LIGHTING

ALS-PDIC17-79NB/TR8

Surface - Mount I²C Digital Ambient Light Sensor




Figure 13. I²C Timing Diagram for Receive Byte Format

Ambient light intensity count value can be obtained by reading registers of this device. Ambient light intensity count is a 15-bit wide number plus a valid bit and hence word (two bytes) read operation is needed, as shown in Figure 14. After receiving the two byte data, the I^2C master terminates this transaction by issuing a NACK command to indicate that the master only wanted to read two bytes from the device. The master generates a stop condition to end this transaction.




Figure 14. I^2C Timing Diagram for Receive Word Format

Theory of Operation

The photocurrent, generated by the built-in photodiode while being illuminated, is proportionally converted to frequency; the digital frequency signal is then integrated by a 15-bit counter for a predetermined period of time (**T**int). This period of time is called integration time which can be adjusted by changing the nominal value of the resistor between the RINT and GND terminals. The converted data are read out through a two-wire, I2C Interface bus. Since the photodiode has been specially processed to suppress the spectral response in infrared region, the readout is very close to the photopia transfer function, $v(\lambda)$, which is the mathematic expression of human-eye's response to ambient light.

Address Option for I²C

The I²C address is determined before placing an order; users can assign any one of the three addresses (0x39, 0x29, 0x44) for their specific application. Without any prior request for a specific I²C address, the default address is 0x39.

Address Pin Configuration	I2C Address
Floating	0x39 (default)
Tied to GND	0x29
Tied to VCC	0x44

Table 1. Connecting options of I^2C address

ADC Register

The ADC register contains 16 bits with a 15-bit wide data from D0 to D14 and a valid bit D15. The register is divided into two groups; D[15..8] is the most significant (MS) byte and D[7..0] is the least significant (LS) byte. See Table 2 for details.

Valid Bit	Data Bits				
D15	D14	D13 ~ D8	D7~D1	D0	
	MSB LSB				
Most Significant (MS) byte		Least Signif	icant (LS) byte		

Surface - Mount

I²C Digital Ambient Light Sensor

Device Command

There are eight command codes are provided for I²C master to control the ambient light sensor. The specific function corresponding to each command code is elaborate in Table 3.

Command Code	Function
1xxx_xxxx (binary code)	Shut-down mode, this is the default state after applying VDD power to the device. During shut-down mode, users can do the communication test. Except the MSB must be logic 1, the value written to the command register will not change any function and can be read back via the I ² C bus by issuing <i>Receive Byte Protocol</i> .
0x0C	Activate the ambient light sensor and put the device in [continuous operation mode], The ADC register will be refreshed every T int integration time which is set by an external resistor Rext. See Table 4 for details.
0x04	Activate the ambient light sensor and put the device in [one time integration mode]. The integration time is controlled by I^2C commands, start and stop integration.
0x08	Start integration: This command will reset the ADC register to 0x0000 and begin a new integration in [one time integration mode]. This is an invalid command in [continuous operation mode].
0x30	Stop integration: This command will stop the integration in [one time integration mode] and set the valid bit (D[15]) high. This is an invalid command in [continuous operation mode].
0x34	Reserved for future expansion.

Table 3. Com	mand	Code	List
--------------	------	------	------

Programming Sequence

Case 1: Using internal integration timing

- (1). After being powered on, the device will initially be in the shut-down mode (default setting).
- (2). To operate the device, issue an Send Byte protocol (see Figure 11-a) with the device address 0x39 followed by a command byte of 0x0C to activate the ambient light sensor and put the device into "continuous operation mode".
- (3). To read the ADC conversion result, issue an Receive Word protocol (see Figure 11-c) with the device address 0x39 followed by two-byte reading procedures.

ALS-PDIC17-79NB/TR8

- Surface Mount I²C Digital Ambient Light Sensor
 - (4). If a conversion has not been completed since being activated, the valid bit (D[15]) will be 0 to indicate that the data is not valid. If there is a valid conversion result available, the valid bit (D[15]) will be set logic high, and the remaining 15 bits will represent valid data from the ADC register.
 - (5). Data may be read repeatedly from the ADC register, and although it will remain valid, the ADC register will not be updated until a new conversion completes.

Case 2: Using external integration timing

- (1). After being powered on, the device will initially be in the shut-down mode (default setting).
- (2). To operate the device, issue an Send Byte protocol (see Figure 11-a) with the device address 0x39 followed by a command byte of 0x04 to activate the ambient light sensor and put the device into "one time integration mode".
- (3). I²C master sends a "start integration command" to the salve device by issuing Send Byte protocol with the device address 0x39 followed by a command byte of 0x08.
- (4). After a period of user defined integration time, I^2C master sends a "stop integration command" to the salve device by issuing Send Byte protocol with the device address 0x39 followed by a command byte of 0x30.
- (5). To read the ADC conversion result, issue an Receive Word protocol (see Figure 11-c) with the device address 0x39 followed by two-byte reading procedures.
- (6). If the stop integration command is not received by the device, the valid bit (D [15]) will be "0" to indicate that the data is not valid. If there is a valid conversion result available, the valid bit (D [15]) will be set logic high, and the remaining 15 bits will represent valid data from the ADC register.
- (7). Data may be read repeatedly from the ADC register, and although it will remain valid, the ADC register will not be updated until a new complete integration cycle has been carried out.

In both cases, the power consumption of the device can be reduced by issue an Send Byte protocol with the device address 0x39 followed by a data byte of 1xxx_xxxx (Binary code).

Noise Rejection and Integration Time

In general, integrating type ADC's have an excellent noise rejection characteristics for periodic noise sources whose frequency is an integer multiple of the integration time. For instance, a 60Hz AC unwanted signal's sum from 0ms to n*16.66ms (n = 1, 2...ni) is zero.

Similarly, setting the ALS-PDIC17-79NB integration time to an integer multiple of periodic noise signal greatly improves the light sensor output signal in the presence of noise. The integration time, **T**int, of the ALS-PDIC17-79NB is set by an external resistor Rext. The maximum detection range is inversely proportional to the integration time; that means the longer integration time the lower detection range.

Rext (KΩ)	Integration time (mS)	Detection range (lux)	Resolution (lux / count)
50 (min.)	50	88,400	2.7
100 (recommended)	100	44,200	1.35
200	200	22,200	0.68
300	300	14,500	0.45
400 (max.)	400	11,100	0.34

Table 4. Rext Resistor Selection Guide

In order to achieve both 60Hz and 50Hz AC rejection, the integration time needs to be adjusted to coincide with an integer multiple of the AC noise cycle times. To determine a suitable integration time, **T**int, that will ignore the presence of both 60Hz and 50Hz noise, users can use the formula:

Tint = n(1/60Hz) = m(1/50Hz), where n and m are integers.

n/m = 60Hz/50Hz = 6/5.

The first instance of integer values at which **T** int rejects both 60Hz and 50Hz is when m = 5, and n = 6, thus,


Tint = 6(1/60Hz) = 5(1/50Hz) = 100ms,

Rext = \mathbf{T} int* (100k Ω /100ms) = 100k Ω , (see Table 4)

By populating Rext = $100k\Omega$, ALS-PDIC17-79NB defaults to 100ms integration time in continuous operation mode, and will reject the presence of both 60Hz and 50Hz power line signals. When working in one-time integration mode, the master must control the integration time to be an integer multiple of 100ms.

Power Supply Decoupling and Layout

The power supply lines must be decoupled with capacitors, 4.7uF and 0.1uF, placed as close to the device package as possible. The bypass capacitor should have low effective series resistance (ESR) and effective series inductance (ESI), such as the common ceramic types, which provide a low impedance path to ground at high frequencies to handle transient currents caused by internal logic switching. ALS-PDIC17-79NB is relatively insensitive to layout. Like other I²C devices, it is intended to provide excellent performance even in significantly noisy environments. There are only a few considerations that will ensure best performance. Route the supply and I²C traces as far as possible from all sources of noise. Use two power-supply decoupling capacitors, 4.7μ F and 0.1μ F, placed close to the device.



ALS-PDIC17-79NB/TR8

Surface - Mount I²C Digital Ambient Light Sensor

Recommended method of storage

- 1. Do not open moisture proof bag before devices are ready to use.
- 2. Shelf life in sealed bag from the bag seal date:


18 months at 10 ℃~30 ℃ and < 90% RH.

- 3. After opening the package, the devices must be stored at $10^{\circ}C\sim 30^{\circ}C$ and $\leq 60^{\circ}RH$, and used within 168 hours (floor life).
- 4. If the moisture absorbent material (desiccant material) has faded or unopened bag has exceeded the shelf life or devices (out of bag) have exceeded the floor life, baking treatment is required.
- 5. If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure or recommend the following conditions:

192 hours at 40 $^{\circ}$ C +5/–0 $^{\circ}$ C and < 5 $^{\circ}$ RH (reeled/tubed/loose units) or 96 hours at 60 $^{\circ}$ C ± 5 $^{\circ}$ C and < 5 $^{\circ}$ RH (reeled/tubed/loose units) or 24 hours at 125 $^{\circ}$ C + 5 $^{\circ}$ C not suitable for real or tubes

24 hours at $125 \,^{\circ}C \pm 5 \,^{\circ}C$, not suitable for reel or tubes.

Recommended Solder Profile



Notice:


- (1) Reflow soldering should not be done more than two times.
- (2) When soldering, do not put stress on the devices during heating.
- (3) After soldering, do not warp the circuit board.

Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

Repairing

Repair should not be done after the device have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the device will or will not be damaged by repairing.





LIGHTING FOREVER Surface - Mount I²C Digital Ambient Light Sensor


Packing Quantity Specification

2000 PCS/ 1 Reel

Label Format




Reel Dimensions



Tolerance: ±0.1mm

Tape Dimensions



Note:

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.