Energy Management Energy Analyzer Type EM24 DIN





- RS485 serial output (MODBUS-RTU), iFIX SCADA compatibility
- M-bus communication port (option M1)
- Dupline communication capability (option DP)
- Application adaptable display and programming procedure (Easyprog function)
- Easy connections management
- Certified according to MID Directive (option PF): see "how to order" below
- Other versions available (not certified, option X):
 see "how to order" on the next page

- Class 1 (kWh) according to EN62053-21
- Class B (kWh) according to EN50470-3
- Class 2 (kvarh) according to EN62053-23
- Accuracy ±0.5 RDG (current/voltage)
- Energy analyzer
- Instantaneous variables readout: 4 DGT
- Energies/gas/water readout: 8 DGT
- System variables: VLL, VLN, Admd max, VA, VAdmd, VAdmd max, W, Wdmd, Wdmd max, var, PF, Hz, Phase-sequence.
- Single phase variables: VLL, VLN, A, VA, W, var, PF
- Energy measurements: total and partial kWh and kvarh or based on 4 different tariffs; single phase measurements
- Gas, cold water, hot water, kWh remote heating measurements
- Hour counter (6+2 DGT)
- TRMS measurements of distorted sine waves (voltages/currents)
- Self power supply (AV2-AV9 inputs)
- Auxiliary power supply (AV5-AV6 inputs)
- 3 digital inputs for tariff selection, DMD synch or gas/ water (hot-cold) and remote heating metering (on request)
- 2 digital outputs for pulses or for alarms or as a mix of them
- Dimensions: 4-DIN modules
- Protection degree (front): IP50

Product Description

Three-phase energy analyzer with built-in configuration joystick and LCD data displaying; particularly indicated for active and reactive energy metering and for cost allocation. Housing for DIN-

rail mounting with IP50 (front) protection degree. Direct connection up to 65A and by means of external current and potential transformers.

Moreover the meter can be

provided with digital outputs that can be either for pulse proportional to the active (imported and exported) and reactive energy being measured or for alarm outputs. In alternative the RS485 communication port and 3 digital inputs or Dupline port and 3 digital inputs or the M-bus communication port are available as an option.






Certified according to MID Directive, Annex "B" + Annex "D" for legal metrology relevant to active electrical energy meters (see Annex MI-003 of MID). Can be used for fiscal (legal)

metrology. Only the total positive energy meter is certified according to MID.

How to order EM24 DIN AV5 3 D O2 PF A



Type Selection for MID version

Range codes

AV5: 400V_{LL} AC - 5(10)A (CT connection)

AV2: 400V_{LL}AC 10(65)A (direct connection)

V_{LN}: 113V to 265V_{LN}

V_{LL}: 196V to 460V_{LL}

AV9: 400V_{LL} AC - 10(65)A

AV9: 400V_{LL} AC - 10(65)A (direct connection)
V_{LN}: 184V to 276V_{LN}
V_{LL}: 318V to 480V_{LL}

System

3: 3-phase, 4-wire

NOTE: please check the availability of the needed code on the verification path diagram below before order.

Power supply

X: Self power supply (See "Power supply specifications") D: 115/230VAC (50Hz)

Options

PF:

Certified according to MID Directive, Annex "B" + Annex "D" for legal metrology relevant to active electrical energy meters (see Annex MI-003 of MID). Can be used for fiscal (legal) metrology.

Inputs/Outputs

XX: none

O2: dual open collector type (dual pulse or one pulse + one alarm or dual alarm)

IS: 3 digital inputs for tariff selection or Gas/Water/ remote heating metering plus RS485 port

DP: Dupline port plus 3 digital inputs for Gas/ water/ remote heating metering

M1: M-bus port

Measurement

- A: The power is always integrated (both in case of positive imported and negative exported power) and the total energy meter is certified according to MID.
- **B:** Only the total positive imported- energy meter is certified according to MID. The negative exported-energy meter is not certified according to MID.



STANDARD

Not certified according to MID directive. Cannot be used for fiscal (legal) metrology.

How to order EM24 DIN AV5 3 D O2 X

Model


Range code


System

Power supply
Inputs/Outputs
Option

Type Selection for standard version

Range codes		System	Powe	er supply	Inputs/Outputs		
AV5:	400V _{LL} AC - 1/5 (10)A (CT connection) V _{LN} : 160 V to 480V _{LN} V _{LL} : 277 V to 830V _{LL} 208V _I , AC - 1/5(10)A	3: balanced and unbalanced load: 3-phase, 4-wire; 3-phase, 3-wire; 2-phase, 3-wire;	X: L:	Self power supply (See "Power supply specifications") 18 to 60VAC/DC (48 to 62Hz)	XX: O2:	none dual open collector type (dual pulse or one pulse + one alarm or dual alarm)	
	(VT/PT and CT connections) V _{LN} : 40V to 144V _{LN} V _{LI} : 70V to 250V _{LI}	1-phase, 2-wire	D:	115/230 VAC (48 to 62Hz)	R2: IS:	dual relay type (functions as per "O2") 3 digital inputs for tariff selection or Gas/	
AV2:	400V _{LL} AC 10(65)A (direct connection) V _{LN} : 113V to 265V _{LN}		Option	ns		water/ remote heating metering plus RS485 port	
AV9:	V _{LL} : 196V to 460V _{LL} 400V _{LL} AC - 10(65)A (direct connection) V _{LN} : 184V to 276V _{LN} V _{ILI} : 318V to 480V _{LL}	NOTE: please check the availability of the needed code on the verification path tables below before order.	X:	none	DP:	Dupline port plus 3 dig- ital inputs for Gas / water / remote heating metering M-bus port	







Input specifications

Rated inputs Current type	System type: 3-phase Galvanic insulation by means		Exported Total/Partial/
Current type	of built-in CT's (AV5 and AV6		Tariff: 6+1or 7DGT (with "-"
	models). By direct connec-	Overload status	sign) EEEE indication when the
	tion (AV2 and AV9)	Overload status	value being measured is
Current range (by CT)	AV5 and AV6: 1/5(10)A		exceeding the "Continuous
Current range (direct)	AV2: 10(65)A; AV9: 10(65)A		inputs overload" (maximum
Voltage	AV5: 400 VLL		measurement capacity)
	AV2: 230/400 VLL AV9: 400 VLL	Max. and Min. indication	Max. instantaneous vari-
Voltage by VT/PT	AV6: 120VLN/208 VLL		ables: 9999; energies:
			99 999 999. Min. instanta- neous variables: 0.000;
Accuracy (Display + RS485)	lb: see below, Un: see below		energies 0.00.
(@25°C ±5°C, R.H. 60%,		LEDs	_
50±5Hz/60±5Hz) AV5 model	In: 5A, Imax: 10A; Un: 160	LEDS	Red LED (Energy consumption), according to
Availlodel	to 480VLN (277 to 830VLL)		EN50470-3, EN62052-11
AV6 model	In: 5A, Imax: 10A; Un: 40 to	AV5, AV6 models	0.001 kWh/kvarh by pulse if
	144VLN (70 to 250VLL)	·	CT ratio by VT ratio is ≤7;
AV2 model	lb: 10A, lmax: 65A, Un: 113		0.01 kWh/kvarh by pulse if CT
	to 265VLN (196 to 460VLL)		ratio by VT ratio is $> 7.1 \le 70.0$;
AV9 model	lb: 10A, Imax: 65A; Un: 184		0.1 kWh/kvarh pulse if CT ratio
Current	to 276VLN (318 to 480VLL)		by VT ratio is > 70.1 ≤ 700.0; 1 kWh/kvarh by pulse if CT
AV5, AV6 models	From 0.002In to 0.2In:		ratio x VT ratio is > 700.1;
AVS, AVO IIIOGEIS	±(0.5% RDG +3DGT)	AV2, AV9 models	0.001kWh/kvarh by pulse
	From 0.2In to Imax:	Max frequency	16Hz
	±(0.5% RDG +1DGT).	Measurements	See "List of the variables
AV2, AV9 models	From 0.004lb to 0.2lb:		that can be connected to:"
	±(0.5% RDG +3DGT)	Method	TRMS measurements of
	From 0.2lb to Imax:		distorted wave forms.
Phase-neutral voltage	±(0.5% RDG +1DGT). In the range Un: ±(0,5%	Coupling type	Direct for AV2 and AV9
i ilase-lieutiai voitage	RDG +1DGT)		models. By means of exter- nal CT's for AV5 and AV6
Phase-phase voltage	In the range Un: ±(1% RDG	Crest factor	
, ,	+1DGT)	Crest factor	Ib 10A 4 (91A max. peak) In 5A 3 (15A max. peak)
Frequency	±0.1Hz (50±5Hz/60±5Hz)	Current Overloads	more of tortinax, pearly
Active and Apparent power	±(1%RDG +2DGT)	Continuous	1/5(10) A: 10A, @ 50Hz
Power Factor	±[0.001+1%(1.000 - "PF RDG")]	33	10(65) A: 65A, @ 50Hz
Reactive power	±(2%RDG +2DGT)	For 500ms	1/S(10) A: 200A, @ 50Hz
Active energy	Class 1 according to	For 10ms	10(65) A: 1920A max, @ 50Hz
3,	EN62053-21 and MID	Voltage Overloads	
	Annex MI-003 Class B	Continuous	1.2 Un
.	according to EN50470-3	For 500ms	2 Un
Reactive energy	Class 2 according to	Input impedance	4000140
AV5, AV6 models	EN62053-23 In: 5A, Imax: 10A;	208VL-L (AV6)	>1600KΩ
AVS, AVO IIIOGEIS	0.1 In: 0.5A,	230/400VL-L (AV2)	Refer to "Power Consumption"
	Start up current: 10mA	400VL-L (AV5)	>1600ΚΩ
AV2, AV9 models	lb: 10A, Imax: 65A;	400VL-L (AV9)	Refer to "Power
	0.1 lb: 1.0A	• •	Consumption"
- <u></u>	Start up current: 40mA	1/5(10)A (AV5-AV6)	< 0.3VA
Energy additional errors	A	10(65)A (AV2-AV9)	< 4VA
Influence quantities	According to EN62053-21, EN50470-3, EN62053-23	Frequency	50±5Hz/60±5Hz
Temperature drift	≤200ppm/°C	Joystick	For variable selection and
Sampling rate	1600 samples/s @ 50Hz		programming of the instrument working
Sampling rate	1900 samples/s @ 50Hz		parameters
Display refresh time	750 ms		
Display	3 lines (1 x 8 DGT; 2 x 4 DGT)		
Type	LCD, h 7mm		
Instantaneous variables read-out	4 DGT		
Energies	Imported Total 6+2, 7+1 or		
	8DGT		



Output specifications

Digital outputs		Connections	2-wire
Pulse type			Max. distance 1000m
Number of outputs	Up to 2, independent. Programmable from 0.001 to 10.00kWh/kvarh by	Addresses Protocol	247, selectable by means of the front joystick MODBUS/JBUS (RTU)
	pulse.		MODBO2/3BO2 (RTO)
Туре	Outputs connectable to the	Data (bidirectional)	Cyatam and phase
Pulse duration	energy meters (kWh/kvarh) T _{OFF} ≥120ms, according to	Dynamic (reading only)	System and phase variables: see table "List of variables"
r dioc duration	EN62053-31 T _{on} selectable (30 ms or	Static (reading and writing)	All the configuration parameters.
	100 ms), according to EN62053-31	Data format	1 start bit, 8 data bit, no parity,1 stop bit
Alarm type		Baud-rate	4800, 9600 bit/s
Number of outputs Alarm modes	Up to 2, independent Up alarm, down alarm (see	Driver input impedance	1/5 unit load Maximum 160 transceivers
	the table "List of the variables that can be connected to")	Insulation	on the same bus. By means of optocouplers, 4000 VRMS output to
Set-point adjustment	From 0 to 100% of the display scale		measuring input, 4000 VRMS output to
Hysteresis	From 0 to full scale		power supply input.
On-time delay	0 to 255s	M-bus	
Output status	Selectable; normally	Type	One-drop, directional
Min. response time	de-energized or normally energized ≤ 700ms, filter excluded,	Connections	2-wire, max. distance according to EN13757-1
Willi. response time	set-point on-time delay: "0 s"	Addresses	
Note	The 2 digital outputs can also work as a dual pulse	Indirizzo primario	247, selectable by means of the front joystick and via M-
	output, dual alarm output, one pulse output and one		bus (default 0). The primary address can be set to 0 again after begin set to
	alarm output.		another value only via M-
Static output			bus.
Purpose	For pulse output or alarm output	Secondary address	Predefined, univocally present during manufacturing
Signal Insulation	V _{ON} 1.2 VDC/ max. 100 mA V _{OFF} 30 VDC max. By means of optocuplers,	Protocol Available data and frame format	M-bus according to EN13757-1 See table "M-bus available
modiation	4000 VRMS output to measuring inputs,	Baud-rate	variables and frame format" 300, 2400 (default), 9600
	4000 VRMS output to power supply input.		bits/s
	power supply input.	Baud-rate selection	Set during programming or
Relay output Purpose	For alarm output or pulse output	Driver input capability	set directly by the M-bus master 1 unit load
Туре	Relay, SPST type	Special functions	None
.,,,,,	AC 1-5A @ 250VAC DC 12-5A @ 24VDC	Insulation	By means of optocouplers, 4000 VRMS output to measuring input
	AC 15-1.5A @ 250VAC DC 13-1.5A @ 24VDC	Nata (fam DOACE	measuring input
Insulation	4000 VRMS output to	Note (for RS485 and	
Insulation	measuring input 4000 VRMS output to	M-bus ports)	The meters equipped with the communication port ("AV9" models with "M1"
Note	power supply input. The meters equipped with the relay outputs ("AV9"		and "IS" options) work even if VL3 is missing (VL1, VL2
	models with "R2" option) work even if VL3 is missing		and neutral have to be available)(see table "work- ing mode notes")
	(VL1, VL2 and neutral have to be available)(see table		ing mode notes)
B0 105	"working mode notes")		
RS485	Multiplyon bigling the selection of		
Туре	Multidrop, bidirectional (static and dynamic variables)		



Dupline specifications

Counters			M1 to N8 (4th group of 16
Used Dupline function	Multiplexer for counter val-		variables)
•	ues		O1 to P8 (5th group of 16 vari-
Number of counters	6 per instrument,		ables)
	128 per network	Available variables	All, except for the "max"
Counter range	0 99 999 999	/ Wallabio Valiabios	variables
Used channels	B to F	O 1 /T ://: 1	variables
Multiplexer	B2 to B8	Synchro/Tariff input	
Reset	B1	Used Dupline functions	Monostable (push-button)
Value	C1 to F8		Realtime
Counter reset	Enable/disable function for	Used channels	A5
Counterreset	all the counters	Working mode	Selectable:
Available counters			• none
Available counters	kWh tot, -kWh tot,		 Wdmd synchronization
	kvarh tot, -kvarh tot,		 total and partial energy
	kWh t1, kWh t2,		meter (kWh, kvarh) managed
	kWh L1, kWh L2, kWh L3,		by time periods (t1-t2).
	counter dig. in. 1,	Alarms	
	counter dig. in. 2,	Used Dupline function	Monostable (push-button)
	counter dig. in. 3,	Used channells	Selectable (A1 to P8). No
	hour counter.	Osed Chamiens	control that the selected
Analogue variables			channels are not used for
Used Dupline function	Multiplexer for analogue		
'	values		counters or analog variables.
Number of variables	8 per instrument	Number of alarms	
	80 per network	Alarm modes	2 per instrument Up alarm, down alarm (see
Dupline data format	3 1/2 DGT BCD	Alami modes	the table "List of the
Full scale value	Selectable from 1.999 to		variables that can be
Full Scale value	1999M		connected to")
Used channels	depending on the number	Set-point adjustment	From 0 to 100% of the dis-
OSCA CHAINICIS	of variables	Get-point adjustifient	play scale
Multiplexer	A1 to A4	Hysteresis	From 0 to full scale
Value	G1 to H8 (1st group of 16	On-time delay	0 to 255s
value	variables)		
	I1 to J8 (2 nd group of 16	Output status Available variables	Normally energised
		Available variables	All, except for the "max"
	variables)		variables
	K1 to L8 (3 th group of 16		
	variables)		

Digital input specifications

Number of inputs Input frequency Prescaler adjustment

Contact measuring voltage Contact measuring current Input impedance Contact resistance

Working modes (DP version excluded)

3 20Hz max, duty cycle 50% From 0.001 to 999.9 m³ or kWh per pulse 5VDC +/- 5% 10mA max 680Ω ≤100 Ω , closed contact ≥500k Ω , open contact

Selectable:

total and partial energy meters (kWh and kvarh) without digital inputs;
total and partial energy meters (kWh and kvarh) managed by time periods

(t1-t2-t3-t4), W dmd synchronisation (the synchronisation is made every time the tariff changes) and GAS (m³) or WATER (hotcold m³) or remote heating (kWh) meters or external kWh meter; • total and partial energy

• total and partial energy meters (kWh and kvarh) managed by time periods (t1-t2), W dmd synchronisation (the synchronisation is made independently from the tariff selection) and GAS (m³) or WATER (hot-cold m³) or remote heating (kWh) meters or external kWh meter;

• total energy (kWh, kvarh) and GAS, WATER (hot-cold



Digital input specifications (cont.)

only).

Working modes (DP version only)

Note

m³), remote heating, external kWh meters (3 choices

Selectable:
• GAS (m³) or WATER (hotcold m³) or remote heating (kWh) meters

The energy metering is

Insulation

only made by means of the analogue inputs. By means of optocouplers, 4000 VRMS digital inputs to measuring inputs, 4000 VRMS digital inputs to power supply input.

Software functions

Password	Numeric code of max. 4 digits; 2 protection levels	Filter Operating range	0 to 100% of the input dis-
1st level 2nd level	of the programming data: Password "0", no protection Password from 1 to 9999, all data are protected	Filtering coefficient Filter action	play scale 1 to 32 Measurements, serial output (fundamental variables: V, A, W and their derived ones).
System selection System 3-P.n unbalanced load System 3-P unbalanced load System 3-P.1 (only AV5 and AV6) balanced load	3-phase (4-wire) 3-phase (3-wire) 3-phase (3-wire) one current and 3-phase to phase	Displaying	Up to 3 variables per page (see « Display pages ») 8 different set of variables available (see « Display pages ») according to the application being selected
System 2-P System 1-P Transformer ratio	voltage measurements 3-phase (4-wire) one current and 1-phase (L1) to neutral voltage measurement 2-phase (3-wire) 1-phase (2-wire)	Reset	By means of the front joystick: - dmd and dmd max; - total energies (kWh and kvarh) and gas/water; - partial energies and tariffs: kWh, kvarh
CT	1.0 to 999.9 / 1000 to 6000 (only AV5 and AV6) 1.0 to 999.9 / 1000 to 9999 / 10.00k to 60.00k (only AV5 and AV6). The maximum VT by CT ratio is 3150 for AV5_PF models, 4629 for AV5_X models. Note 1: for MID complaint applications the maximum power being measured is 25 MW for AV5_PF and AV2_PF models. Note 2: for non-MID complaint applications the maximum power (calculated as maximum input voltage and current) being measured cannot exceed 66 MW for AV5_X models, 62 MW for AV6_X models, 51 kW for AV6_X models and 54 kW for AV9_X models.	Easy connection function AV2 and AV9 models AV5-AV6-AV2-AV9 models	Automatic phase sequence detection with current and voltage synchronisation. For all the display selections, both energy and power measurements are independent from the current direction. The displayed energy is always "imported" with the only exception of "F" and "H" types (see "display pages" table). For those latter selections the energies can be either "imported" or "exported" depending on the current direction.



General specifications

Operating temperature	-25°C to +55°C (-13°F to 131°F) (R.H. from 0 to 90% non-condensing @ 40°C)	Radio frequency suppression	supply input: 1kV According to CISPR 22
	according to EN62053-21, EN50470-1 and EN62053- 23	Standard compliance Safety	IEC60664, IEC61010-1 EN60664, EN61010-1
Storage temperature	-30°C to +70°C (-22°F to 158°F) (R.H. < 90% non-condensing @ 40°C) according to EN62053-21, EN50470-1 and EN62053-23	Metrology Pulse output Approvals	EN62052-11. EN62053-23, EN50470-3. MID "annex MI-003" DIN43864, IEC62053-31 CE, cULus listed (AV5, AV6 options only), MID (PF option only)
Installation category	Cat. III (IEC60664, EN60664)	Connections	Screw-type
Insulation (for 1 minute)	4000 VRMS between measuring inputs and power supply 4000 VRMS between power supply and RS485/digital output	Cable cross-section area AV2-AV9 models	measuring inputs max. 16 mm²; min. 2.5 mm² (by cable lug). Min./Max. screws tightening torque: 1.7 Nm / 3 Nm
Dielectric strength	4000 VRMS for 1 minute		Other inputs: 1.5 mm ²
Noise rejection CMRR	100 dB, 48 to 62 Hz		Screws tightening torque: 0.5 Nm
EMC Electrostatic discharges Immunity to irradiated	According to EN62052-11 15kV air discharge Test with current: 10V/m from 80 to 2000MHz	Cable cross-section area AV5-AV6 models	Max. 1.5 mm ² Screws tightening torque: 0.5 Nm
Electromagnetic fields Burst	Test without any current: 30V/m from 80 to 2000MHz On current and voltage measuring inputs circuit:	Housing DIN Dimensions (WxHxD) Material	71 x 90 x 64.5 mm Nylon PA66, self-extinguishing: UL 94 V-0
Immunity to conducted disturbances	4kV 10V/m from 150KHz to 80MHz	Mounting Protection degree Front	DIN-rail
Surge	On current and voltage measuring inputs circuit: 4kV; on "L" auxiliary power	Screw terminals Weight	Approx. 400 g (packing included)

Power supply specifications


Self supplied version	AV9 models "XX" and "O2" options only: -20% +15%, 48- 62Hz. "R2", "M1" and "IS" options only: -15% +10%, 48-62Hz. AV2 model: "XX", "O2", "IS" and "DP" options: -15% +15%, 48- 62Hz. In case of 3-phase system, 4-wire connection: 113 to 265V. In case of 3- phase system, 3-wire connection: 196 to 460V.	Auxiliary power supply	phase connection has to be performed the L1 and L2 voltage inputs have to be short circuited. The instrument provided with "O2" option, working in a 3-phase system with neutral may work also if one or two phases are missing. AV5-AV6 modules: L: 18 to 60VAC/DC; D: 115VAC/230VAC (-/+15%) from 48 to 62Hz
Note	The instruments provided with "IS" and "R2" options work only if all the voltage inputs are connected (3-phase and neutral) if a 1-	Power consumption AV9-AV2 models AV9-AV2 models (IS and DP option only) AV5-AV6 models	≤ 20VA/1W ≤ 12VA/2W ≤ 2VA/2W





Working mode notes (only "Self power supply" version)


Output	Model	Note				
Open collector output	"AV9" models with "O2" option	The meter works even if up to two voltages "phase to neutral" are missing or if one voltage "phase to phase" is missing.				
Relay output	"AV9" models with "R2" option	The neutral wire has always to be available. The meter works even if "Phase 3" is missing but,				
RS485 and M-bus ports	"AV9" models with "IS" and "M1" options	mandatorily, both "phase 1" and "Phase 2" have to be available.				
Dupline port	"AV2" model with "DP" option	The meter works even if up to two voltages "phase				
Relay output	"AV2" model with "R2" option	to neutral" are missing or if one voltage "phase to				
RS485 and M-bus ports	"AV2" model with "IS" and "M1" options	phase" is missing.				

Accuracy (According to EN50470-3 and EN62053-23)











MID "Annex MI-003" compliance (PF option only)

Accuracy	$0.9 \text{ Un} \le U \le 1.1 \text{ Un};$ $0.98 \text{ fn} \le f \le 1.02 \text{ fn};$ fn: 50Hz;	EMC compliance Mechanical compliance	E2 M2				
AV2-AV9 models	fn: 50Hz; cosφ: 0.5 inductive to 0.8 capacitive. Class B. I st: 0.04A; I min:	Protection degree	in order to achieve the protection against dust and water required by the				
AV5 models	0.5A; I tr: 1A; I ref: 10A; I max: 65A. Class B. I st: 0.01A; I min: 0.05A; I tr: 0.25A; I ref: 5A; I max: 10A.		norms harmonized to MID, the meter must be used only installed in IP51 (or better) cabinets.				
Operating temperature	-25°C to +55°C (-13°F to 131°F) (R.H. from 0 to 90% non-condensing @ 40°C)						

Used calculation formulas

Phase variables

Instantaneous effective voltage

$$V_{1N} = \sqrt{\frac{1}{n} \cdot \sum_{1}^{n} (V_{1N})_{i}^{2}}$$

Instantaneous active power

$$W_1 = \frac{1}{n} \cdot \sum_{i=1}^{n} (V_{1N})_i \cdot (A_1)_i$$

Instantaneous power factor

$$\cos \varphi_1 = \frac{W_1}{VA_1}$$

Instantaneous effective current

$$A_1 = \sqrt{\frac{1}{n} \cdot \sum_{1}^{n} \left(A_1\right)_i^2}$$

Instantaneous apparent power

$$VA_1 = V_{1N} \cdot A_1$$

Instantaneous reactive power

$$var_1 = \sqrt{(VA_1)^2 - (W_1)^2}$$

System variables

Equivalent three-phase voltage $V_{\Sigma} = \frac{V_1 + V_2 + V_3}{3} \cdot \sqrt{3}$

$$V_{\Sigma} = \frac{V_1 + V_2 + V_3}{3} \cdot \sqrt{3}$$

$$ASY_{LL} = \frac{(V_{LL \max} - V_{LL \min})}{V_{LL} \Sigma}$$

Voltage asymmetry
$$ASY_{LL} = \frac{(V_{LL \text{ max}} - V_{LL \text{ min}})}{V_{LL} \Sigma}$$

$$ASY_{LN} = \frac{(V_{LN \text{ max}} - V_{LN \text{ min}})}{V_{LN} \Sigma}$$

Three-phase reactive power

$$var_{\Sigma} = (var_1 + var_2 + var_3)$$

Three-phase active power

$$W_{\Sigma} = W_1 + W_2 + W_3$$

Three-phase apparent power

$$VA_{\Sigma} = \sqrt{W_{\Sigma}^2 + \text{var}_{\Sigma}^2}$$

Three-phase power factor

(TPF)

$$\cos \varphi_{\Sigma} = \frac{W_{\Sigma}}{VA_{\Sigma}}$$

Energy metering

$$k \operatorname{var} hi = \int_{t_1}^{t_2} Qi(t) dt \cong \Delta t \sum_{t_1}^{t_2} Qt$$

$$kWhi = \int_{t_1}^{t_2} Pi(t) dt \cong \Delta t \sum_{t_1}^{n_2} Pnj$$

Where:

i= considered phase (L1, L2 or L3) P= active power; Q= reactive power; t_1 , t_2 =starting and ending time points of consumption recording; n= time unit; Δt = time interval between two successive power consumptions; n_1 , n_2 = starting and ending discrete time points of consumption recording



List of the variables that can be connected to:

- RS485 and M-bus communication port
- Alarm outputs ("max" variable", "energies" and "hour counter" excluded)
- Pulse outputs (imported and exported kWh, imported kvarh)
- Dupline bus

No	Variable	1-phase system	2-phase system	3-ph. 4-wire balanced sys.	3-ph. 4-wire unbal. sys.	3 ph. 3-wire bal. sys.	3 ph. 3-wire unbal. sys.	Notes
1	V L-N sys	0	X	Х	Х	Х	#	sys=system
2	V L1	Х	Х	Х	х	Х	#	
3	V L2	0	X	Х	х	X	#	
4	V L3	0	0	Х	Х	X	#	
5	V L-L sys	0	X	Х	Х	X	Х	sys=system
6	V L1-2	#	Х	Х	Х	X	Х	
7	V L2-3	#	0	Х	х	X	Х	
8	V L3-1	#	0	Х	Х	Х	Х	
9	A dmd max	0	X	Х	х	Х	Х	Highest "dmd" current among the phases (1)(2)
10	A L1	Х	X	Х	Х	X	Х	
11	A L2	0	X	Х	Х	X	Х	
12	A L3	0	0	Х	Х	X	Х	
13	VA sys	Х	X	Х	Х	X	Х	sys=system
14	VA sys dmd	Х	X	Х	Х	X	Х	sys=system (1)
15	VA L1	Х	X	Х	Х	X	#	
16	VA L2	0	X	Х	Х	X	#	
17	VA L3	0	0	Х	Х	X	#	
18	var sys	Х	X	Х	Х	X	#	sys=system
19	var L1	Х	X	Х	х	X	#	
20	var L2	0	X	Х	х	X	#	
21	var L3	0	0	Х	х	X	#	
22	W sys	Х	X	Х	х	X	Х	sys=system
23	W sys dmd	х	X	X	Х	X	Х	sys=system (1)
24	W L1	х	X	X	Х	X	#	
25	W L2	0	X	Х	х	X	#	
26	W L3	0	0	Х	Х	X	#	
27	PF sys	Х	X	Х	х	X	Х	
28	PF L1	Х	X	Х	х	X	#	
29	PF L2	0	X	Х	х	X	#	
30	PF L3	0	0	Х	Х	X	#	
31	Hz	х	X	X	Х	X	Х	
32	Phase seq.	0	X	Х	х	X	х	
33	Hours	Х	X	Х	х	X	х	
34	kWh (+)	х	X	Х	х	X	х	Total or by user
35	kvarh (+)	Х	Х	Х	х	X	#	Total or by user
36	kWh (+)	Х	X	Х	х	X	Х	Partial or by tariff
37	kvarh (+)	х	Х	Х	х	Х	#	Partial or by tariff
38	kWh (-)	х	Х	Х	х	X	Х	Total
39	kvarh (-)	Х	Х	Х	х	Х	#	Total
40	m³ Gas	Х	Х	Х	х	Х	Х	Total (3)
41	m³ Cold H₂O	Х	Х	Х	х	Х	Х	Total (3)
42	m³ Hot H₂O	Х	Х	Х	х	Х	Х	Total (3)
43	kWh H₂O	Х	Х	х	х	Х	Х	Total (3)
44	kWh out	Х	Х	Х	х	Х	х	Total (3)

- (x) = available
- (o) = not available (zero indication on the display)
- (#) = not available (the relevant page is not displayed)
- (1) = max. value with data storage
- (2) = not available with the "DP" option
- (3) = not available via M-bus communication



Display pages

Sel.	No	1st variable (1st	2nd variable (2nd	3rd variable (3rd	Note		Applications							
pos.	NO	line)	line)	line)	Note	Α	В	С	D	Е	F	G	Н	ı
	1	Phase seq.	VLN sys	Hz		7	7	7		7	7	7	7	<u> </u>
	2	Phase seq.	VLL sys	Hz							Х	Х	Х	<u> </u>
	3	Total kWh (+)	W sys dmd	W sys dmd max		Х	Х	Х		Χ	Х	Х	Х	<u> </u>
	4	kWh (+)	A dmd max	(text) "PArt"	"PArt" = Partial kWh (+)						Х	Х	Χ	
	5	Total kvarh (+)	VA sys dmd	VA sys dmd max			7				7	7	7	
	6	kvarh (+)	VA sys	(text) "PArt"	"PArt" = Partial kvarh (+)						7	7	7	
	7	Totalizer 1 (2)	W sys (8)	(text) (3)	(1)			Х			Х	Х	Х	
	8	Totalizer 2 (2)	W sys (8)	(text) (3)	(1)			Х			Х	Х	Χ	
	9	Totalizer 3 (2)	W sys (8)	(text) (3)	(1)			Х			Х	Х	Х	
	10	kWh (+)	t1 tariff (4)	W sys dmd	(1) digital input enabled			Х			Х	Х	Х	
	11	kWh (+)	t2 tariff (4)	W sys dmd	(1) digital input enabled			Х			Х	Х	Χ	
	12	kWh (+)	t3 tariff (4)	W sys dmd	(1) digital input enabled			5			5	5	5	
	13	kWh (+)	t4 tariff (4)	W sys dmd	(1) digital input enebled			5			5	5	5	
	14	kvarh (+)	t1 tariff (4)	W sys dmd	(1) digital input enabled			7			7	7	7	
	15	kvarh (+)	t2 tariff (4)	W sys dmd	(1) digital input enabled			7			7	7	7	
	16	kvarh (+)	t3 tariff (4)	W sys dmd	(1) digital input enabled			5,7			5,7	5,7	5,7	
	17	kvarh (+)	t4 tariff (4)	W sys dmd	(1) digital input enabled			5,7			5,7	5,7	5,7	
	18	kWh (+) X	WX	User X	(1) specific function enabled				Х					
	19	kWh (+) Y	WY	User Y	(1) specific function enabled				Х					
	20	kWh (+) Z	W Z	User Z	(1) specific function enabled				Х					
	21	Total kvarh (-)	VA sys dmd	VA sys dmd max							7		7	
	22	Total kWh (-)	W sys dmd	W sys dmd max						Х	Х		Χ	
	23	Hours	W sys	PF sys						Х	Х	Х	Χ	
	24	Hours	var sys	PF sys						7	7	7	7	
	25	var L1	var L2	var L3								7	7	
	26	VA L1	VA L2	VA L3								7	7	
	27	PF L1	PF L2	PF L3								7	7	
	28	W L1	W L2	W L3						7		7	7	
	29	AL1	A L2	AL3				Х		Х		Х	Х	х
	30	V L1-2	V L2-3	V L3-1				6				6	6	
	31	V L1	V L2	V L3			7		7	7		7	7	7
	32	Total kWh (+)	W sys											х
0	Sele	ctor position which c	an be linked to any o	f the variable combin	ations listed above (No. from 1	to 31	i)							
1	Selector position which can be linked to any of the variable combinations listed above (No. from 1 to 31)													

- 1 Selector position which can be linked to any of the variable combinations listed above (No. from 1 to 31)
- 2 Selector position which can be linked to any of the variable combinations listed above (No. from 1 to 31)
- Selector position which can be linked to any of the variable combinations listed above (No. from 1 to 31) In this position the front LED blinks proportionally to the reactive energy (kvarh) being measured
- (1) The page is available according to the enabled measurement.
- (2) m³ Gas, m³ Water, kWh remote heating, external kWh meter. Not available in M-bus version.
- (3) Hot and Cold (water), GAS. ENE (external energy meter). Not available in M-bus version.
- (4) The active tariff is displayed with an "A" before the "t1-t2-t3-t4" symbols. Not available in M-bus version.
- (5) These pages are not available in case of Dupline model.
- (6) Pages not available in case of 1-phase system (1P selection).
- (7) Pages not available in case of 3-phase unbalanced system (3P selection).
- (8) In case of external kWh meter the text "W sys" is replaced by "out".

Note: in case of alarm the whole display blinks. The blinking stops when either the selector or the joystick are used. The display starts to blink again after 60 seconds of the last command being used. There is a time-out of 60s that brings the scrolled page to the default one (selectable according to the table given above).



Additional available information on the display

Туре	1st line	2nd line	3rd line
Meter information	Firmware revision	YEAr (text)	Year of production
Meter information	PuLSE (text)	LEd (text)	Numb. of kWh per pulse
Meter information	System (1-2-3-phase)	Connection (2-3-4-wire)	dmd (time)
Meter information (AV5-6)	Ct rAtio (text)	1.0 60.0k	
Meter information (AV5-6)	UT rAtio (text)	1.06.0k	
In case of communication port (Modbus or M-bus)	SEriAL (text)	Address number	RS485 status (RX-TX)
In case of communication port (Modbus or M-bus)	Secondary address (for M-bus protocol)		Sn
In case of Dupline port	Dupline (text) or EM24 (text)	OK err	
In case of alarm output 1	AL1 oFF/on (text) Alarm ststus	Set-point value	Alarm type
In case of alarm output 2	AL2 oFF/on (text) Alarm ststus	Set-point value	Alarm type
In case of pulse output 1	PuLSE 1 (text) (variable link kWh/kvarh)	Output pulse weight (kWh-kvarh / pulse)	
In case of pulse output 2	PuLSE 2 (text) (variable link kWh/kvarh)	Output pulse weight (kWh-kvarh / pulse)	

List of selectable applications

	Description	Notes
Α	Basic domestic **	Mainly energy metering
В	Shopping centres **	Mainly energy metering
С	Advanced domestic **	Mainly energy metering (total and based on tariff), gas and water metering
D	Multi domestic (also camping and marinas) * /**	Mainly energy metering (3 by single phase)
Е	Solar *	Energy meter with some basic power analyzer functions
F	Industrial *	Mainly energy metering
G	Advanced industrial **	Energy metering and power analysis
Н	Advanced industrial for power generation *	Complete energy metering and power analysis
I	Basic for metering systems **	Mainly energy metering

Notes: * Not available with option PF A. ** Not available with option PF B

Insulation between inputs and outputs

	Measuring Inputs	Relay outputs	Open collector out- puts	Comm. port and digi- tal inputs	Dupline	Self power supply	Auxiliary power supply
Measuring Inputs	-	4kV	4kV	4kV	4kV	0kV	4kV
Relay outputs	4kV	-	-	-	-	4kV	4kV
Open collector outputs	4kV	-	-	-	-	4kV	4kV
Comm. port and digital inputs	4kV	-	-	-	-	4kV	4kV
Dupline	4kV	-	-	-	=	4kV	4kV
Self power supply	0kV	4kV	4kV	4kV	4kV	-	-
Aux. power supply	4kV	4kV	4kV	4kV	4kV	-	-

NOTE: all the models with auxiliary power supply have, mandatorily, to be connected to external current transformers because the isolation among the current inputs is just functional (100VAC).



Tamper proof accessory kit



The "tamper proof" kit (two screw protection covers) is included.

The instrument (PF option) is sealed in one point:

- Front selector (to lock the instrument programming).

After installation it must be sealed in other two points:

- Upper cover;
- Lower cover.




M-bus available variables and frame format


• According to the selected system, the available variables (see above table) are transmitted via M-bus according to the following frames.


Frame	Number	Variable	Data Format	Frame	Number	Variable	Data Format
1	1	kWh (+) TOT	INT32	1	8	VAsys	INT32
1	2	kvarh (+) TOT	INT32	1	9	PFsys	INT16
1	3	kWh (+) L1	INT32	1	10	VLLsys	INT32
1	4	kWh (+) L2	INT32	1	11	VLNsys	INT32
1	5	kWh (+) L3	INT32	1	12	AL1	INT32
1	6	W sys	INT32	1	13	AL2	INT32
1	7	var sys	INT32	1	14	AL3	INT32
Frame	Number	Variable	Data Format	Frame	Number	Variable	Data Format
2	1	WL1	INT32	2	8	VAL2	INT32
2	2	WL2	INT32	2	9	VAL3	INT32
2	3	WL3	INT32	2	10	PFL1	INT16
2	4	varL1	INT32	2	11	PFL2	INT16
2	5	varL2	INT32	2	12	PFL3	INT16
2	6	varL3	INT32	2	13		
2	7	VAL1	INT32	2	14		
Frame	Number	Variable	Data Format	Frame	Number	Variable	Data Format
3	1	V12	INT32	3	8	kvarh (+) PAR	INT32
3	2	V23	INT32	3	9	kWh (-) TOT	INT32
3	3	V31	INT32	3	10	kvarh (-) TOT	INT32
3	4	VL1-N	INT32	3	11	Hourmeter	INT32
3	5	VL2-N	INT32	3	12	Hz	INT16
3	6	VL3-N	INT32	3	13		
3	7	kWh (+) PAR	INT32	3	14		
_	Number	Variable	Data Format	Frame	Number	Variable	Data Format
Frame							
Frame 4	1	DMD W sys	INT32	4	8		
		DMD W sys DMD W sys max	INT32 INT32	4	9		
4	1	DMD W sys max DMD VA sys					
4	1 2	DMD W sys max	INT32	4	9		
4 4 4	1 2 3	DMD W sys max DMD VA sys	INT32 INT32	4	9		
4 4 4 4	1 2 3 4	DMD W sys max DMD VA sys DMD VA sys max	INT32 INT32 INT32	4 4 4	9 10 11		




Wiring diagrams









(65A) System type selection: 2P





(65A) System type selection: 1P






(10A) System type selection: 3P.n












Wiring diagrams


(10A) System type selection: 3P.n










(10A) System type selection: 3P.1









(10A) System type selection: 2P






(10A) System type selection: 1P







Wiring diagrams


(10A) System type selection: 1P










Power supply wiring diagrams (auxiliary power supply)









Open collector and relay outputs wiring diagrams










The load resistances (RC) must be designed so that the close contact current is lower than 100mA; the VDC voltage must be lower than or equal to 30VDC.




Digital inputs, RS485 and Dupline ports wiring diagrams











M-bus wiring connection





Front panel description



1. Joystick

To program the configuration parameters and scroll the variables on the display.

Red LED blinking proportional to the energy being measured.

3. Display

- LCD-type with alphanumeric indications to:
- display configuration parameters;
- display all the measured variables.

4. Selector

To select the desired display pages and to lock the programming. **5. Connections**

Screw terminal blocks for instrument wiring.

Dimensions

