SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER	:	
DESCRIPTION	:	EC AXIAL FAN
DIMENSION	•	120X120X38mm
SUNON MODEL	:	CF4113MBL-1000U-S99
SUNON SEQ NO	•	E12002740G-00
REV	:	0
ISSUE DATE		2022.03.15
APPROVED BY CUSTOMER	:	

APPROVED BY Addy CHECKED BY Cindy DESIGNED BY Angela	APPROVED BY	Addy	CHECKED BY	Cindy	DESIGNED BY	Angela

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD

NO.30, LN. 296, XINYA RD., QIANZHEN DIST., KAOHSIUNG CITY 806, TAIWAN TEL: 886–7–8135888 FAX: 886–7–8230505

建準電機 SUNONWEALTH Page 1 of 19



HISTORY

REV	DESCRIPTION	DATE	APPROVED
0	DRAFT	2022.03.15	



建 準 電 機 SUNONWEALTH Page 2 of 19

TABLE OF CONTENTS

-		_
١.	SCOPE	5
2.	CHARACTERISTICS	5
3.	MECHANICAL	6
	3.1 BEARING SYSTEM	
	3.2 MATERIALS OF FRAME	6
	3.3 MATERIALS OF FAN BLADE	6
	3.4 IMPELLER BALANCE GRADE	6
	3.5 WEIGHT	6
4.	ENVIRONMENTAL	6
		-
	4.1 OPERATING TEMPERATURE RANGE	
	4.2 STORAGE TEMPERATURE RANGE	
	4.3 OPERATING HUMIDITY RANGE	
	4.4 STORAGE HUMIDITY RANGE	
5.	PROTECTION	6
6.	AIR FLOW & STATIC PRESSURE CURVE	7
7.	DIMENSIONS	8
8.	LABEL	9
9.	LEAD WIRE CONNECTION1	0
10	. SPEED CONTROL1	1
11	. SPEED & PWM CONTROL SIGNAL1	2



I. OTHER SPECIFIED TESTING	.13
1 DROP PROOF TEST	13
2 HUMIDITY PROOF TEST	13
3 VIBRATION PROOF TEST	13
4 THERMAL CYCLING TEST	13
5 SHOCK PROOF TEST	13
6 LIFE EXPECTANCY	
II. CHARACTERISTIC DEFINITION14-	-15
1 INPUT POWER	14
2 RATED CURRENT	14
3 RATED SPEED	14
4 STARTING VOLTAGE	14
5 LOCKED ROTOR CURRENT	.14
6 AIR FLOW AND STATIC PRESSURE	.14
7 INSULATION RESISTANCE	15
8 DIELECTRIC STRENGTH	15
III. NOTE	-18
1 SAFETY	16
2 SPECIFICATION MODIFICATION16	-17
3 OTHER	-18
IV. WARRANTY	.18
I. DECLARATION OF ROHS	.19



1. SCOPE

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE EC AXIAL FAN.

2. CHARACTERISTICS

ITEM	DESCRIPTION				
RATED VOLTAGE	100–240 VAC				
FREQUENCY	50/60 Hz				
RATED CURRENT	0.08 A @ 100 VAC	0.045 A @ 240 VAC			
RATED POWER	3.6 W				
TOLERANCE	± 20% ON RATED POWER	AND CURRENT			
RATED SPEED	3100 RPM \pm 10% IN FREE AIR AT RATED VOLTAGE				
MAX. AIRFLOW AT ZERO STATIC PRESSURE	NOMINAL 90.1 / MIN.77.9 CFM NOMINAL 153 / MIN.132 m³/h				
MAX. STATIC PRESSURE AT ZERO AIRFLOW	NOMINAL 0.31 / MIN.0.25 inch-H2O NOMINAL 77 / MIN.62 Pa				
ACOUSTIC NOISE	NOMINAL 40.2 dB(A) / MAX.44 dB(A) NOTED: 1. FOLLOW ISO 3745:2003. 2. MICROPHONE DISTANCE: 1 METER.				
INSULATION CLASS	F				
INGRESS PROTECTION	NONE				
LIFE EXPECTANCY	70,000 HOURS AT 40 °C WITH 15~65% RH.				
DIRECTION OF ROTATION	COUNTER-CLOCKWISE FROM BLADE SIDE				



3. MECHANICAL

- 3.1 BEARING SYSTEM
- 3.2 MATERIALS OF FRAME
- 3.3 MATERIALS OF FAN BLADE
- 3.4 IMPELLER BALANCE GRADE
- 3.5 WEIGHT

4. ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE
- 4.2 STORAGE TEMPERATURE RANGE
- 4.3 OPERATING HUMIDITY RANGE
- 4.4 STORAGE HUMIDITY RANGE


- : BALL BEARING SYSTEM
- : THERMOPLASTIC PBT OF UL 94V-0
- : THERMOPLASTIC PPS OF UL 94V-0
- : G6.3 PER ISO 1940-1:2003(E)
- : 265 GRAMS
- : -25 TO + 70 DEGREE C
- : -40 TO + 80 DEGREE C
- : 5 TO 90% RH
- : 5 TO 95% RH

5. PROTECTION

- ☑ AUTOMATIC RESTART
- ☑ SOFT START
- □ OVER TEMPERATURE PROTECTION
- ☑ OVER LOAD PROTECTION
- OVER VOLTAGE PROTECTION
- ☑ LOCKED ROTOR PROTECTION



6. AIR FLOW & STATIC PRESSURE CURVE



NOTE: The airflow and static press are measured with SUNON's specific fixture.




建準電機 SUNONWEALTH Page 7 of 19

7. DIMENSIONS

SCREW TYPE						
(PAN HEAD)	TORQUE	SIZE	STANDARD			
MACHINE SCREW	3∼4 kgf–cm	M4.0	JIS B1111-1974			

NOTE: Above spec is available for customization.




ITEM FUNCTIONS		WIRE TYPE	COLOR	
AC CABLE	L	L UL3266#24AWG		
AC CADLE	Ν	UL3266#24AWG	GRAY	
	ISO_GND	UL1007#24AWG	BLACK	
DC CABLE	FG	UL1007#24AWG	YELLOW	
	PWM	UL1007#24AWG	BLUE	

UNIT:mm



建準電機 SUNONWEALTH Page 8 of 19






建準電機 SUNONWEALTH Page 9 of 19


CUSTOMER CIRCUIT

FAN





建準電機 SUNONWEALTH Page 10 of 19



PWM Input								
Parameter	Min.	Тур.	Max.	Unit				
High Level Input Voltage	2.3	5	5.5	V				
Low Level Input Voltage	0	_	0.5	V				
Input Frequency	10	25	50	KHz				
Input Period	2	_	0.05	mS				
Duty Cycle(1)	10	_	100	%				
Start Duty	8	_	10	%				
Max Speed Duty	90	95	100	%				
Sink Current	-	-	0.5	mA				
FREQUENCY G	ENERATO	र						
FG SINK CURRENT(I _{SINK_FG})	0.1	_	5	mA				
OUTPUT PULL HIGH VOLTAGE	3.3	12	14	V				
PULL HIGH RESISTOR(RL)	2.8	10	_	kΩ				
OUTPUT LOW LEVEL VOLTAGE	_	_	0.5	V				
	「「「」」「「」」」 「「」」 「」」 「」」 「」」 「」」 「」」 「」」							

崖 凖 黽 懱 SUNONWEALTH Page 11 of 19


晋

11. SPEED & PWM CONTROL SIGNAL

PWM Duty v.s. Speed curve @ Vcc= rated volt.

PWM Frequency: 25KHZ

PWM Duty(%)	0%	10%	20%	30%	40%	50%	60%	70%	80%	90%	95%	100%
Speed (rpm)	0	290	700	1130	1520	1860	2160	2440	2700	2950	3060	3100



NOTE: It is tested under free air condition. The same spec is not able to apply in static pressure condition



I. OTHER SPECIFIED TESTING

The following is a general description of certain tests that are performed on representative SUNON fans. Nothing in this document is intended to suggest that these tests are performed on every model of SUNON fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this section, SUNON can provide such an explanation upon request.

1. DROP PROOF TEST

Fans are packaged in a standard size shipping box and are dropped to the ground from certain heights and angles depending on the weight of the particular box.

2. HUMIDITY PROOF TEST

The fan is operated for 96 continuous hours in an environment with humidity of 90% to 95% RH at 60°C \pm 2°C.

3. VIBRATION PROOF TEST

Vibration with an amplitude 2mm and a frequency of 5-55-5hz is applied in all 3 directions (X,Y,Z), in cycles of 1 hour each, for a total vibration time of 3hours.

4. THERMAL CYCLING TEST

The fan is operated in a testing chamber for 50 cycles. In each cycle, the temperature is gradually increased from -25° C to 70° C for 90 minutes, and subsequently operated at 70° C for 120 minutes. The temperature is then gradually decreased from 70° C to -25° C for 90 minutes, and subsequently operated at -25° C for 120 minutes.

5. SHOCK PROOF TEST

100G of force is applied in the 3 directions (X,Y, and Z) for 2 milliseconds each.

6. LIFE EXPECTANCY

The "Life Expectancy" of SUNON fans is determined in SUNON's reliability test laboratory by using temperature chambers. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.



建準電機 SUNONWEALTH Page 13 of 19

II. CHARACTERISTIC DEFINITION

The following is a general description of certain tests that are performed on representative SUNON fans in order to determine the specifications of the fan. Nothing in this document is intended to suggest that these tests are performed on every model of SUNON fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this section, SUNON can provide such an explanation upon request.

1. INPUT POWER

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

2. RATED CURRENT

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

3. RATED SPEED

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

4. STARTING VOLTAGE

Measured the voltage which enables to start the fan in the clean air (static pressure = 0) by switching on at the voltage under shaft horizontal condition. It is not at continuously increasing voltage adjustment.

5. LOCKED ROTOR CURRENT

Measured immediately after the fan blade is locked.

6. AIR FLOW AND STATIC PRESSURE

The performance specification of air flow and static pressure shown in this specification for approval is measured using the exhaust method. A double chamber is used in accordance with AMCA 210 standard or DIN 24163 specification. The values are recorded when the fan speed has stabilized at rated voltage.



建準電機 SUNONWEALTH Page 14 of 19

7. INSULATION RESISTANCE

- 7.1. PLASTIC HOUSING:
 - (1) Measured between internal stator and lead wire.
 - (2) Measured between housing and lead wire.
- 7.2. ALUMINIUM HOUSING:

Measured between internal stator and lead wire.

8. DIELECTRIC STRENGTH

Measure between housing and lead wire.



建準電機 SUNONWEALTH Page 15 of 19

III.NOTE

- 1. SAFETY
 - 1.1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
 - 1.2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
 - 1.3. This fan must be installed and used in compliance with all applicable safety standards and regulations.
 - 1.4. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
 - 1.5. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
 - 1.6. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact SUNON to customize the product design for your application.
 - 1.7. For critical or extreme environments, including non stop operation, please contact SUNON and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.
- 2. SPECIFICATION MODIFICATION
 - 2.1. SUNON offers engineering assistance on fan installation and cooling system design.
 - 2.2. All changes, modifications and/or revisions to the specifications, if any are incorporated in the attached specifications.



建準電機 SUNONWEALTH Page 16 of 19

- 2.3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both SUNON and the customer, in writing.
- 2.4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specified in Paragraph 3, above.

3. OTHER

- 3.1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 3.2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3.3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogen, formalin, phenol, or corrosive gas environments including, but not limited to, H2S, SO2, NO2, or Cl2.
- 3.4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements. Re: The term can be excluded, if the fan has been with IP55 design and meets customer's IP requirement.
- 3.5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.
- 3.6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 3.7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.



建準電機 SUNONWEALTH Page 17 of 19

- 3.8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 3.9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 3.10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

IV. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.



建準電機 SUNONWEALTH Page 18 of 19

Declaration of RoHS

Control declaration of environment- related substances/ materials

 In accordance with the Restriction of Hazardous Substances (RoHS) Directive 2011/65/EU, SUNON product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No		Substance	Criteria			
1	CFCs & HCFCs (ozone depleting	substances)	Forbidden			
2	Chlorinated Organic Solvent					
		Plastic (Frame, Impeller, wire harness, etc.)	<100ppm			
		Solder	<1000ppm			
3	Lead and its compounds	Steel alloy	<3500ppm			
		Aluminium alloy	<4000ppm			
		Copper alloy	<4wt%			
		Solder	<20ppm			
4	Cadmium and its compounds	Parts composed of metals containing zinc (e.g. brass, zinc for die casting)	<100ppm			
		Plastic	<5ppm			
5	PBBs and PBDEs					
6	PCB and PCT					
7	CP, Short-chain Chlorinated paraffins C10-13, Cl \ge 48 wt%					
8	Mirex					
9	PCN	Forbidden				
10	Hexavalent Chromium compoun	<100ppm				
11	Mercury and its compounds	Forbidden				
12	Asbestos		Forbidden			
13	Organic Tin compounds		Forbidden			
14	Azo compounds	Forbidden				
15	TBBP-A in external case plastic parts of products (PCB is exempted)					
16	Nickel in external case parts, which are likely to result in prolonged skin exposur					
17	Hexabromocyclododecane (HBCDD)					
18	Di-butyl Phthalate (DBP)					
19	Benzyl butyl Phthalate (BBP)					
20	Di-ethylhexyl Phthalate (DEHP)		<1000ppm			
21	Di-isobutyl Phthalate (DIBP)		<1000ppm			

▲ D.C.C. 2022.04.15 發行章