





### **POWER SUPPLY**

1AC 24V 60W

- · AC 100-240V Wide-range input
- NEC CLASS 2 compliant
- Cost optimized without compromising quality or reliability
- · No PE connection required
- Width only 36mm
- Efficiency up to 91.8%
- · Low no-load power losses
- Full power between -10°C and +60°C
- · Push-in terminals
- 3 Year warranty

### **PRODUCT DESCRIPTION**

The PIM60.241 is a DIN rail mountable single-phase-input power supply, which provides a floating, stabilized and galvanically separated SELV/PELV/ES1 output voltage. The output fulfils the requirements for a limited power source according to NEC CLASS 2.

The device is equipped with Push-in terminals, which are optimized for automated wiring.

The mechanically robust housing is made of a highgrade, reinforced molded material, which permits surrounding temperatures up to +70°C.

The unit is designed as "Class of Protection" II unit and fulfills the safety and EMC requirements without an input PE connection. This saves wiring costs.

The PIANO family is a compact industrial grade DIN rail power supply series that focuses on the essential features needed in today's industrial applications. The excellent cost/performance ratio does not compromise quality or reliability.

## **SHORT-FORM DATA**

Output voltage Adjustment range	DC 24V 24-28V	Nominal Factory setting 24.1V
Output current	2.5-2.1A 1.9-1.6A Derate betwee	Below +60°C ambient At +70°C ambient n +60°C and +70°C
Input voltage AC Mains frequency Input current AC Power factor Input inrush current Efficiency	AC 100-240V 50-60Hz 1 / 0.6A 0.55 / 0.47 15 / 36A <sub>peak</sub> 90.7 / 91.8%	± 10% ±6% At 120 / 230Vac At 120 / 230Vac, +40°C, cold start At 120 / 230Vac
Power losses	6.2 / 5.4W	At 120 / 230Vac
Hold-up time Temperature range	24 / 113ms -10°C to +70°C	At 120 / 230Vac
Size (w x h x d) Weight	36x90x91mm 225g / 0.5lb	Without DIN rail

### **ORDER NUMBERS**

Description: Order Number: PIM60.241 Power supply PIM60.241-xx

### MAIN APPROVALS

For details and the complete approval list, see chapter 18.



**NEC CLASS 2** 

Ind. Cont. Eq.





### Index

1	Intended Use	3	15 Environment 13	3
2	Installation Instructions	3	16 Safety and Protection Features 14	1
3	AC-Input	4	17 Dielectric Strength 14	1
4	DC-Input	5	18 Approved, Fulfilled or Tested Standards 15	5
5	Input Inrush Current	5	19 Regulatory Product Compliance 15	5
6	Output	6	20 Physical Dimensions And Weight 16	õ
7	Hold-up Time	7	21 Application Notes 17	7
8	Efficiency and Power Losses	8	21.1 Charging of Batteries 17	7
9	Lifetime Expectancy	9	21.2 Series Operation 17	7
10	MTBF	9	21.3 Parallel Use to Increase Output Power 17	7
11	Functional Diagram	10	21.4 Parallel Use for 1+1 Redundancy 17	7
12	Terminals And Wiring	10	21.5 Two Phase Operation 17	7
13	Front Side And User Elements	11	21.6 Use in a Tightly Sealed Enclosure 17	7
14	FMC	12		

The information given in this document is correct to the best of our knowledge and experience at the time of publication. If not expressly agreed otherwise, this information does not represent a warranty in the legal sense of the word. As the state of our knowledge and experience is constantly changing, the information in this data sheet is subject to revision. We therefore kindly ask you to always use the latest issue of this document (available under www.pulspower.com).

No part of this document may be reproduced or utilized in any form without our prior permission in writing.

Packaging and packaging aids can and should always be recycled. The product itself may not be disposed of as domestic refuse.

### TERMINOLOGY AND ABBREVIATIONS

PE and 🕏 Symbol	PE is the abbreviation for <b>P</b> rotective <b>E</b> arth and has the same meaning as the symbol $\textcircled{\oplus}$ .
Earth, Ground	This document uses the term "earth" which is the same as the U.S. term "ground".
t.b.d.	To be defined, value or description will follow later.
AC 230V	A figure displayed with the AC or DC before the value represents a nominal voltage with standard tolerances (usually $\pm 15\%$ ) included.
	E.g.: DC 12V describes a 12V battery disregarding whether it is full (13.7V) or flat (10V)
230Vac	A figure with the unit (Vac) at the end is a momentary figure without any additional tolerances included.
50Hz vs. 60Hz	As long as not otherwise stated, AC 100V and AC 230V parameters are valid at 50Hz mains frequency. AC 120V parameters are valid for 60Hz mains frequency.
may	A key word indicating flexibility of choice with no implied preference.
shall	A key word indicating a mandatory requirement.
should	A key word indicating flexibility of choice with a strongly preferred implementation.





### Intended Use

This device is designed for installation in an enclosure and is intended for commercial use, such as in industrial control, process control, monitoring, measurement, Audio/Video, information or communication equipment or the like.

Do not use this device in equipment, where malfunctioning may cause severe personal injury or threaten human life without additional appropriate safety devices, that are suited for the end-application. If this device is used in a manner outside of its specification, the protection provided by the device may be impaired.

Do not use this device on AC 100V mains with more than 1.9A load when the application is sensitive to short output voltage dips during mains interruptions even with a length shorter than 20ms.

### 2. Installation Instructions

### ▲ DANGER

Risk of electrical shock, fire, personal injury or death.

- Turn power off before working on the device. Protect against inadvertent re-powering.
- Do not open, modify or repair the device.
- Use caution to prevent any foreign objects from entering the housing.
- Do not use in wet locations or in areas where moisture or condensation can be expected.
- Do not touch during power-on, and immediately after power-off. Hot surfaces may cause burns.

#### Obey the following installation instructions:

This device may only be installed and put into operation by qualified personnel. This device does not contain serviceable parts. The tripping of an internal fuse is caused by an internal defect. If damage or malfunction should occur during installation or operation, immediately turn power off and send unit to the factory for inspection.

Install device in an enclosure providing protection against electrical, mechanical and fire hazards. Install the device onto a DIN rail according to EN 60715 with the input terminals on the bottom of the device.

Make sure that the wiring is correct by following all local and national codes. Use appropriate copper cables that are designed for a minimum operating temperature of +60°C for ambient temperatures up to +45°C, +75°C for ambient temperatures up to +60°C and +90°C for ambient temperatures up to +70°C. Ensure that all strands of a stranded wire enter the terminal connection.

The device is designed for pollution degree 2 areas in controlled environments. No condensation or frost is allowed. The enclosure of the device provides a degree of protection of IP20. The enclosure does not provide protection against spilled liquids.

The device is designed for overvoltage category II zones. Below 2000m altitude the device is tested for impulse withstand voltages up to 4kV, which corresponds to OVC III according to IEC 60664-1.

The device is designed as "Class of Protection" II equipment according to IEC 61140.

The device is suitable to be supplied from TN, TT or IT mains networks. The continuous voltage between the input terminal and the PE potential must not exceed 300Vac. A disconnecting means shall be provided for the input of the device.

The device is designed for convection cooling and does not require an external fan. Do not obstruct airflow and do not cover ventilation grid!

The device is designed for altitudes up to 5000m (16 400ft). Above 2000m (6560ft) a reduction in output current is required.

Keep the following minimum installation clearances: 40mm on top, 20mm on the bottom, 0mm left and right side. Increase the 0mm to 15mm in case the adjacent device is a heat source.

The device is designed, tested and approved for branch circuits up to 20A without additional protection device. If an external fuse is utilized, do not use circuit breakers smaller than 6A B- or 4A C-Characteristic to avoid a nuisance tripping of the circuit breaker.

The maximum surrounding air temperature is +70°C (158°F). The operational temperature is the same as the ambient or surrounding air temperature and is defined 2cm below the device. The device is designed to operate in areas between 5% and 95% relative humidity.





## **AC-Input**

The device is suitable to be supplied from TN, TT or IT mains networks.

AC input	nom.	AC 100-240V			
AC input range		90-264Vac	Continuous operation		
		264-300Vac	For maximum 500ms		
Allowed voltage L or N to earth	max.	300Vac	Continuous, according to IEC 60664-1		
Input frequency	nom.	50-60Hz	±6%		
Turn-on voltage	typ.	75Vac	Steady-state value, see Fig. 3-1		
Shut-down voltage	typ.	54Vac	Steady-state value, see Fig. 3-1		
External input protection	See rec	ecommendations in chapter 2.			

	<b>AC 100V</b>	AC 120V	AC 230V	
typ.	1.15A	1A	0.6A	At 24V, 2.5A, see Fig. 3-1
typ.	0.58	0.55	0.47	At 24V, 2.5A, see Fig. 3-4
typ.	50ms	50ms	48ms	See Fig. 3-2
typ.	18ms	18ms	18ms	At 24V, 2.5A constant current load, 0mF load capacitance, see Fig. 3-2
typ.	52ms	52ms	50ms	At 24V, 2.5A constant current load, 2mF load capacitance, see Fig. 3-2
max.	100mV	100mV	100mV	See Fig. 3-2
	typ. typ. typ. typ.	typ. 1.15A typ. 0.58 typ. 50ms typ. 18ms typ. 52ms	typ. 1.15A 1A typ. 0.58 0.55 typ. 50ms 50ms typ. 18ms 18ms typ. 52ms 52ms	typ. 1.15A 1A 0.6A typ. 0.58 0.55 0.47 typ. 50ms 50ms 48ms typ. 18ms 18ms 18ms typ. 52ms 52ms 50ms




Fig. 3-1: Input voltage range




Fig. 3-3: Input current vs. output load at 24V output voltage




Fig. 3-2: Turn-on behavior, definitions




Fig. 3-4: Power factor vs. output load at 24V output voltage





### 4. DC-Input

Do not operate this device with DC-input voltage.

## 5. Input Inrush Current

A NTC limits the input inrush current after turn-on of the input voltage. The inrush current is input voltage and ambient temperature dependent. The output load has no impact on the inrush current value.

The charging current into EMI suppression capacitors is disregarded in the first microseconds after switch-on.

		AC 100V	AC 120V	AC 230V	
Inrush current I <sub>peak</sub>	typ.	12A	15A	36A	At 40°C, ambient, cold start
·	typ.	10A	12A	30A	At 25°C, ambient, cold start
	max.	15A	18A	44A	At 40°C, ambient, cold start
	max.	12A	15A	36A	At 25°C, ambient, cold start
Inrush energy I <sup>2</sup> t	max.	$0.2A^2s$	$0.3A^2s$	1.4A <sup>2</sup> s	At 40°C, ambient, cold start




Fig. 5-1: Typical turn-on behavior at 120Vac and 25°C ambient




Fig. 5-2: Zoom into the first inrush peak




Fig. 5-3: Typical turn-on behavior at 230Vac and 25°C ambient




Fig. 5-4: Zoom into the first inrush peak





### 6. Output

The output provides a SELV/PELV/ES1 rated voltage, which is galvanically isolated from the input voltage. The output is electronically protected against no-load, overload and short circuit. In case of a protection event, audible noise may occur.

The output is designed to supply any kind of loads, including inductive and capacitive loads. Capacitive loads should not be larger than  $4\,400\mu\text{F}$  with 2.5A or  $5\,000\mu\text{F}$  with 1.25A additional resistive load.

At heavy overloads (when output voltage falls below 14V), the device delivers continuous output current for 25ms. After this, the output is switched off for approx. 145ms before a new start attempt is automatically performed. This cycle is repeated as long as the overload exists.

If the overload has been cleared, the device will operate normally.

Output voltage	nom.	DC 24V	
Adjustment range		24-28V	Guaranteed value
	max.	29V	This is the maximum output voltage which can occur at the clockwise end position of the potentiometer due to tolerances. It is not a guaranteed value which can be achieved.
Factory settings	typ.	24.1V	±0,2%, at full load, cold unit
Line regulation	max.	10mV	Between 90 and 300Vac
Load regulation	max.	100mV	Between 0 and 2.5A, static value, see Fig. 6-1
Ripple and noise voltage	max.	100mVpp	Bandwidth 20Hz to 20MHz, 50Ohm
Output current	nom.	2.5A	At 24V and an ambient temperature below 60°C
	nom.	1.9A	At 24V and 70°C ambient temperature
	nom.	2.1A	At 28V and an ambient temperature below 60°C
	nom.	1.6A	At 28V and 70°C ambient temperature
Overload behaviour	Continu	ous current	For output voltage above 14Vdc, see Fig. 6-1
	Intermit	tent current	For output voltage below 14Vdc, see Fig. 6-2
Overload/	max.	4A	Continuous current, see Fig. 6-1
short-circuit current	typ.	6A	Intermitted current peak value for typ. 25ms Load impedance 150mOhm, see Fig. 6-2 Discharge current of output capacitors is not included.
	max.	2.5A	Intermitted current average value (R.M.S.) Load impedance 150mOhm, see Fig. 6-2
Output capacitance	typ.	900µF	Included inside the device
Back-feeding loads	max.	35V	The unit is resistant and does not show malfunctioning when a load feeds back voltage to the device. It does not matter whether the device is on or off. The absorbing energy can be calculated according to the built-in large sized output capacitor.




Fig. 6-1: Output voltage vs. output current, typ.




Fig. 6-2: Intermittend current at short circuit, typ.\*)

\*) with cold devices the times are about 15% longer.





## 7. Hold-up Time

The hold-up time is the time during which a device's output voltage remains within specification following the loss of input power. The hold-up time is output load dependent. At no load, the hold-up time can be up to several seconds. The green DC-OK LED is also on during this time.

		<b>AC 100V</b>	<b>AC 120V</b>	AC 230V	
Hold-up time	typ.	14ms	24ms	113ms	At 24V, 2.5A
	typ.	38ms	58ms	230ms	At 24V, 1.25A
	min.	11ms	19ms	90ms	At 24V, 2.5A
	min.	30ms	46ms	184ms	At 24V, 1.25A




Fig. 7-1: Hold-up time vs. input voltage




Fig. 7-2: Shut-down behaviour, definitions





## 8. Efficiency and Power Losses

		<b>AC 100V</b>	AC 120V	AC 230V	
Efficiency	typ.	89.4%	90.7%	91.8%	At 24V, 2.5A (full load)
Average efficiency	typ.	89.3%	90.1%	90.7%	25% at 0.68A, 25% at 1.25A, 25% at 1.88A, 25% at 2.5A
Power losses	typ.	0.3W	0.3W	0.4W	At no load
	typ.	3.8W	3.5W	3.4W	At 24V, 1.25A (half load)
	typ.	7.1W	6.2W	5.4W	At 24V, 2.5A (full load)

The average efficiency is an assumption for a typical application where the device is loaded with 25% of the nominal load for 25% of the time, 50% of the nominal load for another 25% of the time, 75% of the nominal load for another 25% of the time and with 100% of the nominal load for the rest of the time.




Fig. 8-1: Efficiency vs. output current at 24V, typ.




Fig. 8-3: Efficiency vs. input voltage at 24V, 2.5A, typ.




Fig. 8-2: Losses vs. output current at 24V, typ.



Fig. 8-4: Losses vs. input voltage at 24V, 2.5A, typ.





### 9. Lifetime Expectancy

The Lifetime expectancy shown in the table indicates the minimum operating hours (service life) and is determined by the lifetime expectancy of the built-in electrolytic capacitors. Lifetime expectancy is specified in operational hours and is calculated according to the capacitor's manufacturer specification.

**Please note:** The manufacturer of the electrolytic capacitors only guarantees a maximum life of up to 15 years (131 400h). Any number exceeding this value is a calculated theoretical lifetime which can be used to compare devices.

	<b>AC 100V</b>	<b>AC 120V</b>	AC 230V	
Lifetime expectancy	115 000h	131 000h	148 000h	At 24V, 2.5A and 40°C
	260 000h	263 000h	263 000h	At 24V, 1.25A and 40°C
	324 000h	370 000h	419 000h	At 24V, 2.5A and 25°C
	734 000h	744 000h	744 000h	At 24V, 1.25A and 25°C

### 10. MTBF

MTBF stands for Mean Time Between Failure, which is calculated according to statistical device failures, and indicates reliability of a device. It is the statistical representation of the likelihood of a unit to fail and does not necessarily represent the life of a product.

The MTBF figure is a statistical representation of the likelihood of a device to fail. A MTBF figure of e.g. 1 000 000h means that statistically one unit will fail every 100 hours if 10 000 units are installed in the field. However, it cannot be determined if the failed unit has been running for 50 000h or only for 100h.

For these types of units the MTTF (Mean Time To Failure) value is the same value as the MTBF value.

	<b>AC 100V</b>	<b>AC 120V</b>	AC 230V	
MTBF SN 29500, IEC 61709	1 797 000h	1 858 000h	1 982 000h	At 24V, 2.5A and 40°C
	3 093 000h	3 186 000h	3 378 000h	At 24V, 2.5A and 25°C
MTBF MIL HDBK 217F	868 000h	886 000h	803 000h	At 24V, 2.5A and 40°C; Ground Benign GB40
	1 257 000h	1 278 000h	1 175 000h	At 24V, 2.5A and 25°C; Ground Benign GB25
	247 000h	252 000h	247 000h	At 24V, 2.5A and 40°C; Ground Fixed GF40
	325 000h	331 000h	328 000h	At 24V, 2.5A and 25°C; Ground Fixed GF25





## 11. Functional Diagram




Fig. 11-1: Functional diagram

# 12. Terminals And Wiring

The terminals are IP20 Finger safe constructed and suitable for field- and factory wiring.

	All Terminals
Туре	Push-in terminals
Solid wire	max. 2.5mm²
Stranded wire	max. 2.5mm <sup>2</sup>
Stranded wire with ferrules	max. 1.5mm <sup>2</sup>
American Wire Gauge	AWG 24-12
Max. wire diameter (including ferrules)	2.3mm
Wire stripping length	10mm / 0.4inch
Screwdriver	3mm slotted to open the spring





## 13. Front Side And User Elements



Fig. 13-1: Front side

- **A** Input Terminals
  - N Neutral conductor input
  - L Phase (Line) input
- **B** OutputTerminals

Dual terminals for the negative and positive pole. Both poles are internally connected.

- + Positive output
- Negative (return) output
- C DC OK LED (green)

The LED is on, when the output voltage is above 18V.

D Output voltage adustment potentiometer





### 14. EMC

The EMC behavior of the device is designed for applications in industrial environment as well as in residential, commercial and light industry environments.

The device complies with EN 61000-6-1, EN 61000-6-2, EN 61000-6-3, EN 61000-6-4, EN 61000-3-2 and EN 61000-3-3. The device complies with FCC Part 15 rules. Operation is subjected to following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Do not use this device on AC 100V mains with more than 1.9A load when the application is sensitive to short output voltage dips during mains interruptions even with a length shorter than 20ms.

EMC Immunity				
Electrostatic discharge	EN 61000-4-2	Contact discharge	8kV	Criterion A
		Air discharge	8kV	Criterion A
Electromagnetic RF field	EN 61000-4-3	80MHz - 6GHz	10V/m	Criterion A
Fast transients (Burst)	EN 61000-4-4	Input lines	4kV	Criterion A
		Output lines	2kV	Criterion A
Surge voltage on input	EN 61000-4-5	$L \rightarrow N$	2kV	Criterion A
		N / L $\rightarrow$ Earthed output	4kV	Criterion A
Surge voltage on output	EN 61000-4-5	(+) → (−)	1kV	Criterion A
		$(+) \rightarrow (-)$ Earthed	1kV	Criterion A
		(–) $\rightarrow$ (+) Earthed	1kV	Criterion A
Conducted disturbance	EN 61000-4-6	0.15 - 80MHz	10V	Criterion A
Voltage dips	EN 61000-4-11	0% of 100Vac	0Vac, 20ms	Criterion A/C
		40% of 100Vac	40Vac, 200ms	Criterion C
		70% of 100Vac	70Vac, 500ms	Criterion A
		0% of 120Vac	0Vac, 20ms	Criterion A
		40% of 120Vac	48Vac, 200ms	Criterion C
		70% of 120Vac	84Vac, 500ms	Criterion A
		0% of 200Vac	0Vac, 20ms	Criterion A
		40% of 200Vac	80Vac, 200ms	Criterion A
		70% of 200Vac	140Vac, 500ms	Criterion A
Voltage interruptions	EN 61000-4-11	0V	5000ms	Criterion C

#### **Performance criterions:**

Powerful transients

A: The device shows normal operation behavior within the defined limits.

**VDE 0160** 

**B:** The device operates continuously during and after the test. During the test minor temporary impairments may occur, which will be corrected by the device itself.

Over entire load range

750V, 1.3ms

Criterion A

**C:** Temporary loss of function is possible. The device may shut-down and restarts by itself. No damage or hazards for the device will occur.

A/C: Criterion A for output current below 1.9A and criterion C for output currents above 1.9A.

Conducted emission input lines	EN 55011, EN 55032, FCC Part 15, CISPR 11, CISPR32	Class B	
Conducted emission output lines	IEC/CISPR 16-1-2, IEC/CISPR 16-2-1	Limits for local DC power networks fulfilled.	
Radiated emission	EN 55011, EN 55032, CISPR 11, CISPR 32	Class B	
Harmonic input current	EN 61000-3-2	Fulfilled (Class A)	
Voltage fluctuations, flicker	EN 61000-3-3	Fulfilled, tested with non pulsing constant current loads.	
Switching Frequencies			
Main converter	2kHz to 130kHz	Input voltage and output load dependent	

All parameters are specified at 24V, 2.5A, 230Vac, 25°C ambient and after a 5 minutes run-in time unless otherwise noted.





### 15. Environment

Operational temperature	-10°C to +70°C (14°F to 158°F)	The operational temperature is the ambient or surrounding temperature and is defined as the air temperature 2cm below the device.		
Storage temperature	-40°C to +85°C (-40°F to 185°F)	For storage and transportation		
Output derating	0.06A/°C	Between +60°C and +70°C (140°F to 158°F)		
	0.15A/1000m or 5°C/1000m	For altitudes >2000m (6560ft), see Fig. 15-2		
	The derating is not hardware controlled. The user has to take this into consideration to stay below the derated current limits in order not to overload the unit.			
Humidity	5 to 95% r.h.	According to IEC 60068-2-30		
		No condensation allowed.		
Atmospheric pressure	110-54kPa	See Fig. 15-2 for details		
Altitude	Up to 5000m (16 400ft)	See Fig. 15-2 for details		
Over-voltage category	II	According to IEC 60664-1, for altitudes < 5000m		
Impulse withstand voltage	4kV (according to over-voltage	Input to PE		
	category III)	According to IEC 60664-1, for altitudes <2000m		
Degree of pollution	2	According to IEC 60664-1, non conductive		
Vibration sinusoidal	2-17.8Hz: ±1.6mm 17.8-500Hz: 2g 2 hours / axis	According to IEC 60068-2-6		
Shock	30g 6ms, 20g 11ms 3 bumps / direction, 18 bumps in total	According to IEC 60068-2-27 ation with DIN rails according to EN 60715 with		




Fig. 15-1: Output power vs. ambient temp.




Fig. 15-2: Output power vs. altitude

13 / 17





# 16. Safety and Protection Features

Isolation resistance	>500	MOhm	At delivered condition between input and output, measured with 500Vdc
Output over-voltage protection	typ.	30.5Vdc	
	max.	32Vdc	
			lefect, a redundant circuit limits the maximum output itput shuts down. To attempt a restart, turn the input 90s.
Class of protection	II		According to IEC 61140
Degree of protection	IP20		According to EN/IEC 60529
Over-temperature protection	Not I	ncluded	
Input transient protection	MOV	(Metal Oxide Varistor)	For protection values see chapter 14 (EMC).
Internal input fuse	Inclu	ded	Not user replaceable slow-blow high-braking capacity fuse
Touch current (leakage current)	typ.	40μΑ / 80μΑ	At 100Vac, 50Hz, TN-, TT-mains / IT-mains
	typ.	60μΑ / 120μΑ	At 120Vac, 60Hz, TN-, TT-mains / IT-mains
	typ.	100μΑ / 200μΑ	At 230Vac, 50Hz, TN-, TT-mains / IT-mains
	max.	60μΑ / 100μΑ	At 110Vac, 50Hz, TN-, TT-mains / IT-mains
	max.	80μΑ / 150μΑ	At 132Vac, 60Hz, TN-, TT-mains / IT-mains
	max.	140μΑ / 260μΑ	At 264Vac, 50Hz, TN-, TT-mains / IT-mains

## 17. Dielectric Strength

The output voltage is floating and has no ohmic connection to the ground.

The output is insulated to the input by a double or reinforced insulation.

Type and routine tests are conducted by the manufacturer. Field tests may be conducted in the field using the appropriate test equipment which applies the voltage with a slow ramp (2s up and 2s down). Connect all phase-terminals together as well as all output poles before conducting the test. When testing, set the cut-off current settings to the value in the table below

It is recommended that either the (+) pole or the (-) pole shall be connected to the protective earth system. This helps to avoid situations in which a load starts unexpectedly or cannot be switched off when unnoticed earth faults occur.




Fig. 17-1: Dielectric strength

		Α
Type test	60s	3000Vac
Factory test	5s	2500Vac
Field test	5s	2000Vac
Field test cut-off current settings		>2mA





# 18. Approved, Fulfilled or Tested Standards

IEC 61010	CB Report	CB Scheme Certificate IEC 61010-2-201 - Electrical Equipment for Measurement, Control and Laboratory Use - Particular requirements for control equipment
IEC 62368	CB Report	CB Scheme Certificate IEC 62368-1 - Audio/video, information and communication technology equipment - Safety requirements Output safety level: ES1
UL 61010	C UL US LISTED	UL Certificate Listed equipment for category NMTR - UL 61010-2-201 - Electrical equipment for measurement, control and laboratory use - Particular requirements for control equipment Applicable for US and Canada E-File: E198865
NEC Class 2	NEC CLASS 2	UL Certificate Limited Power Source Listed in the UL 61010-2-201 approval report, investigated according to UL 1310
IEC 61558-2-16 (Annex BB)	Safety Isolating Transformer	Test Certificate IEC 61558-2-16 - Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100V Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units
ISA-71.04-1985	Corrosion G3-ISA-71.04	Manufacturer's Declaration (Online Document) Airborne Contaminants Corrosion Test Severity Level: G3 Harsh H2S: 100ppb NOx: 1250ppb Cl2: 20ppb SO2: 300ppb Test Duration: 3 weeks, which simulates a service life of at least 10 years
VDMA 24364	LABS VDMA 24364-C1-L/W	Paint Wetting Impairment Substances Test (or LABS-Test) Tested for Zone 2 and Test Class C1 according to VDMA 24364-C1-L/W for solvents and water-based paints

# 19. Regulatory Product Compliance

EU Declaration of		The CE mark indicates conformance with the European		
Conformity	C€	<ul><li>EMC directive</li><li>Low-voltage directive (LVD)</li><li>RoHS directive</li></ul>		
REACH Regulation	REACH 🗸	Manufacturer's Declaration EU Regulation regarding the Registration, Evaluation, Authorization and Restriction of Chemicals EU Regulation 1907/2006		
WEEE Regulation		Manufacturer's Declaration EU Directive on Waste Electrical and Electronic Equipment Registered in Germany as business to business (B2B) products. EU Directive 2012/19/EU		
RoHS (China RoHS 2)	<b>2</b> 5	Manufacturer's Statement Administrative Measures for the Restriction of the Use of Hazardous Substances in Electrical and Electronic Products 25 years		

All parameters are specified at 24V, 2.5A, 230Vac, 25°C ambient and after a 5 minutes run-in time unless otherwise noted.






**EAC TR Registration** 



EAC Certificate EAC EurAsian Conformity - Registration Russia, Kazakhstan and Belarus 8504408200, 8504409000

# 20. Physical Dimensions And Weight

Width	36mm / 1.42''
Height	90mm / 3.54''
Depth	91mm / 3.58"
	The DIN rail height must be added to the unit depth to calculate the total required installation depth.
Weight	225g / 0.5lb
DIN rail	Use 35mm DIN rails according to EN 60715 or EN 50022 with a height of 7.5 or 15mm.
Housing material	High-grade polycarbonate / ABS blend material
Installation clearances	See chapter 2.
Penetration protection	Small parts like screws, nuts, etc. with a diameter larger than 4.2mm.






Fig. 20-1: Front view

Fig. 20-2: Side view

All dimensions in mm unless otherwise noted.



### 21. Application Notes

### 21.1. CHARGING OF BATTERIES

Do not use the power supply to charge batteries.


#### 21.2. SERIES OPERATION

Power supplies of the same type can be connected in series for higher output voltages. It is possible to connect as many units in series as needed, providing the sum of the output voltage does not exceed 150Vdc. Voltages with a potential above 60Vdc must be installed with a protection against touching.

Avoid return voltage (e.g. from a decelerating motor or battery) which is applied to the output terminals.

Keep an installation clearance of 15mm (left / right) between two power supplies and avoid installing the power supplies on top of each other.

Pay attention that leakage current, EMI, inrush current, harmonics will increase when using multiple power supplies.



### 21.3. PARALLEL USE TO INCREASE OUTPUT POWER

Do not use parallel devices for higher output currents.


#### 21.4. PARALLEL USE FOR 1+1 REDUNDANCY

Do not use this device to build redundant systems since there is no monitoring (DC-OK signal) included.

### 21.5. TWO PHASE OPERATION

The power supply can also be operated on two phases of a three-phase-system. Such a phase-to-phase connection is allowed as long as the supplying voltage is below 240V<sup>+10%</sup>.

Ensure that the wire, which is connected to the N-terminal, is appropriately fused.



#### 21.6. USE IN A TIGHTLY SEALED ENCLOSURE

When the power supply is installed in a tightly sealed enclosure, the temperature inside the enclosure will be higher than outside. In such situations, the inside temperature defines the ambient temperature for the power supply.

The power supply is placed in the middle of the box, no other heat producing items are inside the box. The temperature sensor inside the box is placed in the middle of the right side of the power supply with a distance of 1cm. The following measurement results can be used as a reference to estimate the temperature rise inside the enclosure.

	Case A	Case B	
Enclosure size	<b>110</b> x180x165mm	<b>110</b> x180x165mm	
	Rittal Typ IP66 Box	Rittal Typ IP66 Box	
	PK 9516 100	PK 9516 100	
	plastic	plastic	
Input voltage	230Vac	230Vac	
Load	24V, 2A; (= <b>80</b> %)	24V, 2.5A; (= <b>100</b> %)	
Temperature inside the box	28.6°C	30.2°C	
Temperature outside the box	21°C	21°C	
Temperature rise	7.6K	9.2K	

All parameters are specified at 24V, 2.5A, 230Vac, 25°C ambient and after a 5 minutes run-in time unless otherwise noted.