Tel/tronix[®]

Spectrum Analyzer

RSA600A Series Laboratory Spectrum Analyzer Datasheet



The RSA600A Series USB spectrum analyzers offer high bandwidth laboratory spectrum analysis in a small, very transportable package.

Features and benefits

- 9 kHz to 3.0/7.5 GHz frequency range covers a broad range of analysis
- 40 MHz acquisition bandwidth enables real time analysis for transient capture and vector analysis
- Amplitude accuracy of 0.2 dB to 3 GHz (95% confidence)
- Standard GPS/GLONASS/Beidou receiver
- Optional tracking generator for gain/loss, antenna and cable
- Streaming capture can be used to record and play back long term events
- SignalVu-PC software offers real time signal processing with DPX Spectrum/Spectrogram to minimize time spent finding transient problems
- 100 µsec minimum signal duration with 100% probability of intercept ensure you see problems first time, every time
- Application programming interface included for development of custom programs
- Accessories including tablet PC, calibration kits, adapters and phasestable cables offer a complete solution for design, characterization, and manufacturing

Applications

- Characterization of RF devices, subsystems, and systems
- Manufacturing test
- Mobile field operations

The RSA600 Series gives you the bandwidth and analysis tools you need to succeed

The RSA600 series brings real-time spectrum analysis and wide analysis bandwidth to solving the problems of engineers who need to characterize, validate and manufacture their designs. The heart of the system is the USB-based RF spectrum analyzer that captures 40 MHz bandwidths with great fidelity. With 70 dB dynamic range and frequency coverage to 7.5 GHz, you can fully characterize wideband signals up to 40 MHz bandwidths. The USB form factor moves the processing power to the PC of your choice, so you decide when you need more processing power or

The optional tracking generator enables gain/loss measurements for quick tests of filters, amplifiers, duplexers and other components, and you can add cable and antenna measurements of VSWR, return loss, distance to fault, and cable loss as needed.

SignalVu-PC software offers rich analysis capability for your lab


The RSA600 series operates with SignalVu-PC, a powerful program used as the basis of Tek's traditional spectrum analyzers, offering a deep analysis capability previously unavailable in low-cost laboratory solutions. Real-time processing of the DPX spectrum/spectrogram is enabled in your PC, further reducing the cost of hardware. Customers who need programmatic access to the instrument can choose either the SignalVu-PC programmatic interface or use the included application programming interface (API) that provides a rich set of commands and measurements directly. Basic functionality of the free SignalVu-PC program is far from basic. Base version measurements are shown below.

Measurements and functions included in SignalVu-PC base version


| General signal analysis | Description |
|---|---|
| Spectrum analyzer | Spans from 100 Hz to 7.5 GHz, 3 traces + math and spectrogram trace, 5 markers with power, relative power, integrated power, power density and dBc/Hz functions |
| DPX spectrum/spectrogram | Real time display of spectrum with 100% probability of intercept of 100 usec signals in up to 40 MHz span |
| Amplitude, frequency, phase vs. time, RF I and Q vs. time | Basic vector analysis functions |
| Time overview/navigator | Enables easy setting of acquisition and analysis times for deep analysis in multiple domains |
| Spectrogram | Analyze and re-analyze your signal in 2-D or 3-D waterfall display |
| AM/FM listening | Hear and record to file FM and AM signals |
| Signal recording | Record 40 MHz bandwidth for re- analysis in all domains including real time spectrum analysis (requires application SV56 for Playback) |
| Analog modulation analysis | Description |
| AM, FM, PM analysis | Measures key AM, FM, PM parameters |
| RF measurements | Description |
| Spurious measurement | User-defined limit lines and regions provide automatic spectrum violation testing across the entire range of the instrument. |
| Spectrum emission mask | User-set or standards-specific masks. |
| Occupied bandwidth | Measures 99% power, -xdB down points. |
| Channel power and ACLR | Variable channel and adjacent/alternate channel parameters. |
| MCPR | Sophisticated, flexible multi-channel power measurements. |
| CCDF | Complementary Cumulative Distribution Function plots the statistical variations in signal level. |
| Signal strength with audio tone | Measures signal strength and displays a spectrum and signal strength bar for interference hunting and signal quality evaluations. |

The RSA600A combined with SignalVu-PC offers advanced measurements


With 40 MHz of real-time bandwidth, the unique DPX spectrum/ spectrogram shows you every instance of an interfering or unknown signal, even down to 100 µs in duration. The following image shows a WLAN transmission (green and orange), and the narrow signals that repeat across the screen are a Bluetooth access probe. The spectrogram (upper part of the screen) clearly separates these signals in time to show any signal collisions.



Finding unexpected signals is easy with unattended mask monitoring. A mask can be created on the DPX spectrum display, and actions taken upon every violation, including stop, save a picture, save acquisition, or send an audible alert. In the illustration below, a mask violation has occurred in red on the mask, and a picture of the screen was saved as a result. Mask testing can be used for unattended monitoring and when playing back recorded signals, enabling testing for different violations on the same signals.



The tracking generator (Option 04 on the RSA600) is controlled via SignalVu-PC. Here you can enter start-stop frequencies, set number of steps in the span, adjust reference level, and normalize the tracking generator with a calibrate function. A bandpass filter response from 800 MHz to 3 GHz is shown below.



SignalVu-PC application-specific licenses

SignalVu-PC offers a wealth of application-oriented options including:

- General-purpose modulation analysis (27 modulation types including 16/32/64/256 QAM, QPSK, O-QPSK, GMSK, FSK, APSK)
- Buetooth® analysis of Low Energy, Basic Rate and Enhanced Data Rate
- P25 analysis of phase I and phase 2 signals
- WLAN analysis of 802.11a/b/g/j/p, 802.11n, 802.11ac
- LTE[™] FDD and TDD Base Station (eNB) Cell ID & RF measurements
- Mapping
- Pulse analysis
- AM/FM/PM/Direct Audio Measurement including SINAD, THD
- Playback of recorded files, including complete analysis in all domains
- Signal classification and survey

See the separate SignalVu-PC data sheet for complete details and ordering information. Selected applications are illustrated below.


General purpose modulation analysis

SignalVu-PC application SV21 bundles 27 different modulation types into a single analysis package and offers constellation displays, eye diagrams, symbol tables, trellis diagrams, modulation quality summaries and more. Symbol rates and filter types are adjustable and an internal equalizer is included for signal optimization. The illustration below is of a TETRAstandard signal modulated with pi/4DQPSK modulation at 18.0 ksymbols/ sec




Bluetooth

With application SV27 you can perform Bluetooth SIG standard-based transmitter RF measurements in the time, frequency, and modulation domains. This application supports Basic Rate and Low Energy Transmitter measurements defined by Bluetooth SIG Test Specification RF.TS.4.1.1 for Basic Rate and RF-PHY.TS.4.1.1 for Bluetooth Low Energy. Application SV27 also automatically detects Enhanced Data Rate packets, demodulates them and provides symbol information. Data packet fields are color encoded in the Symbol table for clear identification. Pass/Fail results are provided with customizable limits and the Bluetooth presets make the different test set-ups push-button. The measurement below shows deviation vs. time, frequency offset and drift, and a measurement summary with pass/fail results.



APCO 25

SignalVu-PC application SV26 enables analysis of APCO P25 signals. The following image shows a Phase II HCPM signal being monitored for anomalies with the spectrogram while performing transmitter power, modulation, and frequency measurements to the TIA-102 standards specification.



LTE


Application SV28 enables the following LTE base station transmitter measurements:


- Cell ID
- Channel power
- Occupied bandwidth
- Adjacent channel leakage ratio (ACLR)
- Spectrum emission mask (SEM)
- Transmitter off power for TDD

The measurements follow the definition in 3GPP TS Version 12.5 and support all base station categories, including picocells and femtocells. Pass/Fail information is reported and all channel bandwidths are supported.

The Cell ID preset displays the Primary Synchronization Signal (PSS) and the Secondary Synchronization Signal (SSS) in a Constellation diagram. It also provides Frequency Error.

The illustration below shows spectral monitoring with the spectrogram display combined with a Cell ID/Constellation, Spectrum Emission Mask and ACLR measurements.






Return Loss/VSWR, distance to fault and cable loss – Perform component characterization tasks easily and cost-effectively. When equipped with the option 04 tracking generator, the RSA500A series with application license SV60xx-SVPC makes one-port measurements on cables, devices and antennas.

Return loss of a bandpass filter measured from 700 MHz to 2.6 GHz. Markers have been placed a 1.48 GHz (-34.4 dB return loss) and at 1.73 GHz (-11.68 dB return loss), indicating the best and worse match in the passband of the filter

WLAN 802.11a/b/g/j/p/n/ac

With options SV23, 24 and 25, sophisticated WLAN measurements are easy. On the 802.11ac (20 MHz) signal shown, the spectrogram shows the initial pilot sequence followed by the main signal burst. The modulation is automatically detected as 64 QAM for the packet and displayed as a constellation. The data summary indicates an EVM of -37.02 dB RMS, and burst power is measured at -17.32 dBm. SignalVu-PC applications are available for 802.11a/b/j/g/p, 802.11n, and 802.11ac to 40 MHz bandwidth.




Playback

Application SV56, Playback of recorded signals, can reduce hours of watching and waiting for a spectral violation to minutes at your desk reviewing recorded data.

Recording length is limited only by storage media size, and recording is a basic feature included in SignalVu-PC. SignalVu-PC application SV56 (Playback) allows for complete analysis by all SignalVu-PC measurements, including DPX Spectrogram. Minimum signal duration specifications are maintained during playback. AM/FM audio demodulation can be performed. Variable span, resolution bandwidth, analysis length, and bandwidth are all available.

In the illustration below, the FM band is being replayed, with a mask applied to detect spectral violations, simultaneous with listening to the FM signal at the center frequency of 92.3 MHz.







Rackmount for 1 or 2 RSA600s

Specifications

All specifications are guaranteed unless noted otherwise. All specifications apply to all models unless noted otherwise.

Frequency

Frequency range

RSA603A 9 kHz to 3 GHz RSA607A 9 kHz to 7.5 GHz

Frequency marker readout

accuracy

 \pm (RE × MF + 0.001 × Span) Hz RE: Reference Frequency Error

MF: Marker Frequency [Hz]

Reference frequency accuracy

Initial accuracy at Cal (30 min

warm-up)

±1 x 10⁻⁶

First year aging, typical **Cumulative error (Initial** ±1 x 10⁻⁶ (1 year) 3 x 10⁻⁶ (1 year)

accuracy + temperature +

aging), typical

 $\pm 0.9 \times 10^{-6}$ (-10 to 60 °C) Temperature drift External reference input BNC connector, 50 Ω nominal

External reference input

frequency

Every 1 MHz from 1 to 20 MHz plus the following: 1.2288 MHz, 2.048 MHz, 2.4576 MHz, 4.8 MHz, 4.9152 MHz, 9.8304 MHz,

13 MHz, and 19.6608 MHz.

The spurious level on the input signal must be less than -80 dBc within 100 kHz offset to avoid on-screen spurious.

External reference input range ±5 ppm External reference input level -10 to +10 dBm

RF input

RF input

RF Input Impedance 50 O

RF VSWR (RF Attn = 20 dB),

typical

< 1.2 (10 MHz to 3 GHz) < 1.5 (>3 GHz to 7.5 GHz)

RF VSWR preamp ON, typical < 1.5 (10 MHz to 6 GHz, RF ATT=10 dB, preamp on)

< 1.7 (> 6 GHz to 7.5 GHz, RF ATT=10 dB, preamp on)

Maximum RF input level

Maximum DC voltage ±40 V (RF input)

Maximum safe input power +33 dBm (RF input, 10 MHz to 7.5 GHz, RF Attn ≥ 20 dB)

> +13 dBm (RF input, 9 kHz to 10 MHz) +20 dBm (RF input, RF Attn < 20 dB)

RF input

Maximum safe input power

+33 dBm (RF input, 10 MHz to 7.5 GHz, RF Attn ≥ 20 dB)

(Preamp On)

+13 dBm (RF input, 9 kHz to 10 MHz)

Maximum measurable input

power

+30 dBm (RF input, ≥10 MHz to Fmax, RF ATT Auto)

+20 dBm (RF input, <10 MHz, RF ATT Auto)

Input RF attenuator

0 dB to 51 dB (1 dB step)

Amplitude and RF

Amplitude and RF flatness

Reference level setting range

-170 dBm to +40 dBm, 0.1 dB step, (Standard RF input)

Amplitude accuracy at all center frequencies

| | 18 °C to 28 °C | 18 °C to 28 °C, typical (95% confidence) | -10 °C to 55 °C, typical |
|------------------------|----------------|--|--------------------------|
| 9 kHz ≤ 3.0 GHz | ±0.8 dB | ±0.2 dB | ±1.0 dB |
| > 3 to 7.5 GHz | ±1.5 dB | ±0.6 dB | ±2.0 dB |
| Center frequency range | 18 °C to 28 °C | 18 °C to 28 °C, typical (95% confidence) | 18 °C to 28 °C, typical |

Amplitude Accuracy at All Center Frequencies - Preamp ON (18 ℃ to 28 ℃, 10 dB RF Attenuator)

100 kHz to ≤3.0 GHz ±1.0 dB ±0.5 dB ±1.0 dB > 3 to 7.5 GHz ±1.75 dB ±0.75 dB ±3.0 dB

Preamp gain

27 dB at 2 GHz

21 dB at 6 GHz (RSA607A)

Channel response (amplitude and phase deviation), typical

For these specifications, use a flat top window for maximum CW amplitude verification accuracy with the RF attenuator setting at 10 dB.

| Characteristic | Description | | | |
|------------------------------|----------------------|-----------------------------|-------------------------------------|-------------------------------|
| Measurement center frequency | Span | Amplitude flatness, typical | Amplitude flatness, RMS, typical | Phase linearity, RMS, typical |
| 9 kHz to 40 MHz | ≤40 MHz ¹ | ±1.0 dB | 0.60 dB | |
| >40 MHz to 4.0 GHz | ≤20 MHz | ±0.10 dB | 0.08 dB | 0.3° |
| >4 GHz to 7.5 GHz | ≤20 MHz | ±0.35 dB | 0.20 dB | 0.7° |
| >40 MHz to 4 GHz | ≤40 MHz | ±0.15 dB | 0.08 dB | 0.6° |
| >4 GHz to 7.5 GHz | ≤40 MHz | ±0.40 dB | 0.20 dB | 1.0° |

Channel response (Amplitude flatness)

For these specifications, use a flat top window for maximum CW amplitude verification accuracy with the RF attenuator setting at 10 dB. The specifications are valid for the test center frequencies listed at the end of the table.

| Characte | ristic | Description |
|------------|-------------------------|---|
| Amplitude | eflatness | |
| | Span | |
| | ≤20 MHz | ±0.5 dB |
| | ≤40 MHz | ±0.5 dB |
| Test cente | er frequencies (in MHz) | 21, 30, 500, 1000, 1500, 2000, 2500, 3000, 3500, 3950, 4050, 4500, 4850, 4950, 5500, 5750, 5850, 6200, 6650, 6750, 7000, 7450 |

Span extents cannot exceed lower frequency limit of the instrument

Trigger

Trigger/Sync input, typical Voltage range: TTL, 0.0 V to 5.0 V

Trigger level (Schmitt trigger):

Positive-going threshold voltage: 1.6 V min, 2.1 V max Negative-going threshold voltage: 1.0 V min., 1.35 V max Impedance: 10 k ohms with schottky clamps to 0 V, +3.4 V

External trigger timing uncertainty >20 MHz to 40 MHz acquisition bandwidth: ±250 ns

Uncertainty increases as acquisition bandwidth is decreased.

Power trigger

Power trigger, typical Range: 0 dB to -50 dB from reference level, for trigger levels > 30 dB above the noise floor.

Type: Rising or falling edge

Trigger re-arm time: ≤ 100 µsec

Power trigger position timing

uncertainty

>20 MHz to 40 MHz acquisition bandwidth: ±250 ns

Uncertainty increases as acquisition bandwidth is decreased.

Power trigger level accuracy ±1.5 dB for CW signal at tuned center frequency for trigger levels > 30 dB above the noise floor.

This specification is in addition to the overall amplitude accuracy uncertainty for SA mode.

Noise and distortion

All noise and distortion measurements are made with the Preamp off, except where noted.

3rd Order IM intercept (TOI) +12 dBm at 2.130 GHz

3rd Order IM intercept (TOI),

Preamp off, typical +10 dBm (9 kHz to 25 MHz)

+15 dBm (25 MHz to 3 GHz)

+15 dBm (3 GHz to 4 GHz, RSA607A) +10 dBm (4 GHz to 7.5 GHz, RSA607A)

Preamp on, typical -20 dBm (9 kHz to 25 MHz)

-15 dBm (25 MHz to 3 GHz) -15 dBm (3 GHz to 4 GHz)

-20 dBm (4 GHz to 7.5 GHz, RSA607A)

3rd Order Inter-modulation

distortion

-74 dBc at 2.130 GHz

Each signal level -25 dBm at the RF input. 2 MHz tone separation. Attenuator = 0, Reference level = -20 dBm.

Noise and distortion

3rd Order inter-modulation distortion

> Preamp off, typical < -70 dBc (10 kHz to 25 MHz)

> > < -80 dBc (25 MHz to 3 GHz) < -80 dBc (3 GHz to 4 GHz)

< -70 dBc (4 GHz to 6 GHz, RSA607A) < -70 dBc (6 GHz to 7.5 GHz, RSA607A)

Each signal level -25 dBm at the RF input. 2 MHz tone separation. Attenuator = 0, Reference level = -20 dBm.

< -70 dBc (9 kHz to 25 MHz) Preamp on, typical

> < -80 dBc (25 MHz to 3 GHz) < -80 dBc (3 GHz to 4 GHz)

< -70 dBc (4 GHz to 6 GHz, RSA607A) < -70 dBc (6 GHz to 7.5 GHz, RSA607A)

Each signal level -55 dBm at the RF input. 2 MHz tone separation. Attenuator = 0, Reference level = -50 dBm.

2nd Harmonic distortion, typical

2nd Harmonic distortion < -75 dBc (40 MHz to 1.5 GHz)

< -75 dBc (1.5 GHz to 3.75 GHz, RSA607A)

2nd Harmonic distortion,

Preamp on

< - 60 dBc, 40 MHz to 3.75 GHz, input frequency

2nd Harmonic distortion intercept

(SHI)

+35 dBm, 40 MHz to 1.5 GHz, input frequency

+35 dBm, 1.5 GHz to 3.75 GHz, input frequency

2nd Harmonic distortion intercept

(SHI), Preamp on

+15 dBm, 40 MHz to 3.75 GHz, input frequency

Displayed average noise level (DANL)

(Normalized to 1 Hz RBW, with log-average detector)

| Frequency range | Preamp on | Preamp on, typical | Preamp off, typical |
|----------------------------|-------------|--------------------|---------------------|
| 500 kHz to 1 MHz | -138 dBm/Hz | -145 dBm/Hz | -130 dBm/Hz |
| 1 MHz to 25 MHz | -153 dBm/Hz | -158 dBm/Hz | -130 dBm/Hz |
| >25 MHz to 1 GHz | -161 dBm/Hz | -164 dBm/Hz | -141 dBm/Hz |
| >1 GHz to 2 GHz | -159 dBm/Hz | -162 dBm/Hz | -141 dBm/Hz |
| >2 GHz to 3 GHz | -156 dBm/Hz | -159 dBm/Hz | -138 dBm/Hz |
| >3 GHz to 4.2 GHz, RSA607A | - dBm/Hz | - dBm/Hz | -138 dBm/Hz |
| >4.2 GHz to 6 GHz, RSA607A | -159 dBm/Hz | -162 dBm/Hz | -147 dBm/Hz |
| >6 GHz to 7.5 GHz, RSA607A | -155 dBm/Hz | -158 dBm/Hz | -145 dBm/Hz |

Phase noise

| ь. | | | | |
|----|-----|-----|---|----|
| Рh | asi | e n | n | Se |

| Offset | 1 GHz CF | 1 GHz CF (typical) | 2 GHz CF (typical) | 6 GHz CF, (RSA607A) (typical) | 10 MHz (typical) |
|---------|-------------|--------------------|--------------------|-------------------------------------|------------------|
| 10 kHz | -94 dBc/Hz | -97 dBc/Hz | -96 dBc/Hz | -94 dBc/Hz | -120 dBc/Hz |
| 100 kHz | -94 dBc/Hz | -98 dBc/Hz | -97 dBc/Hz | -96 dBc/Hz | -124 dBc/Hz |
| 1 MHz | -116 dBc/Hz | -121 dBc/Hz | -120 dBc/Hz | -120 dBc/Hz | -124 dBc/Hz |

Integrated Phase (RMS), typical

 7.45×10^{-3} radians @ 1 GHz 8.24×10^{-3} radians @ 2 GHz 9.34×10^{-3} radians @ 6 GHz Integrated from 10 kHz to 10 MHz

Spurious response

Residual spurious response (Reference = -30 dBm, RBW = 1 kHz) $<\!\!\text{-}75~\text{dBm}$ (500 kHz to 60 MHz), typical

< -85 dBm (>60 MHz to 80 MHz), typical

<-100 dBm (>80 MHz to 7.5 GHz), typical

Spurious response with Signal (Image suppression)

< -65 dBc (10 kHz to < 3 GHz, Ref= -30 dBm, Atten = 10 dB, RF input Level = -30 dBm, RBW = 10 Hz)

< -65 dBc (3 GHz to 7.5 GHz, Ref= -30dBm, Atten = 10 dB, RF input Level = -30 dBm, RBW = 10 Hz)

Spurious response with signal at CF

Offset ≥ 1 MHz

| Frequency | Span ≤40 MHz, swept spans >40 MHz | |
|---------------------------|-----------------------------------|---------|
| | | Typical |
| 1 MHz - 100 MHz | | -75 dBc |
| 100 MHz - 3 GHz | -72 dBc | -75 dBc |
| 3 GHz - 7.5 GHz (RSA607A) | -72 dBc | -75 dBc |

Spurious response with signal at CF

(100 kHz ≤ offset <1 MHz, Span=2 MHz):

| Frequency P-TYP(PRI) | Typical |
|---------------------------|----------------------|
| 1 MHz - 100 MHz | -76 dBc |
| 100 MHz - 3 GHz | -76 dBc |
| 3 GHz - 7.5 GHz (RSA607A) | -74 dBc ² |

Spurious response with signal at other than CF, typical

| Frequency | Span ≤40 MHz, swept spans >40 MHz |
|---------------------------|-----------------------------------|
| 1 MHz – 25 MHz (LF Band) | -73 dBc |
| 25 MHz – 3 GHz | -73 dBc |
| 3 GHz – 7.5 GHz (RSA607A) | -73 dBc |

² Power supply sidebands, 620-660 kHz: -67 dBc, typical

Spurious response

Spurious response with signal at

RSA603A, RSA607A < 75 dBc, (CF: 30 MHz to 3 GHz, Ref = -30 dBm, Atten = 10 dB, RBW = 10 Hz, Span = 10 kHz)

Signal frequency = 2310 MHz, RF input level = -30 dBm

RSA607A < 77 dBc, (CF 3 G Hz to 7.5 GHz, Ref= -30 dBm, Atten = 10 dB, RBW=10 Hz, Span=10 kHz)

RF input Level = -30 dBm

Local oscillator feed-through to

input connector, typical

< -70 dBm, preamp off.

< -90 dBm, preamp on.

Attenuator = 10 dB.

Acquisition

IF bandwidth 40 MHz.

A/D converter 14 bits, 112 Ms/s.

Real-Time IF Acquisition Data 112 Ms/s, 16-bit integer samples.

ACLR

ACLR for 3GPP Down Link,

1 DPCH (2130 MHz)

-57 dB (Adjacent Channel)

-68 dB w/Noise Correction (Adjacent Channel)

-57 dB (First Alternate Channel)

-69 dB w/Noise Correction (First Adjacent Channel)

ACLR LTE -58 dB (Adjacent Channel)

-61 dB w/Noise Correction (Adjacent Channel)

-61 dB (First Alternate Channel)

-63 dB w/Noise Correction (First Adjacent Channel)

GPS location

| Format | GPS/GLONASS/BeiDou |
|------------------------------|---|
| GPS antenna power | 3 V, 100 mA maximum |
| Time to first fix, maximum | Lock time ranges from 2 sec (hot) to 46 sec (cold start)130 dBm input signal power. |
| Horizontal position accuracy | GPS: 2.6 m |
| | Glonass: 2.6 m |
| | BeiDou: 10.2 m |
| | GPS + Glonass: 2.6 m |
| | GPS + BeiDou: 2.6 m |
| | Test conditions: 24 hr. static, -130 dBm, full power |

This is an input signal at half of the IF frequency.

Tracking generator (Option 04)

Tracking Generator (Option 04)

Frequency range 9 kHz to 3 GHz

9 kHz to 7.5 GHz

Sweep speed 6700 MHz/second, 101 points, 50 kHz RBW (11 mS per point)

Measured using a Panasonic Toughpad FZ-G1, Intel® Core™ i5-5300U 2.3 GHz Processor, 8 GB RAM, 256 GB SSD,

Windows®7 Pro.

100 Hz Frequency resolution TG output connector N type

VSWR < 1.8:1, 10 MHz to 7.5 GHz, -20 dBm output level

40 dB

Maximum output power Output power level setting

range

Output power level step size 1 dB Output power level step size $\pm 0.5 dB$

accuracy

Harmonics < -22 dBc

< -30 dBc; spurious < 2 GHz from TG output frequency < -25 dBc; spurious ≥ 2 GHz from TG output frequency

± 1.5 dB, 10 MHz to 7.5 GHz, -20 dBm output level

Reverse power without

Non-harmonic spurious

Output level accuracy

damage

40 Vdc, +20 dBm RF

Transmission gain measurement error Gain of +20 to -40 dB: ±1 dB

Transmission gain

70 dB

measurement dynamic range

Return Loss, Distance-to-Fault, and Cable Loss measurements

Return Loss, Distance-to-Fault, and Cable Loss measurements

> Measurements Return Loss, Cable Loss, Distance-to-Fault

Frequency range 10 MHz to 3 GHz (RSA603A)

10 MHz to 7.5 GHz (RSA607A)

Sweep speed 4 5 ms/point, Return Loss measurement

5 ms/point, Distance-to-Fault measurement

5 ms/point, Cable Loss measurement

Frequency resolution 500 Hz

Return Loss measurement

error

Return Loss of 0 to 15 dB: ±0.5 dB

Return Loss of 15 to 25 dB: ±1.5 dB Return Loss of 25 to 35 dB: ±4.0 dB

Return Loss measurement error at 14 dB Return Loss

±1.5 dB from 10 MHz to 6.8 GHz ±3.0 dB from 6.8 GHz to 7.5 GHz

±1.0 dB from 10 MHz to 6.8 GHz ±2.5 dB from 6.8 GHz to 7.5 GHz

²⁰¹ point sweep Measured using a Panasonic Toughpad FZ-G1.

Return Loss, Distance-to-Fault, and Cable Loss measurements 50 dB

Return Loss measurement

Interference immunity

range

Return Loss Measurement Error within specifications for the following conditions:

+5 dBm interferer power within 800 kHz of measurement point

+5 dBm interferer power more than 800 kHz away from measurement point

Distance-to-Fault range

1500 m or 15 dB one-way cable loss capable, user defined.

Maximum range is a function of the cable velocity factor and the frequency step size as follows:

Range =
$$\left(\frac{Vp \times c}{2}\right) \times \left(\frac{N-1}{F_{stop} - F_{start}}\right)$$

Where:

 V_p = Cable velocity factor relative to the speed of light

c = Speed of light (m/s)

F_{start} = Sweep start frequency (Hz)

F_{stop} = Sweep stop frequency (Hz)

N = number of sweep points

Distance-to-Fault resolution 0.03m (RSA503A, RG-58 (Vp=0.66)), User Definable 0.01m (RSA507A, RG-58 (Vp=0.66)), User Definable

Minimum resolution is a function of the cable velocity factor and the frequency step size as follows:

Resolution =
$$\left(\frac{Vp \times c}{2}\right) \times \left(\frac{1}{F_{stop} - F_{start}}\right)$$

Resolution =
$$(\frac{\text{Range}}{N-1})$$

SignalVu-PC standard measurements and performance

Measurements included

| General signal analysis | |
|---|--|
| Spectrum analyzer | Spans from 1 kHz to 7.5 GHz Three traces plus math and spectrogram trace Five markers with power, relative power, integrated power, power density and dBc/Hz functions |
| DPX Spectrum/Spectrogram | Real time display of spectrum with 100% probability of intercept of 100 µsec signals in up to 40 MHz span |
| Amplitude, frequency, phase vs. time, RF I and Q vs. time | Basic vector analysis functions |
| Time Overview/Navigator | Enables easy setting of acquisition and analysis times for deep analysis in multiple domains |
| Spectrogram | Analyze and re-analyze your signal with a 2-D or 3-D waterfall display |
| AM/FM listening | Hear, and record to file, FM and AM signals |
| Analog modulation analysis | |
| AM, FM, PM analysis | Measures key AM, FM, PM parameters |
| RF measurements | |
| Spurious measurement | User-defined limit lines and regions provide automatic spectrum violation testing across the entire range of the instrument |
| Spectrum emission mask | User-defined or standards-specific masks |
| Occupied Bandwidth | Measures 99% power, -xdB down points |
| Channel Power and ACLR | Variable channel and adjacent/alternate channel parameters |
| MCPR | Sophisticated, flexible multi-channel power measurements |
| CCDF | Complementary Cumulative Distribution Function plots the statistical variations in signal level |

SignalVu-PC/RSA607A key characteristics

Maximum span 40 MHz real-time

9 kHz - 3 GHz swept

9 kHz - 7.5 GHz swept

Maximum acquisition time 1.0 s

aximum acquisition time 1.0

Minimum IQ resolution 17.9 ns (acquisition BW = 40 MHz)

Tuning TablesTables that present frequency selection in the form of standards-based channels are available for the following.

Cellular standards families: AMPS, NADC, NMT-450, PDC, GSM, CDMA, CDMA-2000, 1xEV-DO WCDMA, TD-SCDMA, LTE,

WiMax

Unlicensed short range: 802.11a/b/j/g/p/n/ac, Bluetooth

Cordless phone: DECT, PHS

Broadcast: AM, FM, ATSC, DVBT/H, NTSC

Mobile radio, pagers, other: GMRS/FRS, iDEN, FLEX, P25, PWT, SMR, WiMax

DPX spectrum display

Spectrum processing rate (RBW = auto, trace length 801)

≤10,000/s

DPX bitmap resolution 201x801

Marker information Amplitude, frequency, signal density

SignalVu-PC standard measurements and performance

Minimum signal duration for

100% probability of detection

100 µs

Span: 40 MHz, RBW = 300 kHz (Auto)

Due to the non-deterministic execution time of programs running under the Microsoft Windows OS, this specification may not be

met when the host PC is heavily loaded with other processing tasks

Span range (continuous

processing)

1 kHz to 40 MHz

Span range (swept)

Up to maximum frequency range of instrument

Dwell time per step

50 ms to 100 s

Trace processing

Color-graded bitmap, +Peak, -Peak, average

Trace length **RBW** range

801, 2401, 4001, 10401 1 kHz to 4.99 MHz

DPX spectrogram display

Trace detection

+Peak, -Peak, Average(V_{RMS})

Trace length, memory depth

801 (60,000 traces)

2401 (20,000 traces)

4001 (12,000 traces)

Time resolution per line

1 ms to 6400 s, user selectable

Spectrum display

Traces

Detector

Three traces + 1 math trace + 1 trace from spectrogram for spectrum display

Trace functions

Normal, Average (VRMS), Max Hold, Min Hold, Average of Logs Average (VRMS), Average, CISPR peak, +Peak, -Peak, Sample

Spectrum trace length

801, 2401, 4001, 8001,10401, 16001, 32001, and 64001 points

RBW range

10 Hz to 8 MHz

Analog modulation analysis

(standard)

AM demodulation accuracy,

typical

±2%

0 dBm input at center, carrier frequency 1 GHz, 1 kHz/5 kHz input/modulated frequency, 10% to 60% modulation depth

0 dBm input power level, reference level = 10 dBm, Atten=Auto

FM demodulation accuracy,

typical

±1% of span

0 dBm input at center, carrier frequency 1 GHz, 400 Hz/1 kHz input/modulated frequency

0 dBm input power level, reference level = 10 dBm, Atten=Auto

PM demodulation accuracy,

typical

±3% of measurement bandwidth

0 dBm input at center, carrier frequency 1 GHz, 1 kHz/5 kHz input/modulated frequency

0 dBm input power level, reference level = 10 dBm, Atten=Auto

Signal Strength display

Signal strength indicator

Located at right side of display

Measurement bandwidth

Up to 40 MHz, dependent on span and RBW setting Variable frequency based on received signal strength

Tone type

Sweep speed

Full-span sweep speed

Full span sweep speed, typical 5500 MHz/sec (RBW = 1 MHz)

5300 MHz/sec (RBW = 100 kHz) 3700 MHz/sec (RBW = 10 kHz) 950 MHz/sec (RBW = 1 kHz)

Measured using a Panasonic Toughpad FZ-G1, Intel® Core™ i5-5300U 2.3 GHz Processor, 8 GB RAM, 256 GB SSD,

Windows®7 Pro.

Spectrum display is only measurement on screen

Tuning step time via API

SignalVu-PC applications performance summary

AM/FM/PM and direct audio measurement (SVAxx-SVPC)

> Carrier frequency range (for modulation and audio measurements)

(1/2 × audio analysis bandwidth) to maximum input frequency

Maximum audio frequency

10 MHz

>0.1)

FM measurements (Mod. index Carrier Power, Carrier Frequency Error, Audio Frequency, Deviation (+Peak, -Peak, Peak-Peak/2, RMS), SINAD, Modulation

Distortion, S/N, Total Harmonic Distortion, Total Non-harmonic Distortion, Hum and Noise

AM measurements Carrier Power, Audio Frequency, Modulation Depth (+Peak, -Peak, Peak-Peak/2, RMS), SINAD, Modulation Distortion, S/N, Total

Harmonic Distortion, Total Non-harmonic Distortion, Hum and Noise

PM measurements

Carrier Power, Carrier Frequency Error, Audio Frequency, Deviation (+Peak, -Peak, Peak-Peak/2, RMS), SINAD, Modulation

Distortion, S/N, Total Harmonic Distortion, Total Non-harmonic Distortion, Hum and Noise

Audio filters Low pass, kHz: 0.3, 3, 15, 30, 80, 300, and user-entered up to 0.9 × audio bandwidth

High pass, Hz: 20, 50, 300, 400, and user-entered up to $0.9 \times audio bandwidth$

Standard: CCITT, C-Message

De-emphasis (µs): 25, 50, 75, 750, and user-entered

File: User-supplied .TXT or .CSV file of amplitude/frequency pairs. Maximum 1000 pairs

| Performance characteristics, typical | Conditions: Unless otherwise stated, performance is given for: Modulation rate = 5 kHz AM depth: 50% PM deviation 0.628 Radians | | | |
|--------------------------------------|--|--|---|--|
| | FM | AM | PM | Conditions |
| Carrier Power accuracy | Refer to instrument ampl | itude accuracy | | |
| Carrier Frequency accuracy | ± 0.5 Hz + (transmitter frequency × ref. freq. error) | Refer to instrument frequency accuracy | ± 0.2 Hz + (transmitter frequency × ref. freq. error) | FM deviation: 1 kHz / 10 kHz |
| Depth of Modulation accuracy | NA | ± 0.2%+(0.01 * measured value) | NA | Rate: 1 kHz to 100kHz Depth: 10% to 90% |
| Deviation accuracy | ± (1% × (rate + deviation)+50 Hz) | NA | ± 100% * (0.01 + (measured rate/1 MHz)) | FM Rate: 1 kHz to 1 MHz |
| Rate accuracy | ± 0.2 Hz | ± 0.2 Hz | ± 0.2 Hz | FM deviation: 1 kHz to 100 kHz |
| Residual THD | 0.10% | 0.13% | 0.1% | FM Deviation: 5 kHz Rate: 1 kHz to 10 kHz Depth: 50% |
| Residual SINAD | 43 dB | 58 dB | 40 dB | Deviation 5 kHz Rate: 1 kHz to 10 kHz Depth: 50% |

APCO P25 Measurements (SV26xx-SVPC)

Measurements

RF output power, operating frequency accuracy, modulation emission spectrum, unwanted emissions spurious, adjacent channel power ratio, frequency deviation, modulation fidelity, frequency error, eye diagram, symbol table, symbol rate accuracy, transmitter power and encoder attack time, transmitter throughput delay, frequency deviation vs. time, power vs. time, transient frequency behavior, HCPM transmitter logical channel peak adjacent channel power ratio, HCPM transmitter logical channel off slot power, HCPM transmitter logical channel power envelope, HCPM transmitter logical channel time alignment, cross-correlated markers

Modulation fidelity, typical

CF = 460 MHz, 815 MHz

C4FM ≤ 1.0% HCPM ≤ 0.5% HDQPSK ≤ 0.25%

Input signal level is optimized for best modulation fidelity.

Bluetooth Measurements (SV27xx-

SVPC)

Modulation formats Basic Rate, Bluetooth Low Energy, Enhanced Data Rate - Revision 4.1.1

Packet types: DH1, DH3, DH5 (BR), Reference (LE)

Measurements Peak Power, Average Power, Adjacent Channel Power or InBand Emission mask, -20 dB Bandwidth, Frequency Error, Modulation

Characteristics including Δ F1avg (11110000), Δ F2avg (10101010), Δ F2 > 115 kHz, Δ F2/ Δ F1 ratio, frequency deviation vs. time with packet and octet level measurement information, Carrier Frequency f0, Frequency Offset (Preamble and Payload), Max Frequency Offset, Frequency Drift f₁-f₀, Max Drift Rate f_n-f₀ and f_n-f_{n-5}, Center Frequency Offset Table and Frequency Drift table,

color-coded Symbol table, Packet header decoding information, eye diagram, constellation diagram

Output power, In-band emissions and ACP

Level uncertainty: refer to instrument amplitude and flatness specification

Measurement range: signal level > -70 dBm

Modulation characteristics Deviation range: ±280 kHz

Deviation uncertainty (at 0 dBm)

<2 kHz ⁵ + instrument frequency uncertainty (basic rate) <3 kHz ⁵ + instrument frequency uncertainty (low energy) Measurement range: Nominal channel frequency ±100 kHz

Initial Carrier Frequency Tolerance (ICFT) Measurement uncertainty (at 0 dBm): <1 kHz + instrument frequency uncertainty

Measurement range: Nominal channel frequency ±100 kHz

Carrier Frequency Drift Measurement uncertainty: <1 kHz + instrument frequency uncertainty

Measurement range: Nominal channel frequency ±100 kHz

General purpose digital modulation analysis (SVMxx-SVPC)

Modulation formats

BPSK, QPSK, 8PSK, 16QAM, 32QAM, 64QAM, 256QAM, PI/2DBPSK, DQPSK, PI/4DQPSK, D8PSK, D16PSK, SBPSK, OQPSK,

SOQPSK, MSK, GFSK, CPM, 2FSK, 4FSK, 8FSK, 16FSK, C4FM

Analysis period Up to 81,000 samples

Measurement filter Root Raised Cosine, Raised Cosine, Gaussian, Rectangular, IS-95 TX_MEA, IS-95 Base TXEQ_MEA, None

Reference Filter Gaussian, Raised Cosine, Rectangular, IS-95 REF, None

Filter rolloff factor $\alpha: 0.001 \text{ to 1, in } 0.001 \text{ steps}$

Measurements Constellation, Demod I&Q vs. Time, Error Vector Magnitude (EVM) vs. Time, Eye Diagram, Frequency Deviation vs. Time,

Magnitude Error vs. Time, Phase Error vs. Time, Signal Quality, Symbol Table, Trellis Diagram

Symbol rate range 1 k symbols/s to 40 M symbols/s

Modulated signal must be contained entirely within the acquisition bandwidth

Adaptive equalizer Linear, Decision-Directed, Feed-Forward (FIR) equalizer with coefficient adaptation and adjustable convergence rate. Supports

modulation types BPSK, QPSK, QQPSK, π/2-DBPSK, π/4-DQPSK, 8-PSK, 8-DSPK, 16-DPSK, 16/32/64/128/256-QAM

⁵ At nominal power level of 0 dBm

QPSK Residual EVM (center frequency = 2 GHz), typical

0.6 % (100 kHz symbol rate)

0.8 % (1 MHz symbol rate)

0.8 % (10 MHz symbol rate) 0.8 % (30 MHz symbol rate)

400 symbols measurement length, 20 Averages, normalization reference = maximum symbol magnitude

256 QAM Residual EVM (center frequency = 2 GHz), typical

0.6 % (10 MHz symbol rate)

0.7 % (30 MHz symbol rate)

400 symbols measurement length, 20 Averages, normalization reference = maximum symbol magnitude

LTE Downlink RF measurements (SV28xx-SVPC)

Standard Supported 3GPP TS 36.141 Version 12.5

Frame Format supported FDD and TDD

Measurements and Displays

Supported

Adjacent Channel Leakage Ratio (ACLR), Spectrum Emission Mask (SEM), Channel Power, Occupied Bandwidth, Power vs. Time showing Transmitter OFF power for TDD signals and LTE constellation diagram for Primary Synchronization Signal, Secondary

Synchronization Signal with Cell ID, Group ID, Sector ID and Frequency Error.

ACLR with E-UTRA bands (typical, with noise correction)

1st Adjacent Channel 60 dB (RSA607A) 2nd Adjacent Channel 62 dB (RSA607A)

Mapping (MAPxx-SVPC)

Supported map types Pitney Bowes MapInfo (*.mif), Bitmap (*.bmp), Open Street Maps (.osm)

Saved measurement results Measurement data files (exported results)

Map file used for the measurements

Google Earth KMZ file

Recallable results files (trace and setup files)

MapInfo-compatible MIF/MID files

Pulse measurements (SVPxx-SVPC)

> Measurements (nominal) Pulse-Ogram™ waterfall display of multiple segmented captures, with amplitude vs time and spectrum of each pulse. Pulse

frequency, Delta Frequency, Average on power, Peak power, Average transmitted power, Pulse width, Rise time, Fall time, Repetition interval (seconds), Repetition interval (Hz), Duty factor (%), Duty factor (ratio), Ripple (dB), Ripple (%), Droop (dB), Droop (%), Overshoot (dB), Overshoot (%), Pulse- Ref Pulse frequency difference, Pulse- Ref Pulsephase difference, Pulse- Pulse frequency difference, Pulse- Pulse phase difference, RMS frequency error, Max frequency error, RMS phase error, Max phase

error, Frequency deviation, Phase deviation, Impulse response (dB), Impulse response (time), Time stamp.

Minimum pulse width for

detection

150 ns

Average ON power at 18 °C to

28 °C, typical

±0.3 dB + absolute amplitude accuracy

For pulses of 300 ns width or greater, duty cycles of .5 to .001, and S/N ratio ≥ 30 dB

±0.2% of reading **Duty factor, typical**

For pulses of 450 ns width or greater, duty cycles of .5 to .001, and S/N ratio ≥ 30 dB

Average transmitted power,

typical

±0.5 dB + absolute amplitude accuracy

For pulses of 300 ns width or greater, duty cycles of .5 to .001, and S/N ratio ≥ 30 dB

Peak pulse power, typical ±1.2 dB + absolute amplitude accuracy

For pulses of 300 ns width or greater, duty cycles of .5 to .001, and S/N ratio ≥ 30 dB

Pulse width, typical ±0.25% of reading

For pulses of 450 ns width or greater, duty cycles of .5 to .001, and S/N ratio ≥ 30 dB

Playback of recorded signals

(SV56)

Playback file type R3F recorded by RSA306, RSA500, or RSA600

Recorded file bandwidth 40 MHz

File playback controls General: Play, stop, exit playback

> Location: Begin/end points of playback settable from 0-100% Skip: Defined skip size from 73 µs up to 99% of file size

Live rate: Plays back at 1:1 rate to recording time

Loop control: Play once, or loop continuously

Memory requirement Recording of signals requires storage with write rates of 300 MB/sec. Playback of recorded files at live rates requires storage with

read rates of 300 MB/sec.

WLAN Measurements, 802.11a/b/g/ j/p (SV23xx-SVPC)

WLAN power vs. time; WLAN symbol table; WLAN constellation; spectrum emission mask; error vector magnitude (EVM) vs. Measurements

symbol (or time), vs subcarrier (or frequency); mag error vs symbol (or time), vs. subcarrier (or frequency); phase error vs symbol (or time), vs. subcarrier (or frequency); channel frequency response vs. symbol (or time), vs. subcarrier (or frequency); spectral

flatness vs. symbol (or time), vs. subcarrier (or frequency)

Residual EVM - 802.11a/g/j /p

(OFDM), 64-QAM, typical

2.4 GHz, 20 MHz BW: -39 dB

5.8 GHz, 20 MHz BW: -38 dB

Input signal level optimized for best EVM, average of 20 bursts, ≥16 symbols each

Residual EVM - 802.11b,

CCK-11, typical

2.4 GHz, 11 Mbps: 1.3 %

Input signal level optimized for best EVM, average of 1,000 chips, BT = .61

WLAN Measurements 802.11n

(SV24xx-SVPC)

WLAN power vs. time: WLAN symbol table: WLAN constellation; spectrum emission mask; error vector magnitude (EVM) vs.

symbol (or time), vs subcarrier (or frequency); mag error vs symbol (or time), vs. subcarrier (or frequency); phase error vs symbol (or time), vs. subcarrier (or frequency); channel frequency response vs. symbol (or time), vs. subcarrier (or frequency); spectral

flatness vs. symbol (or time), vs. subcarrier (or frequency)

EVM performance - 802.11n,

64-QAM, typical

Measurements

2.4 GHz, 40 MHz BW: -38 dB

5.8 GHz. 40 MHz BW: -38 dB

Input signal level optimized for best EVM, average of 20 bursts, ≥16 symbols each

WLAN Measurements 802.11ac

(SV25xx-SVPC)

Measurements WLAN power vs. time; WLAN symbol table; WLAN constellation; spectrum emission mask; error vector magnitude (EVM) vs.

symbol (or time), vs subcarrier (or frequency); mag error vs symbol (or time), vs. subcarrier (or frequency); phase error vs symbol (or time), vs. subcarrier (or frequency); channel frequency response vs. symbol (or time), vs. subcarrier (or frequency); spectral

flatness vs. symbol (or time), vs. subcarrier (or frequency)

EVM performance - 802.11ac,

256-QAM, typical

5.8 GHz, 40 MHz BW: -38 dB

Input signal level optimized for best EVM, average of 20 bursts, ≥16 symbols each

28 Volt noise source drive

28 Volt noise source drive output

Output Level 28 VDC @ 140 mA

Output voltage turn ON/OFF

Turn on: 100 µS Turn off: $500 \mu S$

Input and output ports

Inputs, outputs, and inferfaces

RF input N type, female External frequency reference BNC, female

input

Trigger/Sync input **Tracking Generator Source**

BNC, female N type, female

Output

GPS Antenna SMA, female **USB Device Port** USB 3.0 - Type A **USB Status LED** LED, dual color red/green

LED states:

Steady Red: USB power applied, or resetting Steady Green: Initialized, ready for use Blinking Green: Transferring data to host

Installation requirements

Maximum power dissipation (fully loaded)

RSA600A: 45 W maximum.

2 A peak maximum, at 25 °C (77 °F) for ≤ 5 line cycles, after the product has been turned off for at least 30 seconds.

Surge current **Cooling clearance**

Bottom, top

0 mm (0 in.) with feet installed

6.3 mm (0.25 in.) without feet installed

Sides 0 mm (0 in.)

Rear: 38.1 mm (1.5 in.)

Physical characteristics

Physical characteristics

Width 222.3 mm (8.75 in) Height 75.0 mm (2.95 in) 358.6 mm (14.12 in) Length Net weight 2.79 kg (6.15 pounds)

Environmental and safety

Temperature

Operating -10 °C to +55 °C (+14 °F to +131 °F) Non-operating -51 °C to +71 °C (-60 °F to +160 °F)

Humidity

MIL-PRF-28800F Class 2

Operating:

5% to 95 \pm 5%RH (relative humidity) in the temperature range of +10 °C to 30 °C (+50 °F to 86 °F)

5% to 75±5% RH above +30 °C to 40 °C (+86 °F to 104 °F) 5% to 45±5% RH above +40 °C up to +55 °C (+86 °F to +131 °F)

<10 °C (+50 °F) humidity is uncontrolled; non-condensing

Altitude

Operating Up to 3000 m (9,842 ft.) Non-operating Up to 12000 m (39,370 ft.)

Dynamics

Vibration

Operating Tektronix Class 3 Random Vibration Test at 0.31 GRMS: 5-500 Hz, 3 Axes at 10 min/axis

Non-Operating MIL-PRF-28800F Class 3

2.06 GRMS, 5 500 Hz, 10 minutes per axis, 3 axes (30 minutes total)

Shock

Operating Test method per Military Standard MIL-PRF-28800F 1-4 Non-Operating Exceeds the requirements of Military Standard MIL-PRF-28800F

Handling and transit

Bench handling, operating MIL-PRF-28800F Class 3 Transit drop, non-operating MIL-PRF-28800F Class 2

Ordering information

Models

RSA600A Series

USB Spectrum Analyzer, 40 MHz acquisition bandwidth.

The RSA600 requires a PC with Windows 7, Windows 8/8.1, or Windows 10, 64-bit operating system. A USB 3.0 connection is required for operation of the RSA600. 8 GB RAM and 20 GB free drive space is required for installation of SignalVu-PC. For full performance of the real time features of the RSA600, an Intel Core i7 4th generation processor is required. Processors of lower performance can be used, with reduced real-time performance. Storage of streaming data requires that the PC be equipped with a drive capable of streaming storage rates of 300 MB/sec.

Includes: USB 3.0 cable (2 M), A-A connection, screw lock, quick-start manual (printed), connector covers, power cord, (see power plug options), USB memory device with SignalVu-PC, API and documentation files.

| Item | Description |
|-------------|--|
| RSA603A | USB real time spectrum analyzer, 9 kHz – 3.0 GHz, 40 MHz acquisition bandwidth |
| Option 04 | Tracking generator, 10 MHz – 3.0 GHz |
| RSA607A | USB real time spectrum analyzer, 9 kHz – 7.5 GHz, 40 MHz acquisition bandwidth |
| Option 04 | Tracking generator, 10 MHz – 7.5 GHz |
| RSA5600RACK | Rackmount, RSA500 and RSA600 Series. Holds 1 RSA500A or 2 RSA600A models |

Options

RSA600A power plug options

North America power plug (115 V, 60 Hz) Opt. A0 Opt. A1 Universal Euro power plug (220 V, 50 Hz) United Kingdom power plug (240 V, 50 Hz) Opt. A2 Opt. A3 Australia power plug (240 V, 50 Hz) Opt. A4 North America power plug (240 V, 50 Hz) Opt. A5 Switzerland power plug (220 V, 50 Hz) Opt. A6 Japan power plug (100 V, 50/60 Hz) Opt. A10 China power plug (50 Hz) Opt. A11 India power plug (50 Hz) Opt. A12 Brazil power plug (60 Hz) Opt. A99 No power cord

RSA600A language options

Opt. L0 English manual Opt. L1 French manual Opt. L2 Italian manual Opt. L3 German manual Opt. L4 Spanish manual Opt. L5 Japanese manual

Opt. L6 Portuguese manual

Opt. L7 Simplified Chinese manual

Opt. L8 Traditional Chinese manual

Opt. L9 Korean manual Opt. L10 Russian manual

Opt. L99 No manual

RSA600A service options

Opt. C3 Calibration Service 3 Years Opt. C5 Calibration Service 5 Years Opt. D1 Calibration Data Report

Opt. D3 Calibration Data Report 3 Years (with Opt. C3) Opt. D5 Calibration Data Report 5 Years (with Opt. C5)

Opt. R5 Repair Service 5 Years (including warranty)

Warranty

- RSA600 series warranty: 3 years.
- FZ-G1 tablet: 3-year warranty with Business Class Support (provided by Panasonic in region of purchase).

Tablet

Tablet controller available

A tablet controller intended for portable applications using the Tektronix RSA306B and RSA500A series spectrum analyzers can be applicated as a controller intended for portable applications using the Tektronix RSA306B and RSA500A series spectrum analyzers can be applicated as a controller intended for portable applications using the Tektronix RSA306B and RSA500A series spectrum analyzers can be applicated as a controller intended for portable applications using the Tektronix RSA306B and RSA500A series spectrum analyzers can be applicated as a controller intended for portable applications using the Tektronix RSA306B and RSA500A series applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable and a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable applications are also as a controller intended for portable and a controller intended for a controller intalso be used with the RSA600A series. The Panasonic ToughPad FZ-G1 is available in limited geographies from Tektronix as shown in the ordering information below.

| Item | Description | Regional availability |
|---------|--|---|
| FZ-G1-N | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord. | Canada, Columbia, Ecuador, Mexico, Philippines, Singapore, United States |
| FZ-G1F | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, digitizer pen and tether, battery charger with power cord | China |
| FZ-G1-I | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord | India |
| FZ-G1-E | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord. | Austria, Baltic States, Belgium, Bosnia, Bulgaria, Chile, Croatia, Czech Republic, Denmark, Finland, France, Germany, Greece, Hungary, Indonesia, Ireland, Italy, Netherlands, Norway, Poland, Portugal, Romania, Slovakia, Slovenia, South Africa, Spain, Sweden, Thailand, Turkey |
| FZ-G1-U | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord. | Egypt, Kenya, Malaysia, United Kingdom |
| FZ-G1-B | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord | Brazil |
| FZ-G1-J | Controller for USB Spectrum Analyzers, Panasonic ToughPad FZ-G1. Includes tablet, battery, digitizer pen and tether, battery charger with power cord | Japan |

Panasonic FZ-G1 accessories

| Item | Description |
|--------------------------|---|
| FZ-VZSU84U ⁶ | Li-ion battery, standard capacity |
| FZ-VZSU88U ⁶ | Long-life battery pack for Panasonic ToughPad FZ-G1 |
| FZ-BNDLG1BATCHRG9 | Single battery charger bundle for FZ-G1. 1 charger and 1 adapter |
| CF-LNDDC120 ⁹ | Lind 120 W 12-32 Volt input vehicle adapter for Tough Pad and RSA500A |
| TBCG1AONL-P | Panasonic Toughmate always on case for FZ-G1 |
| TBCG1XSTP-P | Infocase Toughmate X-strap for Panasonic FZ-G1 |

⁶ Not available in China, Hong Kong, Macau or Mongolia

Licenses

SignalVu-PC application-specific modules

| Application license | Description |
|---------------------|--|
| SVANL-SVPC | AM/FM/PM/Direct Audio Analysis - Node Locked License |
| SVAFL-SVPC | AM/FM/PM/Direct Audio Analysis - Floating License |
| SVTNL-SVPC | Settling Time (frequency and phase) measurements - Node Locked License |
| SVTFL-SVPC | Settling Time (frequency and phase) measurements - Floating License |
| SVMNL-SVPC | General Purpose Modulation Analysis to work with analyzer of acquisition bandwidth <= 40 MHz or MDO - Node Locked License |
| SVMFL-SVPC | General Purpose Modulation Analysis to work with analyzer of acquisition bandwidth <= 40 MHz or MDO- Floating License |
| SVPNL-SVPC | Pulse Analysis to work with analyzer of acquisition bandwidth <= 40 MHz or MDO - Node Locked License |
| SVPFL-SVPC | Pulse Analysis to work with analyzer of acquisition bandwidth <= 40 MHz or MDO- Floating License |
| SVONL-SVPC | Flexible OFDM Analysis - Node Locked License |
| SVOFL-SVPC | Flexible OFDM Analysis - Floating License |
| SV23NL-SVPC | WLAN 802.11a/b/g/j/p measurement - Node Locked License |
| SV23FL-SVPC | WLAN 802.11a/b/g/j/p measurement - Floating License |
| SV24NL-SVPC | WLAN 802.11n measurement (requires SV23) - Node Locked License |
| SV24FL-SVPC | WLAN 802.11n measurement (requires SV23) - Floating License |
| SV25NL-SVPC | WLAN 802.11ac measurement to work with analyzer of acquisition bandwidth <= 40 MHz (requires SV23 and SV24) or MDO - Node Locked License |
| SV25FL-SVPC | WLAN 802.11ac measurement to work with analyzer of acquisition bandwidth <= 40 MHz (requires SV23 and SV24) or MDO - Floating License |
| SV26NL-SVPC | APCO P25 measurement - Node Locked License |
| SV26FL-SVPC | APCO P25 measurement - Floating License |
| SV27NL-SVPC | Bluetooth measurement to work with analyzer of acquisition bandwidth <= 40 MHz or MDO - Node Locked License |
| SV27FL-SVPC | Bluetooth measurement to work with analyzer of acquisition bandwidth <= 40 MHz or MDO- Floating License |
| MAPNL-SVPC | Mapping - Node Locked License |
| MAPFL-SVPC | Mapping - Floating License |
| SV56NL-SVPC | Playback of recorded files - Node Locked License |
| SV56FL-SVPC | Playback of recorded files - Floating License |
| SV60NL-SVPC | Return loss, VSWR, cable loss, and distance to fault - Node Locked License |
| SV60FL-SVPC | Return loss, VSWR, cable loss, and distance to fault - Floating License |
| CONNL-SVPC | SignalVu-PC live link to the MDO4000B series mixed-domain oscilloscopes - Node Locked License |
| CONFL-SVPC | SignalVu-PC live link to the MDO4000B series mixed-domain oscilloscopes - Floating License |
| SV2CNL-SVPC | WLAN 802.11a/b/g/j/p/n/ac and live link to MDO4000B to work with analyzer of acquisition bandwidth <= 40 MHz - Node Locked License |
| SV2CFL-SVPC | WLAN 802.11a/b/g/j/p/n/ac and live link to MDO4000B to work with analyzer of acquisition bandwidth <= 40 MHz - Floating License |
| SV28NL-SVPC | LTE Downlink RF measurement to work with analyzer of acquisition bandwidth <= 40 MHz or MDO - Node Locked License |
| SV28FL-SVPC | LTE Downlink RF measurement to work with analyzer of acquisition bandwidth <= 40 MHz or MDO - Floating License |
| SV54NL-SVPC | Signal survey and classification - Node Locked License |
| SV54FL-SVPC | Signal survey and classification - Floating License |
| SV60NL-SVPC | Return loss, distance to fault, VSWR, cable loss - Node Locked License (requires Option 04 on RSA500A/600A) |
| SV60FL-SVPC | Return loss, distance to fault, VSWR, cable loss - Floating License (requires Option 04 on RSA500A/600A) |
| SV30NL-SVPC | WiGig 802.11ad measurements - Node Locked License |

| Application license | Description |
|---------------------|--|
| SV30FL-SVPC | WiGig 802.11ad measurements - Floating License |
| EDUFL-SVPC | Education-only version of all modules for SignalVu-PC - Floating License |

Recommended accessories

Tektronix offers a wide variety of adapters, attenuators, cables, impedance converters, antennas and other accessories for the RSA600 series.

| General purpose RF cables | |
|--------------------------------------|---|
| 012-1738-00 | Cable,50 Ω , 40 inch,type-N(m) to type-N(M) |
| 012-0482-00 | Cable, 50 Ω , BNC (m) 3 foot (91 cm) |
| Adapters | |
| 103-0045-00 | Adapter, coaxial, 50 Ω type-N(m) to type-BNC(f) |
| 013-0410-00 | Adapter, coaxial, 50 Ω type-N (f) to type-N (f) |
| 013-0411-00 | Adapter, coaxial, 50 Ω type-N (m) to type-N (f) |
| 013-0412-00 | Adapter, coaxial, 50 $\Omega,$ type-N(m) to type-N(m) |
| 013-0402-00 | Adapter, coaxial, 50 Ω type-N (m) to type-N 7/16(m) |
| 013-0404-00 | Adapter, coaxial, 50 Ω type-N(m) to type-7/16 (f) |
| 013-0403-00 | Adapter, coaxial, 50 Ω type-N(m) to type DIN 9.5(m) |
| 013-0405-00 | Adapter, coaxial, 50 Ω type-N(m) to type-DIN 9.5(f) |
| 013-0406-00 | Adapter, coaxial, 50 Ω type-N(m) to type-SMA(f) |
| 013-0407-00 | Adapter, coaxial, 50 Ω type-N(m) to type-SMA(m) |
| 013-0408-00 | Adapter, coaxial, 50 Ω type-N(m) to type-TNC(f) |
| 013-0409-00 | Adapter, coaxial, 50 Ω type-N(m) to type-TNC(m) |
| Attenuators and 50/75 Ω pads | |
| 013-0422-00 | Pad, 50/75 $\Omega,$ minimum loss, type-N(m) 50 Ω to type-BNC(f) 75 Ω |
| 013-0413-00 | Pad, 50/75 $\Omega,$ minimum loss, type-N(m) 50 Ω to type-BNC(m) 75 Ω |
| 013-0415-00 | Pad, 50/75 $\Omega,$ minimum loss, type-N(m) 50 Ω to type-F(m) 75 Ω |
| 015-0787-00 | Pad, 50/75 $\Omega,$ minimum loss, type-N(m) 50 Ω to type-F(f) 75 Ω |
| 015-0788-00 | Pad, 50/75 $\Omega,$ minimum loss, type-N(m) 50 Ω to type-N(f) 75 Ω |
| 011-0222-00 | Attenuator, fixed, 10 dB, 2 W, DC-8 GHz, type-N(f) to type-N(f) $$ |
| 011-0223-00 | Attenuator, fixed, 10 dB, 2 W, DC-8 GHz, type-N(m) to type-N(f) $$ |
| 011-0224-00 | Attenuator, fixed, 10 dB, 2 W, DC-8 GHz, type-N(m) to type-N(m) |
| 011-0228-00 | Attenuator, fixed, 3 dB, 2 W, DC-18 GHz, type-N(m) to type-N(f) $$ |
| 011-0225-00 | Attenuator, fixed, 40 dB, 100 W, DC-3 GHz, type-N(m) to type-N(f) $$ |
| 011-0226-00 | Attenuator, fixed, 40 dB, 50 W, DC-8.5 GHz, type-N(m) to type-N(f) $$ |
| Filters, probes, demonstration board | |
| 119-7246-00 | Pre-filter, general purpose, 824 MHz to 2500 MHz, type-N (f) connector |
| | |

119-7426 Pre-filter, general purpose, 2400 MHz to 6200 MHz, type-N (f) connector

119-4146-00 EMCO E/H-field probes

E/H field probes, lower cost

alternative

Available from Beehive http://beehive-electronics.com/

RSA-DKIT RSA Version 3 demo board with N-BNC adapter, case, antenna, instructions

011-0227-00 Bias-T, type N(m) RF, type N(f) RF+DC, BNC(f) Bias, 1 W, 0.5 A, 2.5 MHz-6 GHz

Chargers, Additional batteries,

Cables, Cases

WFMBA200 Replacement battery pack for RSA500A series

WFMBC200 External battery charger for WFMBA200, charges two batteries

CF-LNDDC120 Lind 120 W 12-32 Volt input vehicle adapter for RSA500A series and Panasonic Tough Pad (not available in China)

016-2109-01 Additional soft carry-case with shoulder strap

174-6810-00 Additional USB 3.0 cable (2 M), A-A connection, screw lock

Tracking generator accessories

A variety of calibration kits and phase-stabilized cables are available for the RSA600 tracking generator when used with the optional cable and antenna measurements software.



CALSOLT35F



Calibration Kits for one-port measurements

for cable and antenna measurements

CALOSLNM Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, Type-N(m), 50 ohm

CALOSLNF Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, Type-N(f), 50 ohm

CALOSLNF Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, 7/16 DIN(m)

CALOSL716F Calibration kit, 3-in-1, open, short, load, DC to 6 GHz, 7/16 DIN(f)

Calibration kit, 4-in-1 3.5 mm (f) short, open, load, through, 13 GHz

CALSOLT35M Calibration kit, 4-in-1 3.5 mm (m) short, open, load, through, 13 GHz

CALSOLTNF Calibration kit, 4-in-1 type-N (f) short, open, load, through, 9 GHz

CALSOLTNM Calibration kit, 4-in-1 type-N (m) short, open, load, through, 9 GHz

CALSOLT716F Calibration kit, 4-in-1 7/16 (f) short, open, load, through, 6 GHz

CALSOLT716M Calibration kit, 4-in-1 7/16 (m) short, open, load, through, 6 GHz

012-1745-00 Cable, rugged, phase-stable, type-N (m) to type-N (f), 5 ft or 1.5 m

012-1746-00 Cable, rugged, phase-stable, type-N(m) to type-N(f), 3.28 ft or 1 m

012-1747-00 Cable, rugged, phase-stable, type-N(m) to 7/16(f), 60 cm (23.6 in.)

| 012-1748-00 | Cable, rugged, phase-stable, type-N(m) to 7/16(f), 3.28 ft or 1 m |
|-------------|--|
| 012-1749-00 | Cable, rugged, phase-stable, type-N(m) to 7/16(f), 5 ft or 1.5 m |
| 012-1750-00 | Cable, rugged, phase-stable, type-N(m) to 7/16(m), 3.28 ft or 1 m |
| 012-1751-00 | Cable, rugged, phase-stable, type-N(m) to 7/16(m), 5 ft or 1.5 m |
| 012-1752-00 | Cable, rugged, phase-stable, type-N(m) to 7/16(m), 60 cm (23.6 in.) |
| 012-1753-00 | Cable, rugged, phase-stable, type-N(m) to DIN 9.5(f), 60 cm (23.6 in.) |
| 012-1754-00 | Cable, rugged, Phase-stable, type-N(m) to DIN 9.5(f), 3.28 ft or 1 m |
| 012-1755-00 | Cable, rugged, phase-stable, type-N(m) to DIN 9.5(f), 5 ft or 1.5 m |
| 012-1756-00 | Cable, rugged, phase-stable, type-N(m) to DIN 9.5(m), 3.28 ft or 1 m $$ |
| 012-1757-00 | Cable, rugged, phase-stable, type-N(m) to DIN 9.5(m), 5 ft or 1.5 m $$ |
| 012-1758-00 | Cable, rugged, phase-stable, type-N(m) to DIN 9.5(m), 60 cm (23.6 in.) |
| 012-1759-00 | Cable, rugged, phase-stable, type-N(m) to TNC(f), 3.28 ft or 1 m |
| 012-1760-00 | Cable, rugged, phase-stable, type-N(m) to TNC(f), 5 ft or 1.5 m $$ |
| 012-1761-00 | Cable, rugged, phase-stable, type-N(m) to TNC(f), 60 cm (23.6 in.) |
| 012-1762-00 | Cable, rugged, phase-stable, type-N(m) to TNC(m), 60 cm (23.6 in.) |
| 012-1763-00 | Cable, rugged, phase-stable, type-N(m) to TNC(m), 3.28 ft or 1 m |
| 012-1764-00 | Cable, rugged, phase-stable, type-N(m) to TNC(m), 5 ft or 1.5 m $$ |
| 012-1765-00 | Cable, rugged, phase-stable, type-N(m) to type-N(f), 60 cm (23.6 in.) |
| 012-1766-00 | Cable, rugged, phase-stable, type-N(m) to type-N(f), 3.28 ft or 1 m $$ |
| 012-1767-00 | Cable, rugged, phase-stable, type-N(m) to type-N(m), 3.28 ft or 1 m $$ |
| 012-1768-00 | Cable, rugged, phase-stable, type-N(m) to type-N(m), 60 cm (23.6 in.) |
| 012-1769-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(f), 60 cm (23.6 in.) $$ |
| 012-1770-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(f), 3.28 ft or 1 m $$ |
| 012-1771-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(f), 5 ft or 1.5 m $$ |
| 012-1772-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(m) 60 cm (23.6 in.) |
| 012-1773-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(m), 3.28 ft or 1 m $$ |
| 012-1774-00 | Cable, rugged, phase-stable, type-N(m) to type-SMA(m), 5 ft or 1.5 m $$ |
| | |





Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.



Product(s) complies with IEEE Standard 488.1-1987, RS-232-C, and with Tektronix Standard Codes and Formats.



Product Area Assessed: The planning, design/development and manufacture of electronic Test and Measurement instruments.

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3086
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea +822 6917 5084, 822 6917 5080
Spain 00800 2255 4835*
Taiwan 886 (2) 2656 6688

Austria 00800 2255 4835*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835*
United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
Canada 1 800 833 9200
Demmark +45 80 88 1401
Germany 00800 2255 4835*
Italy 00800 2255 4835*
Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
Norway 800 16098
Portugal 80 08 12370
South Africa +41 52 675 3777
Switzerland 00800 2255 4835*

USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tek.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

23 Sep 2016 37W-60397-1

www.tek.com

