April 9, 2008



## LM317L 3-Terminal Adjustable Regulator

## **General Description**

The LM317L is an adjustable 3-terminal positive voltage regulator capable of supplying 100mA over a 1.2V to 37V output range. It is exceptionally easy to use and requires only two external resistors to set the output voltage. Further, both line and load regulation are better than standard fixed regulators. Also, the LM317L is available packaged in a standard TO-92 transistor package which is easy to use.

In addition to higher performance than fixed regulators, the LM317L offers full overload protection. Included on the chip are current limit, thermal overload protection and safe area protection. All overload protection circuitry remains fully functional even if the adjustment terminal is disconnected.

Normally, no capacitors are needed unless the device is situated more than 6 inches from the input filter capacitors in which case an input bypass is needed. An optional output capacitor can be added to improve transient response. The adjustment terminal can be bypassed to achieve very high ripple rejection ratios which are difficult to achieve with standard 3-terminal regulators.

Besides replacing fixed regulators, the LM317L is useful in a wide variety of other applications. Since the regulator is "floating" and sees only the input-to-output differential voltage, supplies of several hundred volts can be regulated as long as the maximum input-to-output differential is not exceeded.


Also, it makes an especially simple adjustable switching regulator, a programmable output regulator, or by connecting a fixed resistor between the adjustment and output, the LM317L can be used as a precision current regulator. Supplies with electronic shutdown can be achieved by clamping the adjustment terminal to ground which programs the output to 1.2V where most loads draw little current.


The LM317L is available in a standard TO-92 transistor package, the SO-8 package, and 6-Bump micro SMD package. The LM317L is rated for operation over a  $-25^{\circ}$ C to  $125^{\circ}$ C range.


#### **Features**


- Adjustable output down to 1.2V
- Guaranteed 100mA output current
- Line regulation typically 0.01%V
- Load regulation typically 0.1%
- Current limit constant with temperature
- Eliminates the need to stock many voltages
- Standard 3-lead transistor package
- 80dB ripple rejection
- Available in TO-92, SO-8, or 6-Bump micro SMD package
- Output is short circuit protected
- See AN-1112 for micro SMD considerations

## **Connection Diagrams**









\*NC = Not Internally connected.

Top View (Bump Side Down)

## **Ordering Information**

Package	Part Number	Package Marking	Media Transport	NSC Drawing	
TO-92	LM317LZ	LM317LZ	1.8k Units per Box Z03A		
8-Pin SOIC	LM317LM	LM317LM	Rails	M08A	
	* LM317LIBP	_	250 Units Tape and Reel	BPA06HPB	
6-Bump micro SMD	* LM317LIBPX	_	3k Units Tape and Reel		
	* LM317LITP	_	250 Units Tape and Reel	ТРА06НРА	
	* LM317LITPX	-	3k Units Tape and Reel		

Note: The micro SMD package marking is a single digit manufacturing Date Code only.

## Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Power Dissipation	Internally Limited
Input-Output Voltage Differential	40V
Operating Junction Temperature	
Range	-40°C to +125°C

# Storage Temperature-55°C to +150°CLead Temperature<br/>(Soldering, 4 seconds)260°COutput is Short Circuit ProtectedESD Susceptibility

Human Body Model (Note 5)

2kV

## Electrical Characteristics (Note 2)

ParameterConditionsLine Regulation $T_J = 25^{\circ}C, 3V \le (V_{IN} - V_{OUT}) \le 40V, I_L \le 20mA$ (Note 3)		Min	<b>Typ</b> 0.01	<b>Max</b> 0.04	Units %/V
Thermal Regulation	Thermal Regulation $T_J = 25^{\circ}$ C, 10ms Pulse		0.04	0.2	%/W
Adjustment Pin Current			50	100	μA
Adjustment Pin Current $5mA \le I_{L} \le 100mA$			0.2	5	μA
Change $3V \le (V_{IN} - V_{OUT}) \le 40V, P \le 625mW$					
Reference Voltage	$3V \le (V_{IN} - V_{OUT}) \le 40V$ , (Note 4)	1.20	1.25	1.30	V
	$5mA \le I_{OUT} \le 100mA, P \le 625mW$				
Line Regulation $3V \le (V_{IN} - V_{OUT}) \le 40V, I_L \le 20mA$ (Note 3)			0.02	0.07	%/V
Load Regulation $5mA \le I_{OUT} \le 100mA$ , (Note 3)			0.3	1.5	%
Temperature Stability $T_{MIN} \le T_{J} \le T_{Max}$			0.65		%
Minimum Load Current	$(V_{IN} - V_{OUT}) \le 40V$		3.5	5	mA
	$3V \le (V_{IN} - V_{OUT}) \le 15V$		1.5	2.5	
Current Limit	$3V \le (V_{IN} - V_{OUT}) \le 13V$	100	200	300	mA
	$(V_{IN} - V_{OUT}) = 40V$		50	150	mA
Rms Output Noise, % of $V_{OUT}$	$T_J = 25^{\circ}C$ , 10Hz $\leq f \leq 10$ kHz		0.003		%
Ripple Rejection Ratio	V <sub>OUT</sub> = 10V, f = 120Hz, C <sub>ADJ</sub> = 0		65		dB
	C <sub>ADJ</sub> = 10μF	66	80		dB
Long-Term Stability	T <sub>J</sub> = 125°C, 1000 Hours		0.3	1	%
Thermal Resistance	Z Package 0.4 Leads		180		°C/W
Junction to Ambient	Z Package 0.125 Leads		160		°C/W
	SO-8 Package		165		°C/W
	6-Bump micro SMD		290		°C/W

Note 1: "Absolute Maximum Ratings" indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits.


Note 2: Unless otherwise noted, these specifications apply:  $-25^{\circ}C \leq T_j \leq 125^{\circ}C$  for the LM317L;  $V_{IN} - V_{OUT} = 5V$  and  $I_{OUT} = 40$ mA. Although power dissipation is internally limited, these specifications are applicable for power dissipations up to 625mW.  $I_{MAX}$  is 100mA.


Note 3: Regulation is measured at constant junction temperature, using pulse testing with a low duty cycle. Changes in output voltage due to heating effects are covered under the specification for thermal regulation.


Note 4: Thermal resistance of the TO-92 package is 180°C/W junction to ambient with 0.4 leads from a PC board and 160°C/W junction to ambient with 0.125 lead length to PC board.

Note 5: The human body model is a 100pF capacitor discharged through a  $1.5k\Omega$  resistor into each pin.

## Typical Performance Characteristics (Output capacitor = 0µF unless otherwise noted.)



















**Reference Voltage Temperature Stability** 








### **Application Hints**

In operation, the LM317L develops a nominal 1.25V reference voltage,  $V_{\text{REF}}$ , between the output and adjustment terminal. The reference voltage is impressed across program resistor R1 and, since the voltage is constant, a constant current I<sub>1</sub> then flows through the output set resistor R2, giving an output voltage of

$$V_{OUT} = V_{REF} \left( 1 + \frac{R^2}{R^2} \right) + I_{ADJ}(R^2)$$

Since the 100µA current from the adjustment terminal represents an error term, the LM317L was designed to minimize  $I_{ADJ}$  and make it very constant with line and load changes. To do this, all quiescent operating current is returned to the output establishing a minimum load current requirement. If there is insufficient load on the output, the output will rise.



#### **EXTERNAL CAPACITORS**

An input bypass capacitor is recommended in case the regulator is more than 6 inches away from the usual large filter capacitor. A  $0.1\mu F$  disc or  $1\mu F$  solid tantalum on the input is suitable input bypassing for almost all applications. The device is more sensitive to the absence of input bypassing when adjustment or output capacitors are used, but the above values will eliminate the possibility of problems.

The adjustment terminal can be bypassed to ground on the LM317L to improve ripple rejection and noise. This bypass capacitor prevents ripple and noise from being amplified as the output voltage is increased. With a 10 $\mu$ F bypass capacitor 80dB ripple rejection is obtainable at any output level. Increases over 10 $\mu$ F do not appreciably improve the ripple rejection at frequencies above 120Hz. If the bypass capacitor is used, it is sometimes necessary to include protection diodes to prevent the capacitor from discharging through internal low current paths and damaging the device.

In general, the best type of capacitors to use is solid tantalum. Solid tantalum capacitors have low impedance even at high frequencies. Depending upon capacitor construction, it takes about  $25\mu$ F in aluminum electrolytic to equal  $1\mu$ F solid tantalum at high frequencies. Ceramic capacitors are also good at high frequencies; but some types have a large decrease in capacitance at frequencies around 0.5MHz. For this reason, a 0.01 $\mu$ F disc may seem to work better than a 0.1 $\mu$ F disc as a bypass.

Although the LM317L is stable with no output capacitors, like any feedback circuit, certain values of external capacitance can cause excessive ringing. This occurs with values between 500pF and 5000pF. A 1 $\mu$ F solid tantalum (or 25 $\mu$ F aluminum electrolytic) on the output swamps this effect and insures stability.

#### LOAD REGULATION

The LM317L is capable of providing extremely good load regulation but a few precautions are needed to obtain maximum performance. The current set resistor connected between the adjustment terminal and the output terminal (usually 240 $\Omega$ ) should be tied directly to the output of the regulator rather than near the load. This eliminates line drops from appearing effectively in series with the reference and degrading regulation. For example, a 15V regulator with 0.05 $\Omega$  resistance between the regulator and load will have a load regulation due to line resistance of  $0.05\Omega \times I_L$ . If the set resistor is connected near the load the effective line resistance will be  $0.05\Omega$  (1 + R2/R1) or in this case, 11.5 times worse.

Figure 2 shows the effect of resistance between the regulator and 240  $\Omega$  set resistor.

With the TO-92 package, it is easy to minimize the resistance from the case to the set resistor, by using two separate leads to the output pin. The ground of R2 can be returned near the ground of the load to provide remote ground sensing and improve load regulation.




FIGURE 2. Regulator with Line Resistance in Output Lead

#### THERMAL REGULATION

When power is dissipated in an IC, a temperature gradient occurs across the IC chip affecting the individual IC circuit components. With an IC regulator, this gradient can be especially severe since power dissipation is large. Thermal regulation is the effect of these temperature gradients on output voltage (in percentage output change) per watt of power change in a specified time. Thermal regulation error is independent of electrical regulation or temperature coefficient, and occurs within 5ms to 50ms after a change in power dissipation. Thermal regulation depends on IC layout as well as electrical design. The thermal regulation of a voltage regulator is defined as the percentage change of  $V_{OUT}$ , per watt, within the first 10ms after a step of power is applied. The LM317L specification is 0.2%/W, maximum.

In the Thermal Regulation curve at the bottom of the Typical Performance Characteristics page, a typical LM317L's output changes only 7mV (or 0.07% of  $V_{OUT} = -10V$ ) when a 1W pulse is applied for 10ms. This performance is thus well inside the specification limit of 0.2%/W × 1W = 0.2% maximum. When the 1W pulse is ended, the thermal regulation again shows a 7mV change as the gradients across the LM317L

chip die out. Note that the load regulation error of about 14mV (0.14%) is additional to the thermal regulation error.

#### **PROTECTION DIODES**


When external capacitors are used with *any* IC regulator it is sometimes necessary to add protection diodes to prevent the capacitors from discharging through low current points into the regulator. Most  $10\mu$ F capacitors have low enough internal series resistance to deliver 20A spikes when shorted. Although the surge is short, there is enough energy to damage parts of the IC.

When an output capacitor is connected to a regulator and the input is shorted, the output capacitor will discharge into the output of the regulator. The discharge current depends on the value of the capacitor, the output voltage of the regulator, and

the rate of decrease of V<sub>IN</sub>. In the LM317L, this discharge path is through a large junction that is able to sustain a 2A surge with no problem. This is not true of other types of positive regulators. For output capacitors of 25  $\mu$ F or less, the LM317L's ballast resistors and output structure limit the peak current to a low enough level so that there is no need to use a protection diode.

LM317L

The bypass capacitor on the adjustment terminal can discharge through a low current junction. Discharge occurs when *either* the input or output is shorted. Internal to the LM317L is a 50 $\Omega$  resistor which limits the peak discharge current. No protection is needed for output voltages of 25V or less and 10 $\mu$ F capacitance. *Figure 3* shows an LM317L with protection diodes included for use with outputs greater than 25V and high values of output capacitance.



01

$$V_{OUT} = V_{REF} \left( 1 + \frac{R2}{R1} \right) + I_{ADJ}(R2)$$


D1 protects against C1 D2 protects against C2


#### FIGURE 3. Regulator with Protection Diodes


#### LM317L micro SMD Light Sensitivity

Exposing the LM317L micro SMD package to bright sunlight may cause the  $V_{\text{REF}}$  to drop. In a normal office environment of fluorescent lighting the output is not affected. The LM317


micro SMD does not sustain permanent damage from light exposure. Removing the light source will cause LM317L's  $V_{\text{RFF}}$  to recover to the proper value.










LM317L









\*Sets peak current,  $I_{PEAK} = 0.6V/R1$ \*\*1000µF is recommended to filter out any input transients.








Full output current not available at high input-output voltages †Optional—improves transient response


\*Needed if device is more than 6 inches from filter capacitors


$$\dagger \dagger V_{\text{OUT}} = 1.25V \left(1 + \frac{\text{R2}}{\text{R1}}\right) + I_{\text{ADJ}} \left(\text{R}_{2}\right)$$

#### Fully Protected (Bulletproof) Lamp Driver



Output rate—4 flashes per second at 10% duty cycle





ZOJA (Rev G)

#### TO-92 Plastic Package (Z) NS Package Number Z03A

PKG SYMM (0 5) PKG SYMM C. DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN ( ) FOR REFERENCE ONLY 6x Ø 0.17 В Χ2 LAND PATTERN RECOMMENDATION зүмм C- $0.125 \\ 0.050$ TOP SIDE COATINGвимр 2 sүмм – ⊊ 0.5 X1 -BUMP A1 CORNER SILICON-0.15 A  $6x \ \emptyset_{0.16}^{0.18}$ 

0.001\$ C A\$ B\$

NOTE: UNLESS OTHERWISE SPECIFIED.

1. EPOXY COATING

2. 63Sn/37Pb EUTECTIC BUMP.

3. RECOMMEND NON-SOLDER MASK DEFINED LANDING PAD.

4. PIN A1 IS ESTABLISHED BY LOWER LEFT CORNER WITH RESPECT TO TEXT ORIENTATION PINS ARE NUMBERED COUNTERCLOCKWISE. 5. XXX IN DRAWING NUMBER REPRESENTS PACKAGE SIZE VARIATION WHERE  $X_1$  IS PACKAGE WIDTH,  $X_2$  IS PACKAGE LENGTH AND  $X_3$  IS PACKAGE HEIGHT.


6. REFERENCE JEDEC REGISTRATION MO-211, VARIATION BC.

 $\begin{array}{l} \mbox{6-Bump micro SMD} \\ \mbox{NS Package Number BPA06HPB} \\ \mbox{X}_1 = 0.955 \quad \mbox{X}_2 = 1.615 \quad \mbox{X}_3 = 0.850 \end{array}$ 

www.national.com

LM317L

BPA06XXX (Rev D)



TPA06XXX (Rev B)

NOTE: UNLESS OTHERWISE SPECIFIED.

1. EPOXY COATING

2. 63Sn/37Pb EUTECTIC BUMP.

3. RECOMMEND NON-SOLDER MASK DEFINED LANDING PAD.

4. PIN A1 IS ESTABLISHED BY LOWER LEFT CORNER WITH RESPECT TO TEXT ORIENTATION PINS ARE NUMBERED COUNTERCLOCKWISE. 5. XXX IN DRAWING NUMBER REPRESENTS PACKAGE SIZE VARIATION WHERE  $X_1$  IS PACKAGE WIDTH,  $X_2$  IS PACKAGE LENGTH AND  $X_3$  IS PACKAGE HEIGHT.

6. REFERENCE JEDEC REGISTRATION MO-211, VARIATION BC.

## $\begin{array}{l} \mbox{6-Bump micro SMD} \\ \mbox{NS Package Number TPA06HPA} \\ \mbox{X}_1 = 0.955 \quad \mbox{X}_2 = 1.615 \quad \mbox{X}_3 = 0.500 \end{array}$

## Notes

LM317L

## Notes

For more National Somiconductor product information and proven design tools, visit the following Web sites at

Products		Design Support		
Amplifiers	www.national.com/amplifiers	WEBENCH	www.national.com/webench	
Audio	www.national.com/audio	Analog University	www.national.com/AU	
Clock Conditioners	www.national.com/timing	App Notes	www.national.com/appnotes	
Data Converters	www.national.com/adc	Distributors	www.national.com/contacts	
Displays	www.national.com/displays	Green Compliance	www.national.com/quality/green	
Ethernet	www.national.com/ethernet	Packaging	www.national.com/packaging	
Interface	www.national.com/interface	Quality and Reliability	www.national.com/quality	
LVDS	www.national.com/lvds	Reference Designs	www.national.com/refdesigns	
Power Management	www.national.com/power	Feedback	www.national.com/feedback	
Switching Regulators	www.national.com/switchers			
LDOs	www.national.com/ldo			
LED Lighting	www.national.com/led			
PowerWise	www.national.com/powerwise			
Serial Digital Interface (SDI)	www.national.com/sdi			
Temperature Sensors	www.national.com/tempsensors			
Wireless (PLL/VCO)	www.national.com/wireless			

THE CONTENTS OF THIS DOCUMENT ARE PROVIDED IN CONNECTION WITH NATIONAL SEMICONDUCTOR CORPORATION ("NATIONAL") PRODUCTS. NATIONAL MAKES NO REPRESENTATIONS OR WARRANTIES WITH RESPECT TO THE ACCURACY OR COMPLETENESS OF THE CONTENTS OF THIS PUBLICATION AND RESERVES THE RIGHT TO MAKE CHANGES TO SPECIFICATIONS AND PRODUCT DESCRIPTIONS AT ANY TIME WITHOUT NOTICE. NO LICENSE, WHETHER EXPRESS, IMPLIED, ARISING BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT.

TESTING AND OTHER QUALITY CONTROLS ARE USED TO THE EXTENT NATIONAL DEEMS NECESSARY TO SUPPORT NATIONAL'S PRODUCT WARRANTY. EXCEPT WHERE MANDATED BY GOVERNMENT REQUIREMENTS, TESTING OF ALL PARAMETERS OF EACH PRODUCT IS NOT NECESSARILY PERFORMED. NATIONAL ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR BUYER PRODUCT DESIGN. BUYERS ARE RESPONSIBLE FOR THEIR PRODUCTS AND APPLICATIONS USING NATIONAL COMPONENTS. PRIOR TO USING OR DISTRIBUTING ANY PRODUCTS THAT INCLUDE NATIONAL COMPONENTS, BUYERS SHOULD PROVIDE ADEQUATE DESIGN, TESTING AND OPERATING SAFEGUARDS.

EXCEPT AS PROVIDED IN NATIONAL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, NATIONAL ASSUMES NO LIABILITY WHATSOEVER, AND NATIONAL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY RELATING TO THE SALE AND/OR USE OF NATIONAL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

#### LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

Life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness.

National Semiconductor and the National Semiconductor logo are registered trademarks of National Semiconductor Corporation. All other brand or product names may be trademarks or registered trademarks of their respective holders.

#### Copyright© 2008 National Semiconductor Corporation

For the most current product information visit us at www.national.com



Americas Technical Support Center Email: new.feedback@nsc.com Tel: 1-800-272-9959

National Semiconductor

National Semiconductor Europe Technical Support Center Email: europe.support@nsc.com German Tel: +49 (0) 180 5010 771 English Tel: +44 (0) 870 850 4288 National Semiconductor Asia Pacific Technical Support Center Email: ap.support@nsc.com National Semiconductor Japan Technical Support Center Email: jpn.feedback@nsc.com