

HIGH PERFORMANCE. POWERFUL TOOLBOX.



WaveSurfer 510

Superior User Experience

Powerful, Deep Toolbox

Exceptional Serial Data Tools

Uncompromised Performance


The WaveSurfer 510 combines a superior oscilloscope experience with an extensive toolbox to deliver faster time to insight.



HIGH PERFORMANCE. POWERFUL TOOLBOX.

WaveSurfer 510







The WaveSurfer 510 combines a superior oscilloscope experience with an extensive toolbox to deliver faster time to insight.

- 1 Superior User Experience
- 2 Powerful, Deep Toolbox
- 3 Exceptional Serial Data Tools
- Uncompromised Performance



Faster Time to Insight

Insight alone is not enough.

Markets and technologies change too rapidly.

The timing of critical design

decisions is significant.

Time to insight is what matters.



MAUI - SUPERIOR USER EXPERIENCE



MAUI – Most Advanced User Interface was developed to put all the power and capabilities of the modern oscilloscope right at your fingertips. Designed for touch; all important oscilloscope controls are accessed through the intuitive touch screen. Built for simplicity; time saving shortcuts and intuitive dialogs simplify setup. Made to solve; a deep set of debug and analysis tools helps identify problems and find solutions quickly.

Designed for Touch

MAUI is designed for touch. Operate the oscilloscope just like a phone or tablet with the most unique touch screen features on any oscilloscope. All important controls are always one touch away. Touch the waveform to position or zoom in for more details using intuitive actions.

Built for Simplicity

MAUI is built for simplicity. Basic waveform viewing and measurement tools as well as advanced math and analysis capabilities are seamlessly integrated in a single user interface. Time saving shortcuts and intuitive dialogs simplify setup and shorten debug time.

Made to Solve

MAUI is made to solve. A deep set of integrated debug and analysis tools help identify problems and find solutions quickly. Unsurpassed integration provides critical flexibility when debugging. Solve problems fast with powerful analysis tools.

MAUI with OneTouch


MAUI with OneTouch introduces a new paradigm for oscilloscope user experience. Dramatically reduce setup time with revolutionary drag and drop actions to copy and setup channels, math functions, and measurement parameters without lifting a finger. Use common gestures like drag, drop, and flick to instinctively interact with the oscilloscope. Quickly enable a new channel, math or measurement using the "Add New" button and simply turn off any trace with a flick of the finger. These OneTouch innovations provide unsurpassed efficiency in oscilloscope operation.



- Channel, timebase, and trigger descriptors provide easy access to controls without navigating menus.
- Configure parameters by touching measurement results.
- Shortcuts to commonly used functions are displayed at the bottom of the channel, math and memory menus.
- Use the "Add New" button for one-touch trace creation.
- Drag to change source, copy setup, or turn on new trace.
- Drag to copy measurement parameters to streamline setup process.
- G Drag to quickly position cursors on a trace.



POWERFUL, DEEP TOOLBOX





Our Heritage

Teledyne LeCroy's 50+ year heritage has its origins in the high-speed collection of data in the field of high-energy physics, and the processing of long records to extract meaningful insight. We didn't invent the oscilloscope, but we did invent the digital oscilloscope, which can take full advantage of advanced digital signal processing and waveshape analysis tools to provide unparalleled insight.

Our Obsession

Our developers are true to our heritage — they are more obsessed with making better and smarter tools than anybody else. Our tools and operating philosophy are standardized across much of our product line for a consistent user experience. Our mission is to help you use these tools to understand problems, including the ones you don't even know you have. Our deep toolbox inspires insight; and your moment of insight is our reward.

Our Invitation

Our Periodic Table of Oscilloscope
Tools provides a framework to
understand the toolsets that Teledyne
LeCroy has created and deployed in
our oscilloscopes. Visit our interactive
website to learn more about what we
offer and how we can help you develop
and debug more efficiently.

teledynelecroy.com/tools

WAVESURFER 510 AT A GLANCE

The WaveSurfer 510 combines the MAUI with OneTouch user interface with powerful waveform processing, in addition to advanced math, measurement, and debug tools, to quickly analyze and find the root cause of problems. The 12.1" touch-screen display of the WaveSurfer 510 is the largest in its class and makes viewing waveform abnormalities fast and easy.

Key Features

1 GHz, 10 GS/s, up to 16 Mpts/ch

MAUI with OneTouch

- Designed for touch
- Built for simplicity
- Made to solve

WaveScan - Advanced Search and Find

LabNotebook Documentation and Report Generation

History Mode - Waveform Playback

Sequence Mode Segmented Memory

Spectrum Analyzer Mode

Power Analysis Software

Serial Trigger and Decode

- I²C, SPI, UART
- CAN, LIN, FlexRay, SENT
- Ethernet 10/100BaseT, USB 1.0/1.1/2.0, USB2.0-HSIC
- Audio (I²S, LJ, RJ, TDM)
- MIL-STD-1553, ARINC 429
- MIPI D-PHY, DigRF 3G, DigRF v4
- Manchester, NRZ



Superior User Experience

The WaveSurfer 510 with MAUI
OneTouch sets the standard for
oscilloscope user experience by
providing the most unique touch
features on any oscilloscope. Common
gestures are used to instinctively interact
with the oscilloscope and dramatically
reduce setup time. Convenience and
efficiency are optimized - all common
operations can be performed with one
touch and do not require opening and
closing of pop-up dialogs or menus.

Uncompromised Performance

Many 1 GHz oscilloscopes are available at attractive entry-point prices, however, they are often limited in sample rate, memory or features. The WaveSurfer 510 provides uncompromised 1 GHz performance with up to 10 GS/s per channel and 32 Mpts of memory.

Advanced Debug Tools

Advanced debug tools make the WaveSurfer 510 an unparalleled debug and analysis machine providing 10 GS/s sample rate on 4 channels, 32 Mpts of memory, sequence mode, history mode, advanced math functions, and 2 simultaneous math traces.

Capture Debug, Analyze, Document

Easily accessible measurement, math and debug tools, plus a wide variety of serial data protocol decoders, and active probes ensure the WaveSurfer 510 can capture and analyze any type of waveform and simplify the debug process. The LabNotebook tool provides a fast way to save waveforms, save setups and screen images, report results, and view offline.



Key Attributes

- 1 12.1" Widescreen (16 x 9) high resolution WXGA color touch screen display
- 2 MAUI with OneTouch optimized for convenience and efficiency
- 3 "Add New" button for fast waveform creation
- "Push" Knobs All knobs have push functionality that provide shortcuts to common actions such as Set to Variable, Find Trigger Level, Zero Offset, and Zero Delay
- Waveform Control Knobs –
 Control channel, zoom, math
 and memory traces with the
 multiplexed vertical and
 horizontal knobs
- 6 Dedicated Cursor Knob –
 Select type of cursor, position
 them on your signal, and read
 values without ever opening
 a menu
- 7 Dedicated buttons to quickly access popular debug tools.

- 8 L-Bus connectivity allow for the addition of the MS-250 or MS-500 mixed signal options.
- 9 Easy connectivity with four USB 3.1 ports and three USB 2.0 ports




ADVANCED TOOLS FOR WAVEFORM ANALYSIS



Embedded Controller Design and Debug

Save time when working with embedded controllers by adding high-performance mixed signal capability with the WaveSurfer 510. Capture digital signals up to 250 MHz with up to 10 Mpts/Ch memory, 1 GS/s and 18 channels. Quickly and easily isolate specific serial data events with I²C, SPI, UART, RS-232, USB 1.0/1.1/2.0, USB2-HSIC, 10/100Base T ENET, Audio (I²S, LJ, RJ, TDM), MIL-STD-1553, ARINC 429, MIPI D-PHY, DigRF, CAN, CAN FD, LIN, FlexRay, SENT, Manchester, and NRZ trigger and decode options.



WaveScan Advanced Search and Find Tool

Quickly search waveforms for runts, glitches or other anomalies with WaveScan.



LabNotebook Documentation and Report Generation Tool

Save all results and data with a single button press and create custom reports with LabNotebook.



Pass/Fail Mask Testing

Built-in masking testing quickly identifies problems and marks the location. A history of the pass/fail results can be displayed on the screen.

Enhanced Resolution

The enhanced resolution (ERES) feature improves vertical resolution of the oscilloscope resulting in cleaner traces and the ability to see more signal details. Up to 3 bits of ERES can be applied.

Advanced Math and Measure


Use automatic measurement parameters with statistics and histicons as well as math functions to understand every waveform detail.

WaveStream Fast Viewing Mode

WaveStream provides a vibrant, intensity graded (256 levels) display with a fast update to closely simulate the look and feel of an analog oscilloscope.


LabNotebook Documentation Tool

LabNotebook is a one-button tool to save and restore waveforms, measurements and settings without navigating multiple menus. Custom reports can be created and easily shared; saved waveforms can be measured and analyzed later both on the oscilloscope or offline using the WaveStudio PC Utility.



WaveStudio Offline Analysis Tool

WaveStudio is a fast and easy way to analyze acquired waveforms offline. Offline tools include x and y axis cursors for quick measurements and 21 built-in automatic measurements for more precise and accurate results. WaveStudio can also connect to the oscilloscope for direct data transfer to the PC. Data saved with LabNotebook can be shared with others using WaveStudio for easy collaboration.



Advanced Probe Interface

The advanced active probe interface gives tremendous flexibility for measuring high voltages, high frequencies, currents, or differential signals.

High Impedance Active Probes



High Bandwidth Differential Probes



High Voltage Differential Probes



High Voltage Passive Probes




Current Probes



ADVANCED DEBUG TOOLS

The WaveSurfer 510 includes the advanced debug tools which makes it an unparalleled debug and analysis machine. The high sample rate of 10 GS/s on all 4 channels. 32 Mpts of memory, sequence mode segmented memory, history mode waveform playback, 13 additional math functions, and 2 simultaneous math traces, all included in this powerful debug package, enable the WaveSurfer 510 to perform advanced analysis on long captures with 10x oversampling to find the root cause of problems.



- A With 10 GS/s and 16 Mpts per channel every detail of a signal will be captured and displayed. In 4 channel operation 1.6ms of data can be captured at full sample rate, in 2 channel mode, 3.2ms, to ensure no detail or anomaly is missed.
- B Configure and view 2 simultaneous math traces, each math trace can perform dual math operation enabling complex analysis and faster troubleshooting.
- Advanced math and measurements capabilities allow deeper analysis. Included functions are absolute value, average (summed or continuous), derivative, difference, envelope, enhanced resolution, exp (base e), exp (base 10), FFT, floor, integral, invert, log (base e), log (base 10), product, ratio, reciprocal, rescale, roof, square, square root, sum, trend and zoom.
- Display up to 6 measurement parameters together with statistics, including mean, minimum, maximum, standard deviation, and total number. Each occurrence of each parameter is measured and added to the statistics table. Histicons provide a fast, dynamic view of parameters and waveshape characteristics. Parameter gates define the location for measurement on the source waveform.




Advanced Waveform Capture with Sequence Mode

Use Sequence mode to store up to 5,000 triggered events as "segments" into memory. This can be ideal when capturing many fast pulses in quick succession or when capturing events separated by long time periods. Sequence mode provides timestamps for each acquisition and minimizes dead-time between triggers to less than 1 µs. Combine Sequence mode with advanced triggers to isolate rare events over time and analyze afterwards.

History Mode Waveform Playback

Scroll back in time using History Mode to view previous waveforms and isolate anomalies. Use cursors and measurement parameters to quickly find the source of problems. History mode is always available with a single button press, no need to enable this mode and never miss a waveform.




SERIAL TRIGGER AND DECODE OPTIONS

The HDO4000A features the widest range and most complete serial data debug and validation solutions.

- Triggering
- Decoding

	WaveSurfer 510 Serial Data Protocol Support	Trigger	Decode	
Embedded trial Computing	I ² C	•	•	
	SPI	•	•	
	UART-RS232	•	•	
	USB2-HSIC		•	
	CAN	•	•	
npu	CAN FD	•	•	
/e +	FlexRay	•	•	
moti	LIN	•	•	
Auto	SENT		•	
Avionics Automotive + Industrial	ARINC429		•	
ionic	MIL-STD-1553	•	•	
Ą	SPACEWIRE		•	
als	Ethernet (10/100Base-T)		•	
putin	MDIO		•	
Computing + Peripherals	USB 1.1/2.0	•	•	
+	8b/10b	•	•	
MIPI	D-PHY/CSI-2/DSI		•	
	DigRF3G		•	
	DigRFv4		•	
	SPMI		•	
	Audio (I ² S, LJ, RJ, TDM)	•	•	
Other	Manchester		•	
	NRZ	•	•	



Trigger

Powerful, flexible triggers designed by people who know the standards, with the unique capabilities you want to isolate unusual events. Conditional data triggering permits maximum flexibility and highly adaptable error frame triggering is available to isolate error conditions. Efficiently acquire bursted data using Sequence Mode to maximize the oscilloscope's memory usage. Sequence Mode enables the oscilloscope to ignore idle time and acquire only data of interest.





Decode

Decoded protocol information is color-coded to specific portions of the serial data waveform and transparently overlaid for an intuitive, easy-to-understand visual record. All decoded protocols are displayed in a single time-interleaved table. Touch a row in the interactive table to quickly zoom to a packet of interest and select a column header to create filter criteria, as is commonly done in spreadsheets. Easily search through long records for specific protocol events using the built-in search feature.

EMBEDDED CONTROLLER DESIGN AND DEBUG

Teledyne LeCroy's versatile WaveSurfer 510 mixed signal oscilloscope combines the powerful WaveSurfer 510 with the flexibility of digital inputs using the MS-250. In addition, the many triggering and decoding options turn the WaveSurfer 510 into an all-in-one analog, digital, and serial data trigger, acquisition, and debug machine.

High-performance Mixed Signal Capabilities

Embedded controller design and debug involves capturing and viewing a number of different types of signals. These signals are typically a mix of analog, digital, and serial data waveforms from a combination of analog sensors, microcontrollers and peripheral devices. With the ability to capture digital signals with speeds up to 250 MHz and long memory of 10 Mpts/Ch the WaveSurfer 510 provides unmatched mixed signal performance. The WaveSurfer 510 is the ideal tool for testing embedded systems with 8-bit microcontrollers or slower digital signals. With 18 digital inputs each with 250 MHz maximum input frequency and 10 Mpts/Ch memory, the WaveSurfer 510 is an outstanding value and provides a complete set of tools for embedded system testing.

Extensive Triggering

The WaveSurfer 510 has extensive digital trigger capabilities. Normal oscilloscope triggers will operate on digital inputs. Cross-pattern triggering allows for simple or complex trigger patterns to be setup with any combination of analog and digital channels. Event triggering can be configured to arm on an analog signal and trigger on a digital pattern.

Quick Mixed Signal Setup, Easy-to-use


Unlike a traditional Logic Analyzer, the WaveSurfer 510 is easy to use. A simple connection links the oscilloscope with the digital inputs so users can start viewing signals and begin debugging quickly. In addition, all standard oscilloscope tools are readily accessible. Signal debug is simple, using standard oscilloscope tools, such as cursors, measurement parameters, and zooming.



SPECTRUM AND POWER ANALYZER

Simple Frequency Domain Analysis

Get better insight to the frequency content of any signal with use of the Spectrum Analyzer mode on the WaveSurfer 510. This mode provides a spectrum analyzer style user interface with controls for start/stop frequency or center frequency and span. The unique peak search automatically labels spectral components and presents frequency and level in an interactive table. Utilize up to 20 markers to automatically identify harmonics and monitor how the spectrum changes over time using the spectrogram which can display a 2D or 3D history of the frequency content.



Power Analyzer Automates Switching Device Loss Measurements

Quickly measure and analyze the operating characteristics of power conversion devices and circuits with the Power Analyzer option. Critical power switching device measurements, control loop modulation analysis, and line power harmonic testing are all simplified with a dedicated user interface and automatic measurements. Areas of turn-on, turn-off, and conduction loss are all identified with color-coded waveform overlays for faster analysis.

Power Analyzer provides quick and easy setup of voltage and current inputs and makes measurements as simple as the push of a button. Tools are provided to help reduce sources of measurement



errors and the measurement parameters provide details of single cycle or average device power losses. Beyond the advanced power loss measurement capabilities, the Power Analyzer modulation analysis capabilities provide insight to understand control loop response to critical events such as a power supply's soft start performance or step response to line and load changes.

The Line Power Analysis tool allows simple and quick pre-compliance testing to EN 61000-3-2.

SPECIFICATIONS

WaveSurfer 510

Vertical System	WaveSurfer 510
Analog Bandwidth @ 50 Ω (-3 dB)	1 CUz (, 2 m)//div)
	1 GHz (≥ 2 mV/div)
Analog Bandwidth @ 1 MΩ (-3 dB)	500 MHz (typical)
Rise Time (10–90%, 50 Ω)	415 ps (typical)
Input Channels	''
Vertical Resolution	8-bits; up to 11-bits with enhanced resolution (ERES) 50 Ω: 1 mV/div–1 V/div, fully variable; 1 MΩ: 1 mV/div–10 V/div, fully variable
Sensitivity	
DC Vertical Gain Accuracy (Gain Component of DC Accuracy)	±1% F.S. (typical), offset at 0 V
Channel-Channel Isolation	DC up to rated BW: 40 dB (>100:1), (For any two ProBus input channels, same v/div settings, typical)
Offset Range	50 Ω:
	±1.6 V @ 1 mV- 4.95 mV/div, ±4 V @ 5 mV-9.9 mV/div, ±8 V @ 10 mV-19.8 mV/div, ±10 V @ 20 mV-1 V/div
	1 M Ω :
	±1.6 V @ 1 mV-4.95 mV/div, ±4 V @ 5 mV-9.9 mV/div, ±8 V @ 10 mV-19.8 mV/div, ±16 V @ 20 mV-100 mV/div,
	±8 V @ 10 mV = 19.8 mV/div, ±16 V @ 20 mV = 100 mV/div, ±80 V @ 102 mV = 1.0 V/div, ±160 V @ 1.02 V=10 V/div
DC Vertical Offset Accuracy	±(1.5% of offset setting +1% of full scale + 1 mV) (test limit)
Maximum Input Voltage	$\pm (1.3\% \text{ of othset setting} + 1\% \text{ of rule scale} + 1 \text{ ThV})$ (test limit) 50 Ω : 5 V _{rms} ± 10 V peak; 1 MΩ : 400 V max. (DC + peak AC < 10 kHz)
Input Coupling	1 MΩ: AC, DC, GND; 50 Ω: DC, GND
Input Impedance	$10 \Omega \pm 2\%$ or $1 \Omega \parallel 17$ pF, $10 \Omega \parallel 9.5$ pF with supplied Probe
Bandwidth Limiters	20 MHz, 200 MHz
Danuwidin Limiters	20 Minz, 200 Minz
Horizontal System	
Timebases	Internal timebase common to 4 input channels; an external clock may be applied at the EXT input
Acquisition Modes	Real-time, Roll, Random Interleaved Sampling (RIS), Sequence
Time/Division Range	200 ps/div - 1000 s/div
	RIS available at ≤ 10 ns/div;
	Roll Mode available at ≥ 100 ms/div and ≤ 5 MS/s
Clock Accuracy	≤ 1.5 ppm +(aging of 0.5 ppm/yr from last calibration)
Sample Clock Jitter	Up to 10µs Acquired Time Range: 100fsrms (Internal Timebase Reference) Up to 10ms Acquired Time Range: 360fsrms (Internal Timebase Reference)
Delta Time Measurement Accuracy	
•	$\sqrt{2} * \left[\left(\frac{\text{Noise}}{\text{Noise}} \right)^2 + \left(\text{Sample Clock Jitter} \right)^2 \right] (RMS) + (clock accuracy * reading) (seconds)$
	\ \ SlewRate \
Jitter Measurement Floor	$\left(\frac{Noise}{SlewRate}\right)^2 + (Sample Clock Jitter)^2 (RMS, seconds, TIE)$
	V V 7
Channel-Channel Deskew Range	±9 x time/div. setting, 100 ms max., each channel
Acquisition System	
Sample Rate (Single-Shot)	10 GS/s on 4 Ch
Sample Rate (Repetitive)	50 GS/s for repetitive signals (20 ps/div to 10 ns/div)
Memory Length	16 Mpts/ch for all channels, 32 Mpts (interleaved) (5,000 segments)
(# of Segments in Sequence Mode)	
Intersegment Time	1 μs
Averaging	Summed averaging to 1 million sweeps; continuous averaging to 1 million sweeps
Enhanced Resolution (ERES)	From 8.5 to 11 bits vertical resolution
Envelope (Extrema)	Envelope, floor, or roof for up to 1 million sweeps
Interpolation	Linear or Sin x/x

SPECIFICATIONS

WaveSurfer 510

T: : 0 :	WaveSurfer 510
Triggering System	Name of Acts Charles and Otton
Modes	Normal, Auto, Single, and Stop
Sources	Any input channel, Ext, Ext/10, or line; slope and level unique to each source (except line trigger)
Coupling Mode	DC, AC, HFRej, LFRej 0 - 100% of memory size (adjustable in 1% increments or 100 ns)
Pre-trigger Delay	
Post-trigger Delay Hold-off	0 - 10,000 divisions in real time mode, limited at slower time/div settings or in roll mode From 2 ns up to 20 s or from 1 to 99,999,999 events
	≤ 3.5 ps RMS (typical)
Trigger and Interpolator Jitter Internal Trigger Level Range	±4.1 div from center (typical)
External Trigger Level Range	Ext (±0.4 V); Ext/10 (±4 V)
Maximum Trigger Level Harige	1,000,000 waveforms/second (in Sequence Mode, up to 4 channels)
Trigger Sensitivity with Edge Trigger	2 div @ < 1 GHz
(Ch 1-4)	1.5 div @ < 500 MHz
	1 div @ < 200 MHz
	0.9 div @ < 10 MHz
	(DC, AC, and LFRej coupling, ≥ 10 mV/div, 50 Ω)
Trigger Sensitivity with Edge Trigger	2 div @ <1 GHz
(External Input)	1.5 div @ < 500 MHz
	1 div @ < 200 MHz
	0.9 div @ < 10 MHz (DC, AC, and LFRej coupling)
May Trigger Frequency SMART Trigge	r 1.0 GHz @ ≥ 10 mV/div (minimum triggerable width 750 ps)
iviax. Trigger i requericy, SiviAnt Trigge	in 1.0 on 2 to 1117/div (itili ilitiditi diggerable widdi 100 μs)
Basic Triggers	
Edge	Triggers when signal meets slope (positive, negative, or either) and level condition
Width	Triggers on positive or negative glitches with selectable widths.
Glitch	Triggers on positive or negative glitches with selectable widths. Minimum width 200 ps, maximum width: 20 s
Window	Triggers when signal exits a window defined by adjustable thresholds
Pattern	Logic combination (AND, NAND, OR, NOR) of 5 inputs (4 channels and external trigger input). Each source can be hig low, or don't care. The High and Low level can be selected independently. Triggers at start or end of the pattern.
TV-Composite Video	Triggers NTSC or PAL with selectable line and field:
	HDTV (720p, 1080i, 1080p) with selectable frame rate (50 or 60 Hz) and Line; or CUSTOM with selectable Fields (1–8), Lines (up to 2000), Frame Rates (25, 30, 50, or 60 Hz),
	Interlacing (1:1, 2:1, 4:1, 8:1), or Synch Pulse Slope (Positive or Negative)
Runt	Trigger on positive or negative runts defined by two voltage limits and two time limits. Select between 1 ns and 20 ns
Slew Rate	Trigger on edge rates. Select limits for dV, dt, and slope. Select edge limits between 1 ns and 20 ns.
Interval	Triggers on intervals selectable between 1 ns and 20 s.
Dropout	Triggers if signal drops out for longer than selected time between 1 ns and 20 s.
Triggers with Exclusion Technology	Trigger on intermittent faults by specifying the expected behavior and triggering when that condition is not met
Qualified (Timeout or State/Edge Qualified)	Triggers on any input source only if a defined state or edge occurred on another input source. Delay between sources is selectable by time or events.
Low Speed Serial Protocol Trigger (Optional)	I2C, SPI (SPI, SSPI, SIOP), UART-RS232, CAN1.1, CAN2.0, CAN FD, LIN, FlexRay, MIL-STD-1553, AudioBus (I2S, LJ, RJ, TDM), USB1.x/2.0, SATA
Measurement Tools	
Measurement Functionality	Display up to 6 measurement parameters together with statistics, including mean, minimum, maximum, standard deviation, and total number. Each occurrence of each parameter is measured and added to the statistics table. Parameter gates define the location for measurement on the source waveform.
Measurement Parameters -	Delay (from trigger, 50%), Duty Cycle, Edges, Fall Time (90-10, 80-20), Frequency, Period, Δ Period, Phase, Rise Tim (10-90, 20-80), Skew, Width+, Width-
Horizontal + Jitter Measurement Parameters - Vertical	Amplitude, Base, Maximum, Mean, Minimum, Peak-to-Peak, RMS, Std. Deviation, Top.
Measurement Parameters - Pulse	Area, Base, Fall Time (90-10, 80-20), Overshoot (positive, negative), Rise Time (10-90, 80-20), Top, Width+, Width-
Math Tools	
Math Functionality	Display up to 2 math functions traces (F1-F2). The easy-to-use graphical interface simplifies setup of up to two op
Math Operators - Basic Math	erations on each function trace, and function traces can be chained together to perform math-on-math. Average (summed), Average (continuous), Difference (–), Envelope, Exp (base e, base 10), Floor, Invert (negate), Log (base
·	e, base 10), Product (x), Ratio (/), Reciprocal, Rescale (with units), Roof, Sum (+).
Holdoff	Holdoff between A and B, B and C, C and D is selectable by time (1ns to 20s) or number of events.
	Measurement trigger selection as the last stage in a Cascade precludes a holdoff setting between the
Math Operators - Filters	prior stage and the last stage. Enhanced resolution (to 11 bits vertical)
Math Operators - Filters Math Operators - Frequency Analysis	FFT (power spectrum, magnitude), up to full record length. Select from Rectangular, VonHann, Hamming, FlatTop
	and Blackman Harris windows.
Math Operators - Functions	Absolute value, Derivative, Integral, Invert (negate), Reciprocal, Rescale (with units), Square, Square root, Zoom (identity).

Measurement and Math Integration

Trend (datalog) of up to 1 million measurement parameters

SPECIFICATIONS

	WaveSurfer 510		
Pass/Fail Testing			
	Mask Test (pre-defined or user-defined mask, waveform All In, All Out, Any In, or Any Out conditions) with following THEN Save (waveforms), Stop, Alarm, (send) Pulse, Hardcopy (send email, save screen image, save to clipboard, send to printer), or (save) LabNotebook.		
Display System			
Display Size	Color 12.1" widescreen flat panel TFT-Active Matrix with high resolution touch screen		
Display Resolution	WXGA; 1280 x 800 pixels		
Number of Traces	Display a maximum of 16 traces. Simultaneously display channel, zoom, memory and math traces.		
Grid Styles	Auto, Single,X-Y, Single+X-Y		
Waveform Representation	Sample dots joined, or sample dots only		
Processor/CPU			
Type	Intel® Core™ i3-6100 Dual, 3.7 GHz (or better)		
Processor Memory	8 GB standard		
Operating System	Microsoft Windows® 7 For Embedded Systems 64Bits		
Oscilloscope Operating Software	Teledyne LeCroy MAUI™		
Real Time Clock	Date and time displayed with waveform in hardcopy files. SNTP support to synchronize to precision internal clocks		
Connectivity			
Ethernet Port	Supports 2 10/100/1000BaseT Ethernet interface (RJ45 ports)		
USB	4 side USB 3.1 Gen1 ports, and 1 front USB 3.1 port support Windows compatible devices		
USB Device Port	1 port - USBTMC over USB 3.1 Gen1		
GPIB Port (optional)	Supports IEEE – 488.2 (External)		
External Monitor Port	DisplayPort 1.1 and HDMI to support customer-supplied external monitor. Includes support for extended desktop operation with UHD (3840 x 2160) pixel resolution and split-grid capability on external monitor. Supports touch screen integration of external monitor (Note: external display can not use a Fujitsu touch-screen driver).		
Remote Control	Via Windows Automation, or via Teledyne LeCroy Remote Command Set		
Network Communication Standard	VXI-11 or VICP, LXI Class C (v1.2) Compliant		
Probes			
Standard Probes	Qty. (4) ÷10 Passive Probes		
Probing System	ProBus. Automatically detects and supports a variety of compatible probes		
Power Requirements			
Voltage	100-240 VAC ±10% at 50/60 Hz ±5%; 110-120 VAC ±10% at 400 Hz ±5%; Automatic AC Voltage Selection		
Power Consumption (Nominal)	285 W / 285 VA		
Max Power Consumption	375 W / 375 VA (with all PC peripherals and active probes connected to 4 channels)		
	_ · · · · · · · · · · · · · · · · · · ·		
Environmental Temperature (Operating)	+5 °C to +40 °C		
Temperature (Non-Operating)	-20 °C to +60 °C		
Humidity (Operating)	5% to 90% relative humidity (non-condensing) up to +31 °C.		
riarmany (operating)	Upper limit derates to 50% relative humidity (non-condensing) at +40 °C.		
Humidity (Non-Operating)	5% to 95% relative humidity (non-condensing) as tested per MIL-PRF-28800F		
Altitude (Operating)	Up to 10,000 ft. (3048 m) at or below +30 °C		
Altitude (Non-Operating)	Up to 40,000 ft. (12,192 m)		
Random Vibration (Operating)	0.31 grms 5 Hz to 500 Hz, 15 minutes in each of three orthogonal axes		
Random Vibration (Non-Operating)	2.4 grms 5 Hz to 500 Hz, 15 minutes in each of three orthogonal axes		
Functional Shock	30 g peak, half sine, 11 ms pulse, 3 shocks (positive and negative) in each of three orthogonal axes, 18 shocks total		
Physical Dimensions			
Dimensions (HWD)	12.44"H x 16.42"W x 9.37"D (316 x 417 x 238 mm)		
Weight	22.8 lbs. (10.3 kg)		
Certifications			
	CE Compliant, UL and cUL listed; conforms to UL 61010-1 (3rd Edition), UL 61010-2-030 (1st Edition) CAN/CSA C22.2 No. 61010-1-12		
Warranty and Service			
	3-year warranty; calibration recommended annually. Optional service programs include extended warranty, upgrades, and calibration services.		

ORDERING INFORMATION

Product Description	Product Code	Product Description Produc	ct Code
WaveSurfer 510 Oscilloscopes		Serial Data Options	
1 GHz, 10 GS/s, 4 Ch, 16 Mpts/Ch DSO with 12.1"	WaveSurfer 510	ARINC 429 Symbolic Decode Option WS510-ARINC429bus	DSymbolic
Touch Screen Display. 10 GS/s, 32 Mpts Interleaved			udiobus TD
Included with Standard Configurations		CAN Trigger and Decode Option WS510-0	CANbus TD
÷10 Passive Probe (Total of 1 Per Channel), Protective	Front Cover, Getting	CAN FD Trigger and Decode Option WS510-CAN	FDbus TD
Started Guide, Commercial NIST Traceable Calibration	n with Certificate,	D-PHY Decode Option WS510-D	DPHYbus D
Power Cable for the Destination Country, 3-year Warra	anty	DigRF 3G Decode Option WS510-DigF	RF3Gbus D
		DigRF v4 Decode Option WS510-Dig	RFv4bus D
General Accessories		ENET Decode Option WS510-E	ENETbus D
External GPIB Accessory	USB2-GPIB	FlexRay Trigger and Decode Option WS510-Flex	Raybus TD
Instrument Cart	OC1021-A	I ² C, SPI and UART Trigger and Decode Option W	/S510-EMB
Hard Carrying Case	WS510-HARDCASE	I ² C Bus Trigger and Decode Option WS510-	-I2Cbus TD
Rack Mount Accessory	WS510-RACK	LIN Trigger and Decode Option WS510-	-LINbus TD
Local Language Organism		Manchester Decode Option WS510-Manch	esterbus D
Local Language Overlays	WOE10 ED OEDWAN		MDIObus D
German Front Panel Overlay	WS510-FP-GERMAN	MIL-STD-1553 Trigger and Decode Option WS51	0-1553 TD
French Front Panel Overlay	WS510-FP-FRENCH	NRZ Decode Option WS510-	-NRZbus D
Italian Front Panel Overlay	WS510-FP-ITALIAN	SENT Decode Option WS510-S	SENTbus D
Spanish Front Panel Overlay	WS510-FP-SPANISH	SpaceWire Decode Option WS510-S	SENTbus D
Japanese Front Panel Overlay	WS510-FP-JAPANESE	SPI Bus Trigger and Decode Option WS510-	-SPIbus TD
Korean Front Panel Overlay	WS510-FP-KOREAN	SPMI Decode Option WS510-S	SPMIbus D
Chinese (Tr) Front Panel Overlay	WS510-FP-CHNES-TR	UART and RS-232 Trigger and Decode Option WS510-UART-RS:	232bus TD
Chinese (Simp) Front Panel Overlay Russian Front Panel Overlay	WS510-FP-CHNES-SI WS510-FP-RUSSIAN	USB 2.0 Decode Option WS510-U	JSB2bus D
Mixed Signal Solutions 500 MHz, 18 Channels, 2 GS/s, 50 Mpts/ch	MS-500	Probes 500 MHz Passive Probe, 2.5mm, 10:1, 10 M Ω	PP008
Mixed Signal Oscilloscope Option	MO 500 00	500 MHz Passive Probe 10:1, 10 M Ω	PP011
250 MHz,36 Ch,1 GS/s, 25 Mpts/ch (500 MHz,18 Ch,2 GS/s, 50 Mpts/ch Interleaved)	MS-500-36	500 MHz Passive Probe, 2.5mm, 10:1, 10 MΩ	PP021
Mixed Signal Option		500 MHz Passive Probe, 5mm, 10:1, 10 MΩ	PP025
250 MHz, 18 Channels, 1 GS/s, 10 Mpts/ch	MS-250	700 V, 15 MHz High-Voltage Differential Probe	AP031
Mixed Signal Oscilloscope Option	1010 200	200 MHz, 3.5 pF, 1 MΩ Active Differential Probe	ZD200
Wince digital additionable aparent		500 MHz, 1.0 pF Active Differential Probe, ±8 V	ZD500
Mixed Signal Accessories		1 GHz, 1.0 pF, 1 M Ω Active Differential Probe	ZD1000
Extra Large Gripper Probe Set, Includes 22 probes	PK400-0	1.5 GHz, 1.0 pF Active Differential Probe, ±8 V	ZD1500
Large Gripper Probe Set for 0.10 Inch (2.54 mm)	PK400-1	Deskew Calibration Source for CP031 and CP030	DCS015
Pin Pitch. Includes 10 Probes with Color-coded Leads		30 A; 50 MHz Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pulse	CP030
Medium Gripper Probe Set for 0.04 Inch (1.0 mm) Pin Pitch. Includes 10 Probes with Color-coded Leads	PK400-2	30 A; 50 MHz High Sensitivity Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pulse	CP030A
Small Gripper Probe Set for 0.008 Inch (0.2 mm)	PK400-3	30 A; 100 MHz Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pulse	CP031
Pin Pitch. Includes 10 Probes with Color-coded Leads 18-pin 3M Interface Cable MSO-3M	MSO-3M	30 A; 100 MHz High Sensitivity Current Probe – AC/DC; 30 A _{rms} ; 50 A _{peak} Pulse	CP031A
(Mates with 3M Part Number 2520-6002)	1000 0101	150 A; 10 MHz Current Probe – AC/DC; 150 A _{rms} ; 500 A _{peak} Pulse	CP150
36 Channel Mictor Connector	MSO-Mictor	500 A; 2 MHz Current Probe – AC/DC; 500 A _{rms} ; 700 A _{peak} Pulse	CP500
(Includes 1 MSO-MICTOR-SHROUD)		1,400 V, 100 MHz High-Voltage Differential Probe	ADP305
16" Digital Lead Set, D0-D17	MSO-DLS-18	1,400 V, 20 MHz High-Voltage Differential Probe	ADP300
16" Digital Lead Set, D18-D35	MSO-DLS-36	1 Ch, 100 MHz Differential Amplifier with Precision Voltage Source	DA1855A
		1.5 GHz, 0.9 pF, 1 MΩ High Impedance Active Probe	ZS1500
		Set of 4 ZS1500, 1.5 GHz, 0.9 pF, 1 M Ω ZS1500 High Impedance Active Probe	-QUADPAK
		1 CUIZ 0.0 pE 1 MQ High Impedance Active Probe	701000

1 GHz, 0.9 pF, 1 M Ω High Impedance Active Probe

Set of 4 ZS1000, 1 GHz, 0.9 pF, 1 M Ω

High Impedance Active Probe

ZS1000

ZS1000-QUADPAK

Product Description

Product Code

Probes (cont'd)

· robes (conta)	
25 MHz High Voltage Differential Probe	HVD3102
1kV, 25 MHz High Voltage Differential Probe without tip	HVD3102-NOACC
Accessories	
80 MHz High Voltage Differential Probe with 6m cable	HVD3106-6M
120 MHz High Voltage Differential Probe	HVD3106
1kV, 120 MHz High Voltage Differential Probe without tip	HVD3106-NOACC
Accessories	
2kV, 120 MHz High Voltage Differential Probe	HVD3206
2kV, 80 MHz High Voltage Differential Probe with 6m cable	HVD3206-6M
6kV, 100 MHz High Voltage Differential Probe	HVD3605
100:1 400 MHz 50 MΩ 1 kV High-voltage Probe	HVP120
100:1 400 MHz 50 MΩ 4 kV High-voltage Probe	PPE4KV
1000:1 400 MHz 50 MΩ 5 kV High-voltage Probe	PPE5KV
1000:1 400 MHz 50 MΩ 6 kV High-voltage Probe	PPE6KV
TekProbe to ProBus Probe Adapter	TPA10
Set of 4 TPA10 TekProbe to ProBus Probe Adapters.	TPA10-QUADPAK
Includes soft carrying case.	

Customer Service Teledyne LeCroy oscilloscopes and probes are designed, built, and tested to ensure high reliability. In the unlikely event you experience difficulties, our digital oscilloscopes are fully warranted for three years and our probes are warranted for one year. This warranty includes: No charge for return shipping Long-term 7-year support Upgrade to latest software at no charge



1-800-5-LeCroy teledynelecroy.com

Local sales offices are located throughout the world. Visit our website to find the most convenient location.