Disposable Antistatic Wrist Strap



Description

Image shown for illustration purposes only.

Disposable wrist straps are designed for users who temporarily need an ESD wrist strap without the requirement of being durable or reusable. Individually bagged and complete with instructions, the strap can be shipped with components and devices for assembly eg. memory upgrades, servers components, circuit boards etc.

Features

- · Low cost, static control that can be shipped with your product
- · 1.5m total length
- · Fully adjustable wrist loop no messy adhesives
- Copper foil for ground connection no tape residues left on equipment
- · Each wrist strap is packaged individually with instructions
- 1 Mohm resistance



Product code	Description	Length
RND 560-00211	Disposable Antistatic Wrist Strap	1.5 m

Instructions



Remove wrist strap from external packaging.



Peel back to reveal adhesive layer.




Place the tacky side on wrist.



Ensure wrist is covered and the black conductive strip is against the skin.



Peel back to reveal copper foil layer at the other end.



Fix the copper foil to your grounding point.